

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P310248

Luminaire Tested: **24FCZ2-50-UNV-L82765-RDP-CP187-W2A-U-3000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P310248
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-50-UNV-L82765-RDP-CP187-W2A-U-3000K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS WITH INSERT, 0.187" POLYCARB SHEET
Light Source: (168) 3000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2717.0 lumens
Efficiency: N/A
Efficacy: 64.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 42.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P310248

CATALOG NUMBER: 24FCZ2-50-UNV-L82765-RDP-CP187-W2A-U-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P310248

CATALOG NUMBER: 24FCZ2-50-UNV-L82765-RDP-CP187-W2A-U-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67
3	88	77	68	62	86	76	67	61	72	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1150	1150	1150
5°	1154	1147	1152
10°	1151	1147	1153
15°	1149	1147	1154
20°	1140	1146	1158
25°	1136	1148	1160
30°	1126	1145	1164
35°	1116	1142	1169
40°	1103	1141	1183
45°	1085	1141	1210
50°	1061	1148	1247
55°	1034	1167	1302
60°	990	1189	1375
65°	927	1231	1459
70°	843	1288	1569
75°	715	1359	1640
80°	564	1368	1327
85°	417	1041	1166



TEST NUMBER: P310248

CATALOG NUMBER: 24FCZ2-50-UNV-L82765-RDP-CP187-W2A-U-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.0	3.0
10°-20°	233.3	8.6
20°-30°	356.7	13.1
30°-40°	436.1	16.0
40°-50°	464.8	17.1
50°-60°	444.4	16.4
60°-70°	376.4	13.9
70°-80°	253.0	9.3
80°-90°	71.4	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	671.0	24.7
0°-40°	1107.1	40.7
0°-60°	2016.2	74.2
0°-90°	2717.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2717.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	854	854	854	854	854	
5°	854	853	849	853	853	81
15°	825	825	823	830	829	233
25°	766	768	774	780	782	353
35°	679	685	695	709	712	425
45°	570	580	600	625	636	440
55°	441	457	497	536	555	393
65°	291	321	387	438	458	289
75°	138	187	261	306	315	147
85°	27	55	67	73	76	33
90°	0	0	0	0	0	



TEST NUMBER: P310248

CATALOG NUMBER: 24FCZ2-50-UNV-L82765-RDP-CP187-W2A-U-3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	854.4	854.4	854.4	854.4	854.4
2.5°	855.8	855.8	851.7	854.4	854.4
5°	854.4	853.1	849.0	853.1	853.1
7.5°	850.4	849.0	846.3	850.4	849.0
10°	842.3	842.3	839.6	843.6	843.6
12.5°	835.6	834.2	832.9	838.2	836.9
15°	824.8	824.8	823.4	830.2	828.8
17.5°	811.3	812.6	814.0	819.4	820.7
20°	796.5	799.2	800.5	808.6	808.6
22.5°	783.0	784.3	787.0	795.1	795.1
25°	765.5	768.2	773.6	780.3	781.6
27.5°	748.0	749.3	756.0	765.5	766.8
30°	725.0	729.1	737.2	748.0	749.3
32.5°	704.8	708.9	718.3	729.1	731.8
35°	679.2	684.6	695.4	708.9	711.6
37.5°	656.3	660.4	673.8	688.7	692.7
40°	628.0	636.1	649.6	667.1	673.8
42.5°	599.7	607.8	624.0	646.9	655.0
45°	570.1	579.5	599.7	625.3	636.1
47.5°	540.4	551.2	574.1	603.8	615.9
50°	506.7	520.2	548.5	582.2	595.7
52.5°	474.4	490.5	521.5	559.3	576.8
55°	440.7	456.9	497.3	536.4	555.2
57.5°	403.0	424.5	469.0	513.5	533.7
60°	367.9	388.1	442.0	490.5	510.8
62.5°	330.2	357.1	415.1	466.3	486.5
65°	291.1	320.7	386.8	438.0	458.2
67.5°	256.1	288.4	358.5	409.7	429.9
70°	214.3	254.7	327.5	378.7	398.9
72.5°	175.2	219.7	295.1	345.0	363.9
75°	137.5	187.3	261.4	305.9	315.4
77.5°	102.4	155.0	226.4	245.3	238.5
80°	72.8	124.0	176.5	167.1	171.2
82.5°	47.2	94.3	109.2	124.0	128.0
85°	27.0	55.3	67.4	72.8	75.5
87.5°	12.1	20.2	27.0	27.0	25.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)