

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P309277

Luminaire Tested: **24FCZ2-35-UNV-L82765-HRP-CA08-W2A-U-3500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P309277  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: 24FCZ2-35-UNV-L82765-HRP-CA08-W2A-U-3500K  
Description: 2'X4' TROFFER LED MODULE, HIGH EFFICIENCY RND PERF. LENS, 0.08" ACRYLIC SHEET  
Light Source: (168) 3500K TUNABLE CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2409.0 lumens  
Efficiency: N/A  
Efficacy: 85.7 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P309277

CATALOG NUMBER: 24FCZ2-35-UNV-L82765-HRP-CA08-W2A-U-3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P309277

CATALOG NUMBER: 24FCZ2-35-UNV-L82765-HRP-CA08-W2A-U-3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	96	93	96	93	90	92	90	87	89	86	84	82
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	77	73	70	67
3	89	78	69	62	86	76	68	62	73	66	61	70	64	59	68	63	58	56
4	81	68	59	52	79	67	59	52	65	57	51	62	56	50	60	54	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	63	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	36	30	57	44	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	24	35	29	24	23

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1052	1052	1052
5°	1053	1049	1053
10°	1050	1049	1055
15°	1044	1047	1056
20°	1037	1044	1058
25°	1024	1039	1060
30°	1012	1036	1064
35°	996	1030	1065
40°	978	1024	1075
45°	956	1023	1092
50°	925	1022	1121
55°	892	1029	1162
60°	841	1045	1213
65°	777	1069	1281
70°	679	1107	1365
75°	551	1164	1410
80°	406	1141	1141
85°	312	841	949



TEST NUMBER: P309277

CATALOG NUMBER: 24FCZ2-35-UNV-L82765-HRP-CA08-W2A-U-3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.0	3.1
10°-20°	212.6	8.8
20°-30°	323.7	13.4
30°-40°	393.0	16.3
40°-50°	415.2	17.2
50°-60°	391.8	16.3
60°-70°	325.8	13.5
70°-80°	214.3	8.9
80°-90°	58.4	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	610.3	25.3
0°-40°	1003.4	41.7
0°-60°	1810.4	75.2
0°-90°	2409.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2409.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	782	782	782	782	782	
5°	780	780	777	780	780	74
15°	749	750	751	758	758	211
25°	690	694	700	712	714	318
35°	606	613	627	643	648	379
45°	502	512	538	564	574	387
55°	380	396	439	480	495	339
65°	244	272	336	385	402	241
75°	106	154	224	265	271	114
85°	20	44	54	60	62	25
90°	0	0	0	0	0	



TEST NUMBER: P309277

CATALOG NUMBER: 24FCZ2-35-UNV-L82765-HRP-CA08-W2A-U-3500K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	781.6	781.6	781.6	781.6	781.6
2.5°	782.6	781.6	777.6	781.6	781.6
5°	779.6	779.6	776.6	779.6	779.6
7.5°	774.5	774.5	772.5	776.6	776.6
10°	768.5	768.5	767.5	772.5	772.5
12.5°	759.4	760.4	759.4	765.5	765.5
15°	749.3	750.3	751.3	758.4	758.4
17.5°	736.2	738.2	740.3	748.3	749.3
20°	724.1	725.1	729.2	738.2	739.2
22.5°	708.0	711.0	716.0	725.1	728.2
25°	689.8	693.9	699.9	712.0	714.0
27.5°	672.7	675.7	683.8	696.9	700.9
30°	651.5	656.5	666.6	679.7	684.8
32.5°	631.3	636.4	648.5	662.6	666.6
35°	606.1	613.2	627.3	643.4	648.5
37.5°	581.9	589.0	606.1	624.3	630.3
40°	556.7	564.8	582.9	604.1	612.2
42.5°	529.5	540.6	560.7	583.9	593.0
45°	502.2	512.3	537.5	563.8	573.8
47.5°	473.0	485.1	512.3	543.6	555.7
50°	441.7	456.9	488.1	522.4	535.5
52.5°	410.5	427.6	462.9	501.2	515.4
55°	380.2	396.3	438.7	480.1	495.2
57.5°	346.9	367.1	413.5	457.9	473.0
60°	312.6	334.8	388.3	434.7	450.8
62.5°	278.4	303.6	364.1	410.5	427.6
65°	244.1	272.3	335.8	385.3	402.4
67.5°	210.8	242.0	309.6	359.0	376.2
70°	172.5	211.8	281.4	329.8	346.9
72.5°	137.2	182.5	254.1	299.5	314.7
75°	105.9	154.3	223.9	265.2	271.3
77.5°	77.7	126.1	192.6	206.7	207.8
80°	52.4	100.9	147.2	145.2	147.2
82.5°	34.3	75.6	92.8	103.9	104.9
85°	20.2	44.4	54.5	60.5	61.5
87.5°	10.1	15.1	19.2	20.2	22.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)