

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P310210

Luminaire Tested: **24FCZ2-50HE-UNV-L82765-RDP-CP187-W2A-U-6500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P310210
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-50HE-UNV-L82765-RDP-CP187-W2A-U-6500K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS WITH INSERT, 0.187" POLYCARB SHEET
Light Source: (336) 6500K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3023.0 lumens
Efficiency: N/A
Efficacy: 75.4 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 40.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P310210

CATALOG NUMBER: 24FCZ2-50HE-UNV-L82765-RDP-CP187-W2A-U-6500K

Luminous Intensity Polar Plot





TEST NUMBER: P310210

CATALOG NUMBER: 24FCZ2-50HE-UNV-L82765-RDP-CP187-W2A-U-6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67
3	88	77	68	62	86	76	67	61	72	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1279	1279	1279
5°	1284	1276	1282
10°	1280	1276	1282
15°	1278	1276	1285
20°	1269	1275	1288
25°	1264	1278	1291
30°	1253	1274	1295
35°	1241	1271	1300
40°	1227	1269	1317
45°	1207	1270	1347
50°	1180	1277	1387
55°	1150	1298	1449
60°	1101	1323	1529
65°	1031	1370	1623
70°	938	1434	1746
75°	795	1512	1824
80°	628	1522	1475
85°	463	1158	1297



TEST NUMBER: P310210

CATALOG NUMBER: 24FCZ2-50HE-UNV-L82765-RDP-CP187-W2A-U-6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.2	3.0
10°-20°	259.5	8.6
20°-30°	396.9	13.1
30°-40°	485.2	16.0
40°-50°	517.1	17.1
50°-60°	494.4	16.4
60°-70°	418.8	13.9
70°-80°	281.5	9.3
80°-90°	79.4	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	746.6	24.7
0°-40°	1231.8	40.7
0°-60°	2243.3	74.2
0°-90°	3023.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3023.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	951	951	951	951	951	
5°	951	949	945	949	949	90
15°	918	918	916	924	922	259
25°	852	855	861	868	870	393
35°	756	762	774	789	792	473
45°	634	645	667	696	708	489
55°	490	508	553	597	618	437
65°	324	357	430	487	510	322
75°	153	208	291	340	351	164
85°	30	62	75	81	84	37
90°	0	0	0	0	0	



TEST NUMBER: P310210

CATALOG NUMBER: 24FCZ2-50HE-UNV-L82765-RDP-CP187-W2A-U-6500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	950.6	950.6	950.6	950.6	950.6
2.5°	952.1	952.1	947.6	950.6	950.6
5°	950.6	949.1	944.6	949.1	949.1
7.5°	946.1	944.6	941.7	946.1	944.6
10°	937.2	937.2	934.2	938.7	938.7
12.5°	929.7	928.2	926.7	932.7	931.2
15°	917.7	917.7	916.2	923.7	922.2
17.5°	902.7	904.2	905.7	911.7	913.2
20°	886.2	889.2	890.7	899.7	899.7
22.5°	871.2	872.7	875.7	884.7	884.7
25°	851.7	854.7	860.7	868.2	869.7
27.5°	832.2	833.7	841.2	851.7	853.2
30°	806.7	811.2	820.2	832.2	833.7
32.5°	784.2	788.7	799.2	811.2	814.2
35°	755.7	761.7	773.7	788.7	791.7
37.5°	730.2	734.7	749.7	766.2	770.7
40°	698.7	707.7	722.7	742.2	749.7
42.5°	667.3	676.2	694.2	719.7	728.7
45°	634.3	644.8	667.3	695.7	707.7
47.5°	601.3	613.3	638.8	671.8	685.2
50°	563.8	578.8	610.3	647.8	662.8
52.5°	527.8	545.8	580.3	622.3	641.8
55°	490.3	508.3	553.3	596.8	617.8
57.5°	448.3	472.3	521.8	571.3	593.8
60°	409.3	431.8	491.8	545.8	568.3
62.5°	367.4	397.4	461.8	518.8	541.3
65°	323.9	356.9	430.3	487.3	509.8
67.5°	284.9	320.9	398.9	455.8	478.3
70°	238.4	283.4	364.4	421.3	443.8
72.5°	194.9	244.4	328.4	383.9	404.8
75°	152.9	208.4	290.9	340.4	350.9
77.5°	114.0	172.4	251.9	272.9	265.4
80°	81.0	137.9	196.4	185.9	190.4
82.5°	52.5	105.0	121.5	137.9	142.4
85°	30.0	61.5	75.0	81.0	84.0
87.5°	13.5	22.5	30.0	30.0	28.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)