

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P309253

Luminaire Tested: **24FCZ2-35HE-UNV-L82765-HRP-CP125-W2A-U-5000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P309253
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-35HE-UNV-L82765-HRP-CP125-W2A-U-5000K
Description: 2'X4' TROFFER LED MODULE, HIGH EFFICIENCY RND PERF. LENS, 0.125" POLYCARB SHEET
Light Source: (336) 5000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2455.0 lumens
Efficiency: N/A
Efficacy: 92.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 26.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P309253

CATALOG NUMBER: 24FCZ2-35HE-UNV-L82765-HRP-CP125-W2A-U-5000K

Luminous Intensity Polar Plot





TEST NUMBER: P309253

CATALOG NUMBER: 24FCZ2-35HE-UNV-L82765-HRP-CP125-W2A-U-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	96	93	96	93	90	92	90	87	89	86	84	82
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	77	73	70	67
3	89	78	69	62	86	76	68	62	73	66	61	70	64	59	68	63	58	56
4	81	68	59	52	79	67	59	52	65	57	51	62	56	50	60	54	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	63	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	36	30	57	44	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	24	35	29	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1072	1072	1072
5°	1073	1069	1073
10°	1070	1069	1076
15°	1064	1067	1077
20°	1057	1064	1079
25°	1044	1059	1080
30°	1031	1056	1084
35°	1015	1050	1086
40°	996	1043	1096
45°	974	1042	1113
50°	942	1041	1142
55°	909	1049	1184
60°	857	1065	1236
65°	792	1089	1306
70°	691	1128	1391
75°	561	1186	1437
80°	414	1163	1163
85°	318	857	968



TEST NUMBER: P309253

CATALOG NUMBER: 24FCZ2-35HE-UNV-L82765-HRP-CP125-W2A-U-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.5	3.1
10°-20°	216.7	8.8
20°-30°	329.9	13.4
30°-40°	400.5	16.3
40°-50°	423.2	17.2
50°-60°	399.3	16.3
60°-70°	332.0	13.5
70°-80°	218.4	8.9
80°-90°	59.6	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	622.0	25.3
0°-40°	1022.6	41.7
0°-60°	1845.0	75.2
0°-90°	2455.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2455.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	796	796	796	796	796	
5°	794	794	791	794	794	75
15°	764	765	766	773	773	215
25°	703	707	713	726	728	324
35°	618	625	639	656	661	387
45°	512	522	548	574	585	394
55°	388	404	447	489	505	345
65°	249	278	342	393	410	246
75°	108	157	228	270	276	116
85°	21	45	56	62	63	25
90°	0	0	0	0	0	



TEST NUMBER: P309253

CATALOG NUMBER: 24FCZ2-35HE-UNV-L82765-HRP-CP125-W2A-U-5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	796.5	796.5	796.5	796.5	796.5
2.5°	797.6	796.5	792.4	796.5	796.5
5°	794.5	794.5	791.4	794.5	794.5
7.5°	789.3	789.3	787.3	791.4	791.4
10°	783.2	783.2	782.1	787.3	787.3
12.5°	773.9	774.9	773.9	780.1	780.1
15°	763.6	764.7	765.7	772.9	772.9
17.5°	750.3	752.3	754.4	762.6	763.6
20°	737.9	739.0	743.1	752.3	753.4
22.5°	721.5	724.6	729.7	739.0	742.1
25°	703.0	707.1	713.3	725.6	727.7
27.5°	685.5	688.6	696.8	710.2	714.3
30°	663.9	669.1	679.4	692.7	697.9
32.5°	643.4	648.5	660.9	675.2	679.4
35°	617.7	624.9	639.3	655.7	660.9
37.5°	593.0	600.2	617.7	636.2	642.4
40°	567.3	575.6	594.1	615.6	623.9
42.5°	539.6	550.9	571.4	595.1	604.3
45°	511.8	522.1	547.8	574.5	584.8
47.5°	482.0	494.4	522.1	554.0	566.3
50°	450.2	465.6	497.4	532.4	545.7
52.5°	418.3	435.8	471.7	510.8	525.2
55°	387.5	403.9	447.1	489.2	504.6
57.5°	353.6	374.1	421.4	466.6	482.0
60°	318.6	341.2	395.7	443.0	459.4
62.5°	283.7	309.4	371.0	418.3	435.8
65°	248.7	277.5	342.2	392.6	410.1
67.5°	214.8	246.7	315.5	365.9	383.4
70°	175.7	215.8	286.7	336.1	353.6
72.5°	139.8	186.0	259.0	305.2	320.7
75°	107.9	157.2	228.2	270.3	276.5
77.5°	79.1	128.5	196.3	210.7	211.7
80°	53.4	102.8	150.1	148.0	150.1
82.5°	34.9	77.1	94.6	105.9	106.9
85°	20.6	45.2	55.5	61.7	62.7
87.5°	10.3	15.4	19.5	20.6	22.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)