

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P309373

Luminaire Tested: **24FCZ2-40-UNV-L82765-HRP-CA08-W2A-U-6500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P309373  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: 24FCZ2-40-UNV-L82765-HRP-CA08-W2A-U-6500K  
Description: 2'X4' TROFFER LED MODULE, HIGH EFFICIENCY RND PERF. LENS, 0.08" ACRYLIC SHEET  
Light Source: (168) 6500K TUNABLE CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment: 

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2934.0 lumens  
Efficiency: N/A  
Efficacy: 85.8 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 34.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P309373

CATALOG NUMBER: 24FCZ2-40-UNV-L82765-HRP-CA08-W2A-U-6500K

### Luminous Intensity Polar Plot





TEST NUMBER: P309373

CATALOG NUMBER: 24FCZ2-40-UNV-L82765-HRP-CA08-W2A-U-6500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	96	93	96	93	90	92	90	87	89	86	84	82
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	77	73	70	67
3	89	78	69	62	86	76	68	62	73	66	61	70	64	59	68	63	58	56
4	81	68	59	52	79	67	59	52	65	57	51	62	56	50	60	54	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	63	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	36	30	57	44	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	24	35	29	24	23

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1281	1281	1281
5°	1282	1277	1282
10°	1279	1277	1286
15°	1271	1275	1287
20°	1263	1272	1289
25°	1247	1265	1291
30°	1233	1261	1296
35°	1213	1255	1297
40°	1191	1247	1310
45°	1164	1246	1330
50°	1126	1244	1365
55°	1086	1253	1415
60°	1025	1273	1478
65°	947	1302	1560
70°	826	1348	1662
75°	671	1418	1718
80°	495	1389	1389
85°	380	1024	1156



TEST NUMBER: P309373

CATALOG NUMBER: 24FCZ2-40-UNV-L82765-HRP-CA08-W2A-U-6500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	90.2	3.1
10°-20°	259.0	8.8
20°-30°	394.2	13.4
30°-40°	478.7	16.3
40°-50°	505.7	17.2
50°-60°	477.2	16.3
60°-70°	396.8	13.5
70°-80°	261.0	8.9
80°-90°	71.1	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	743.4	25.3
0°-40°	1222.1	41.7
0°-60°	2205.0	75.2
0°-90°	2934.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2934.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	952	952	952	952	952	
5°	950	950	946	950	950	90
15°	913	914	915	924	924	257
25°	840	845	852	867	870	388
35°	738	747	764	784	790	462
45°	612	624	655	687	699	471
55°	463	483	534	585	603	412
65°	297	332	409	469	490	294
75°	129	188	273	323	330	139
85°	25	54	66	74	75	30
90°	0	0	0	0	0	



TEST NUMBER: P309373

CATALOG NUMBER: 24FCZ2-40-UNV-L82765-HRP-CA08-W2A-U-6500K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	951.9	951.9	951.9	951.9	951.9
2.5°	953.2	951.9	947.0	951.9	951.9
5°	949.5	949.5	945.8	949.5	949.5
7.5°	943.3	943.3	940.9	945.8	945.8
10°	936.0	936.0	934.7	940.9	940.9
12.5°	924.9	926.1	924.9	932.3	932.3
15°	912.6	913.9	915.1	923.7	923.7
17.5°	896.7	899.1	901.6	911.4	912.6
20°	881.9	883.2	888.1	899.1	900.3
22.5°	862.3	866.0	872.1	883.2	886.8
25°	840.2	845.1	852.4	867.2	869.6
27.5°	819.3	823.0	832.8	848.8	853.7
30°	793.5	799.6	811.9	827.9	834.0
32.5°	768.9	775.1	789.8	807.0	811.9
35°	738.2	746.8	764.0	783.7	789.8
37.5°	708.7	717.3	738.2	760.3	767.7
40°	678.0	687.9	710.0	735.8	745.6
42.5°	644.9	658.4	682.9	711.2	722.2
45°	611.7	624.0	654.7	686.6	698.9
47.5°	576.1	590.8	624.0	662.1	676.8
50°	538.0	556.4	594.5	636.3	652.2
52.5°	499.9	520.8	563.8	610.5	627.7
55°	463.1	482.7	534.3	584.7	603.1
57.5°	422.5	447.1	503.6	557.7	576.1
60°	380.8	407.8	472.9	529.4	549.1
62.5°	339.0	369.7	443.4	499.9	520.8
65°	297.3	331.6	409.0	469.2	490.1
67.5°	256.7	294.8	377.1	437.3	458.2
70°	210.0	257.9	342.7	401.7	422.5
72.5°	167.0	222.3	309.5	364.8	383.2
75°	129.0	187.9	272.7	323.0	330.4
77.5°	94.6	153.5	234.6	251.8	253.0
80°	63.9	122.8	179.3	176.9	179.3
82.5°	41.8	92.1	113.0	126.5	127.7
85°	24.6	54.0	66.3	73.7	74.9
87.5°	12.3	18.4	23.3	24.6	27.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)