

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P310648

Luminaire Tested: **24FCZ2-35-UNV-L82765-CP125-W2A-U-5000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P310648
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-15)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-35-UNV-L82765-CP125-W2A-U-5000K
Description: 2'X4' TROFFER LED MODULE, RIBBED LENS, 0.125" POLYCARB SHEET
Light Source: (168) 5000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3271.0 lumens
Efficiency: N/A
Efficacy: 114.0 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.29 / 1.38
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 28.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P310648

CATALOG NUMBER: 24FCZ2-35-UNV-L82765-CP125-W2A-U-5000K

Luminous Intensity Polar Plot





TEST NUMBER: P310648

CATALOG NUMBER: 24FCZ2-35-UNV-L82765-CP125-W2A-U-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	92	89	92	89	87	88	86	84	82
2	98	89	81	75	95	87	80	74	83	78	73	80	75	71	77	73	69	67
3	89	77	69	62	86	76	68	61	73	66	60	70	64	59	67	62	58	56
4	81	68	59	52	79	67	58	52	64	57	51	62	56	50	60	54	50	47
5	74	61	52	45	72	60	51	44	58	50	44	56	49	43	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	64	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	37	31	57	45	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	25	35	29	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1451	1451	1451
5°	1454	1445	1454
10°	1446	1441	1453
15°	1433	1436	1454
20°	1416	1427	1453
25°	1394	1416	1452
30°	1367	1404	1450
35°	1340	1390	1451
40°	1310	1380	1460
45°	1278	1371	1472
50°	1240	1367	1495
55°	1209	1370	1525
60°	1162	1381	1577
65°	1109	1396	1634
70°	1050	1439	1725
75°	937	1501	1884
80°	799	1589	1925
85°	570	1575	1843



TEST NUMBER: P310648

CATALOG NUMBER: 24FCZ2-35-UNV-L82765-CP125-W2A-U-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.1	3.1
10°-20°	291.9	8.9
20°-30°	440.9	13.5
30°-40°	531.4	16.2
40°-50°	557.9	17.1
50°-60°	521.9	16.0
60°-70°	431.0	13.2
70°-80°	293.7	9.0
80°-90°	100.2	3.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	834.9	25.5
0°-40°	1366.3	41.8
0°-60°	2446.1	74.8
0°-90°	3271.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3271.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1079	1079	1079	1079	1079	
5°	1077	1076	1070	1077	1077	102
15°	1029	1030	1031	1042	1044	290
25°	939	943	954	972	978	432
35°	816	825	846	875	883	510
45°	672	686	721	760	774	518
55°	516	536	584	632	650	460
65°	348	378	438	494	513	346
75°	180	221	289	343	362	192
85°	37	73	102	115	119	46
90°	0	0	0	0	0	



TEST NUMBER: P310648

CATALOG NUMBER: 24FCZ2-35-UNV-L82765-CP125-W2A-U-5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1078.7	1078.7	1078.7	1078.7	1078.7
2.5°	1079.8	1078.7	1073.3	1078.7	1077.7
5°	1076.6	1075.5	1070.1	1076.6	1076.6
7.5°	1069.0	1069.0	1063.6	1071.2	1072.2
10°	1058.1	1058.1	1054.9	1063.6	1063.6
12.5°	1045.1	1045.1	1045.1	1053.8	1054.9
15°	1028.8	1029.9	1031.0	1041.8	1044.0
17.5°	1009.3	1011.5	1014.7	1027.7	1029.9
20°	988.7	990.8	996.3	1011.5	1014.7
22.5°	962.6	968.1	975.6	993.0	996.3
25°	938.7	943.1	953.9	972.4	977.8
27.5°	909.4	916.0	930.1	949.6	957.2
30°	880.1	886.7	904.0	926.8	933.3
32.5°	848.7	858.4	876.9	900.8	908.4
35°	816.1	824.8	846.5	874.7	883.4
37.5°	780.3	792.2	816.1	846.5	857.4
40°	745.6	758.6	785.7	818.3	831.3
42.5°	710.8	723.9	754.3	791.2	804.2
45°	671.8	685.9	720.6	759.7	773.8
47.5°	632.7	650.1	688.1	729.3	744.5
50°	592.6	612.1	653.3	696.7	714.1
52.5°	556.7	575.2	618.6	665.3	681.5
55°	515.5	536.1	583.9	631.6	650.1
57.5°	473.2	496.0	547.0	599.1	617.5
60°	431.9	456.9	513.3	565.4	586.0
62.5°	391.8	416.7	475.3	529.6	550.2
65°	348.4	377.7	438.4	493.8	513.3
67.5°	307.1	338.6	402.6	456.9	476.4
70°	267.0	297.4	365.7	418.9	438.4
72.5°	223.6	258.3	326.7	382.0	402.6
75°	180.2	221.4	288.7	342.9	362.5
77.5°	140.0	182.3	249.6	294.1	303.9
80°	103.1	146.5	205.1	236.6	248.5
82.5°	66.2	109.6	156.3	179.1	188.8
85°	36.9	72.7	102.0	115.0	119.4
87.5°	15.2	31.5	41.2	46.7	46.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)