

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P310703

Luminaire Tested: **24FCZ2-40HE-UNV-L82765-CP187-W2A-U-5500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P310703
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-15)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-40HE-UNV-L82765-CP187-W2A-U-5500K
Description: 2'X4' TROFFER LED MODULE, RIBBED LENS, 0.187" POLYCARB SHEET
Light Source: (336) 5500K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3623.0 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.29 / 1.38
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 31.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P310703

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-CP187-W2A-U-5500K

Luminous Intensity Polar Plot





TEST NUMBER: P310703

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-CP187-W2A-U-5500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	92	89	92	89	87	88	86	84	82
2	98	89	81	75	95	87	80	74	83	78	73	80	75	71	77	73	69	67
3	89	77	69	62	86	76	68	61	73	66	60	70	64	59	67	62	58	56
4	81	68	59	52	79	67	58	52	64	57	51	62	56	50	60	54	50	47
5	74	61	52	45	72	60	51	44	58	50	44	56	49	43	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	64	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	37	31	57	45	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	25	35	29	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1608	1608	1608
5°	1610	1601	1610
10°	1601	1596	1609
15°	1587	1591	1611
20°	1568	1580	1609
25°	1544	1569	1608
30°	1515	1556	1606
35°	1485	1540	1607
40°	1450	1529	1617
45°	1416	1519	1631
50°	1374	1515	1656
55°	1339	1517	1689
60°	1287	1530	1747
65°	1229	1546	1810
70°	1163	1594	1910
75°	1037	1662	2087
80°	885	1760	2133
85°	631	1744	2041



TEST NUMBER: P310703

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-CP187-W2A-U-5500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.1	3.1
10°-20°	323.3	8.9
20°-30°	488.4	13.5
30°-40°	588.6	16.2
40°-50°	617.9	17.1
50°-60°	578.1	16.0
60°-70°	477.4	13.2
70°-80°	325.3	9.0
80°-90°	110.9	3.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	924.8	25.5
0°-40°	1513.3	41.8
0°-60°	2709.3	74.8
0°-90°	3623.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3623.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1195	1195	1195	1195	1195	
5°	1192	1191	1185	1192	1192	113
15°	1140	1141	1142	1154	1156	321
25°	1040	1045	1057	1077	1083	478
35°	904	914	938	969	978	565
45°	744	760	798	841	857	574
55°	571	594	647	700	720	510
65°	386	418	486	547	569	383
75°	200	245	320	380	402	213
85°	41	80	113	127	132	51
90°	0	0	0	0	0	



TEST NUMBER: P310703

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-CP187-W2A-U-5500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1194.8	1194.8	1194.8	1194.8	1194.8
2.5°	1196.0	1194.8	1188.8	1194.8	1193.6
5°	1192.4	1191.2	1185.2	1192.4	1192.4
7.5°	1184.0	1184.0	1178.0	1186.4	1187.6
10°	1172.0	1172.0	1168.4	1178.0	1178.0
12.5°	1157.6	1157.6	1157.6	1167.2	1168.4
15°	1139.5	1140.7	1141.9	1154.0	1156.4
17.5°	1117.9	1120.3	1123.9	1138.3	1140.7
20°	1095.1	1097.5	1103.5	1120.3	1123.9
22.5°	1066.2	1072.2	1080.6	1099.9	1103.5
25°	1039.8	1044.6	1056.6	1077.0	1083.0
27.5°	1007.3	1014.5	1030.2	1051.8	1060.2
30°	974.9	982.1	1001.3	1026.5	1033.8
32.5°	940.0	950.8	971.3	997.7	1006.1
35°	903.9	913.6	937.6	968.8	978.5
37.5°	864.3	877.5	903.9	937.6	949.6
40°	825.8	840.2	870.3	906.3	920.8
42.5°	787.3	801.8	835.4	876.3	890.7
45°	744.1	759.7	798.2	841.4	857.1
47.5°	700.8	720.0	762.1	807.8	824.6
50°	656.3	678.0	723.6	771.7	790.9
52.5°	616.6	637.1	685.2	736.9	754.9
55°	571.0	593.8	646.7	699.6	720.0
57.5°	524.1	549.3	605.8	663.5	684.0
60°	478.4	506.1	568.6	626.3	649.1
62.5°	433.9	461.6	526.5	586.6	609.4
65°	385.9	418.3	485.6	546.9	568.6
67.5°	340.2	375.0	446.0	506.1	527.7
70°	295.7	329.4	405.1	464.0	485.6
72.5°	247.6	286.1	361.8	423.1	446.0
75°	199.5	245.2	319.7	379.8	401.5
77.5°	155.1	201.9	276.5	325.8	336.6
80°	114.2	162.3	227.2	262.0	275.3
82.5°	73.3	121.4	173.1	198.3	209.2
85°	40.9	80.5	113.0	127.4	132.2
87.5°	16.8	34.9	45.7	51.7	51.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)