

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P309686

Luminaire Tested: **24FCZ2-65HE-UNV-L82765-HRP-CA08-W2A-U-5500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P309686
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-65HE-UNV-L82765-HRP-CA08-W2A-U-5500K
Description: 2'X4' TROFFER LED MODULE, HIGH EFFICIENCY RND PERF. LENS, 0.08" ACRYLIC SHEET
Light Source: (336) 5500K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4713.0 lumens
Efficiency: N/A
Efficacy: 87.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 54.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P309686

CATALOG NUMBER: 24FCZ2-65HE-UNV-L82765-HRP-CA08-W2A-U-5500K

Luminous Intensity Polar Plot





TEST NUMBER: P309686

CATALOG NUMBER: 24FCZ2-65HE-UNV-L82765-HRP-CA08-W2A-U-5500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	96	93	96	93	90	92	90	87	89	86	84	82
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	77	73	70	67
3	89	78	69	62	86	76	68	62	73	66	61	70	64	59	68	63	58	56
4	81	68	59	52	79	67	59	52	65	57	51	62	56	50	60	54	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	63	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	36	30	57	44	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	24	35	29	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2057	2057	2057
5°	2060	2052	2060
10°	2054	2051	2065
15°	2042	2048	2067
20°	2028	2043	2071
25°	2004	2033	2074
30°	1980	2026	2081
35°	1948	2016	2084
40°	1913	2003	2104
45°	1870	2001	2136
50°	1809	1999	2193
55°	1745	2013	2273
60°	1646	2044	2373
65°	1520	2092	2507
70°	1327	2166	2670
75°	1077	2277	2759
80°	795	2232	2232
85°	610	1644	1859



TEST NUMBER: P309686

CATALOG NUMBER: 24FCZ2-65HE-UNV-L82765-HRP-CA08-W2A-U-5500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.9	3.1
10°-20°	416.0	8.8
20°-30°	633.3	13.4
30°-40°	768.9	16.3
40°-50°	812.4	17.2
50°-60°	766.6	16.3
60°-70°	637.4	13.5
70°-80°	419.3	8.9
80°-90°	114.3	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1194.1	25.3
0°-40°	1963.0	41.7
0°-60°	3542.0	75.2
0°-90°	4713.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4713.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1529	1529	1529	1529	1529	
5°	1525	1525	1519	1525	1525	145
15°	1466	1468	1470	1484	1484	413
25°	1350	1358	1369	1393	1397	623
35°	1186	1200	1227	1259	1269	742
45°	983	1002	1052	1103	1123	757
55°	744	775	858	939	969	663
65°	478	533	657	754	787	472
75°	207	302	438	519	531	223
85°	40	87	106	118	120	48
90°	0	0	0	0	0	



TEST NUMBER: P309686

CATALOG NUMBER: 24FCZ2-65HE-UNV-L82765-HRP-CA08-W2A-U-5500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1529.1	1529.1	1529.1	1529.1	1529.1
2.5°	1531.1	1529.1	1521.2	1529.1	1529.1
5°	1525.2	1525.2	1519.3	1525.2	1525.2
7.5°	1515.3	1515.3	1511.4	1519.3	1519.3
10°	1503.5	1503.5	1501.5	1511.4	1511.4
12.5°	1485.7	1487.7	1485.7	1497.6	1497.6
15°	1466.0	1468.0	1469.9	1483.8	1483.8
17.5°	1440.3	1444.3	1448.2	1464.0	1466.0
20°	1416.7	1418.6	1426.5	1444.3	1446.3
22.5°	1385.1	1391.0	1400.9	1418.6	1424.6
25°	1349.6	1357.5	1369.3	1393.0	1396.9
27.5°	1316.0	1322.0	1337.7	1363.4	1371.3
30°	1274.6	1284.5	1304.2	1329.9	1339.7
32.5°	1235.1	1245.0	1268.7	1296.3	1304.2
35°	1185.8	1199.6	1227.3	1258.8	1268.7
37.5°	1138.5	1152.3	1185.8	1221.3	1233.2
40°	1089.1	1104.9	1140.4	1181.9	1197.7
42.5°	1035.9	1057.6	1097.0	1142.4	1160.2
45°	982.6	1002.3	1051.7	1103.0	1122.7
47.5°	925.4	949.1	1002.3	1063.5	1087.2
50°	864.2	893.8	955.0	1022.1	1047.7
52.5°	803.0	836.6	905.6	980.6	1008.2
55°	743.9	775.4	858.3	939.2	968.8
57.5°	678.7	718.2	809.0	895.8	925.4
60°	611.7	655.1	759.6	850.4	882.0
62.5°	544.6	593.9	712.3	803.0	836.6
65°	477.5	532.7	657.0	753.7	787.3
67.5°	412.4	473.5	605.7	702.4	736.0
70°	337.4	414.3	550.5	645.2	678.7
72.5°	268.3	357.1	497.2	586.0	615.6
75°	207.2	301.9	438.0	518.9	530.8
77.5°	151.9	246.6	376.9	404.5	406.5
80°	102.6	197.3	288.1	284.1	288.1
82.5°	67.1	148.0	181.5	203.2	205.2
85°	39.5	86.8	106.5	118.4	120.4
87.5°	19.7	29.6	37.5	39.5	43.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)