

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P309884

Luminaire Tested: **24FCZ2-30-UNV-L82765-RDP-CP125-W2A-U-5500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P309884
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-30-UNV-L82765-RDP-CP125-W2A-U-5500K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS WITH INSERT, 0.125" POLYCARB SHEET
Light Source: (168) 5500K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1895.0 lumens
Efficiency: N/A
Efficacy: 78.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 24.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P309884

CATALOG NUMBER: 24FCZ2-30-UNV-L82765-RDP-CP125-W2A-U-5500K

Luminous Intensity Polar Plot





TEST NUMBER: P309884

CATALOG NUMBER: 24FCZ2-30-UNV-L82765-RDP-CP125-W2A-U-5500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67
3	88	77	68	62	86	76	67	61	72	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	802	802	802
5°	805	800	804
10°	803	800	804
15°	801	800	805
20°	795	799	808
25°	793	801	809
30°	786	799	812
35°	778	797	815
40°	769	796	826
45°	757	796	844
50°	740	801	870
55°	721	814	909
60°	691	830	959
65°	646	859	1018
70°	588	899	1094
75°	499	948	1143
80°	394	954	925
85°	290	726	812



TEST NUMBER: P309884

CATALOG NUMBER: 24FCZ2-30-UNV-L82765-RDP-CP125-W2A-U-5500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.5	3.0
10°-20°	162.7	8.6
20°-30°	248.8	13.1
30°-40°	304.1	16.0
40°-50°	324.2	17.1
50°-60°	309.9	16.4
60°-70°	262.5	13.9
70°-80°	176.5	9.3
80°-90°	49.8	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	468.0	24.7
0°-40°	772.1	40.7
0°-60°	1406.2	74.2
0°-90°	1895.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1895.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	596	596	596	596	596	
5°	596	595	592	595	595	57
15°	575	575	574	579	578	162
25°	534	536	540	544	545	246
35°	474	478	485	494	496	297
45°	398	404	418	436	444	307
55°	307	319	347	374	387	274
65°	203	224	270	306	320	202
75°	96	131	182	213	220	103
85°	19	38	47	51	53	23
90°	0	0	0	0	0	



TEST NUMBER: P309884

CATALOG NUMBER: 24FCZ2-30-UNV-L82765-RDP-CP125-W2A-U-5500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	595.9	595.9	595.9	595.9	595.9
2.5°	596.9	596.9	594.0	595.9	595.9
5°	595.9	595.0	592.2	595.0	595.0
7.5°	593.1	592.2	590.3	593.1	592.2
10°	587.5	587.5	585.6	588.4	588.4
12.5°	582.8	581.8	580.9	584.6	583.7
15°	575.2	575.2	574.3	579.0	578.1
17.5°	565.8	566.8	567.7	571.5	572.4
20°	555.5	557.4	558.3	564.0	564.0
22.5°	546.1	547.0	548.9	554.6	554.6
25°	533.9	535.8	539.5	544.2	545.2
27.5°	521.7	522.6	527.3	533.9	534.8
30°	505.7	508.5	514.1	521.7	522.6
32.5°	491.6	494.4	501.0	508.5	510.4
35°	473.7	477.5	485.0	494.4	496.3
37.5°	457.8	460.6	470.0	480.3	483.1
40°	438.0	443.7	453.1	465.3	470.0
42.5°	418.3	423.9	435.2	451.2	456.8
45°	397.6	404.2	418.3	436.1	443.7
47.5°	376.9	384.4	400.4	421.1	429.6
50°	353.4	362.8	382.6	406.1	415.5
52.5°	330.9	342.1	363.8	390.1	402.3
55°	307.4	318.6	346.8	374.1	387.3
57.5°	281.0	296.1	327.1	358.1	372.2
60°	256.6	270.7	308.3	342.1	356.2
62.5°	230.3	249.1	289.5	325.2	339.3
65°	203.0	223.7	269.8	305.5	319.6
67.5°	178.6	201.1	250.0	285.7	299.8
70°	149.5	177.6	228.4	264.1	278.2
72.5°	122.2	153.2	205.8	240.6	253.8
75°	95.9	130.7	182.3	213.4	219.9
77.5°	71.4	108.1	157.9	171.1	166.4
80°	50.8	86.5	123.1	116.6	119.4
82.5°	32.9	65.8	76.1	86.5	89.3
85°	18.8	38.5	47.0	50.8	52.6
87.5°	8.5	14.1	18.8	18.8	17.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)