

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P311203

Luminaire Tested: **24FCZ2-30HE-UNV-L82765-S-CP250-W2A-U-3500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P311203  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: 24FCZ2-30HE-UNV-L82765-S-CP250-W2A-U-3500K  
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS, 0.250" POLYCARB SHEET  
Light Source: (336) 3500K TUNABLE CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment: 

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2673.0 lumens  
Efficiency: N/A  
Efficacy: 126.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P311203

CATALOG NUMBER: 24FCZ2-30HE-UNV-L82765-S-CP250-W2A-U-3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P311203

CATALOG NUMBER: 24FC22-30HE-UNV-L82765-S-CP250-W2A-U-3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42
6	70	56	47	40	68	55	47	40	53	46	40	52	45	40	50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1263	1263	1263
5°	1263	1259	1267
10°	1257	1257	1267
15°	1245	1251	1264
20°	1229	1241	1261
25°	1206	1229	1253
30°	1179	1215	1243
35°	1153	1195	1233
40°	1114	1175	1218
45°	1078	1152	1205
50°	1036	1130	1191
55°	990	1109	1179
60°	944	1092	1177
65°	884	1073	1184
70°	818	1079	1216
75°	732	1099	1285
80°	592	1165	1257
85°	446	1022	996



TEST NUMBER: P311203

CATALOG NUMBER: 24FCZ2-30HE-UNV-L82765-S-CP250-W2A-U-3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	88.9	3.3
10°-20°	254.0	9.5
20°-30°	381.8	14.3
30°-40°	454.8	17.0
40°-50°	465.5	17.4
50°-60°	419.1	15.7
60°-70°	329.1	12.3
70°-80°	213.6	8.0
80°-90°	66.1	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	724.8	27.1
0°-40°	1179.6	44.1
0°-60°	2064.2	77.2
0°-90°	2673.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2673.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	939	939	939	939	939	
5°	935	936	932	937	938	89
15°	894	897	898	906	908	252
25°	812	819	828	841	844	374
35°	702	711	728	746	751	438
45°	566	580	605	628	633	437
55°	422	441	473	498	503	378
65°	278	299	337	365	372	276
75°	141	168	211	240	247	149
85°	29	54	66	64	64	35
90°	0	0	0	0	0	



TEST NUMBER: P311203

CATALOG NUMBER: 24FCZ2-30HE-UNV-L82765-S-CP250-W2A-U-3500K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	939.0	939.0	939.0	939.0	939.0
2.5°	939.9	939.9	935.6	939.9	940.7
5°	934.8	936.5	932.3	937.3	938.2
7.5°	929.7	929.7	927.2	932.3	933.1
10°	920.4	921.2	920.4	926.3	927.2
12.5°	908.5	910.2	911.0	917.0	917.8
15°	894.0	896.6	898.3	905.9	907.6
17.5°	877.9	880.5	884.7	893.2	894.9
20°	858.4	861.8	866.9	877.9	880.5
22.5°	837.2	840.6	849.0	859.2	863.5
25°	812.5	819.3	827.8	841.4	843.9
27.5°	787.9	793.9	804.9	819.3	822.7
30°	759.0	768.4	782.0	796.4	799.8
32.5°	731.0	740.4	756.5	771.8	776.0
35°	702.2	710.6	727.6	745.5	750.6
37.5°	669.0	680.1	698.8	716.6	721.7
40°	634.2	647.8	669.0	687.7	693.7
42.5°	601.1	615.6	636.8	657.2	664.0
45°	566.3	579.9	605.4	628.3	633.4
47.5°	530.7	545.9	573.1	596.0	604.5
50°	495.0	511.1	540.0	563.8	568.9
52.5°	459.3	476.3	506.9	532.4	534.9
55°	422.0	440.7	472.9	497.5	502.6
57.5°	388.0	404.1	439.0	464.4	470.4
60°	350.7	368.5	405.8	429.6	437.3
62.5°	315.0	333.7	372.7	396.5	403.3
65°	277.6	298.9	337.1	365.1	371.9
67.5°	245.4	265.8	306.5	333.7	340.5
70°	208.0	230.9	274.2	302.3	309.1
72.5°	175.8	199.5	242.8	270.0	280.2
75°	140.9	168.1	211.4	240.3	247.1
77.5°	107.0	138.4	182.5	204.6	204.6
80°	76.4	109.5	150.3	160.5	162.2
82.5°	50.1	82.4	111.2	110.4	110.4
85°	28.9	53.5	66.2	64.5	64.5
87.5°	11.0	22.1	23.8	23.8	22.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)