

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P309952

Luminaire Tested: **24FCZ2-35-UNV-L82765-RDP-CA08-W2A-U-3500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P309952
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-35-UNV-L82765-RDP-CA08-W2A-U-3500K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS WITH INSERT, 0.08" ACRYLIC SHEET
Light Source: (168) 3500K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2136.0 lumens
Efficiency: N/A
Efficacy: 76.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 28.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P309952

CATALOG NUMBER: 24FCZ2-35-UNV-L82765-RDP-CA08-W2A-U-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P309952

CATALOG NUMBER: 24FCZ2-35-UNV-L82765-RDP-CA08-W2A-U-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67
3	88	77	68	62	86	76	67	61	72	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	904	904	904
5°	907	902	906
10°	905	902	906
15°	903	902	908
20°	897	901	910
25°	893	903	912
30°	886	900	915
35°	877	898	919
40°	867	897	930
45°	853	897	952
50°	834	903	980
55°	813	917	1024
60°	778	935	1080
65°	728	968	1147
70°	663	1013	1234
75°	562	1068	1289
80°	443	1075	1043
85°	327	818	915



TEST NUMBER: P309952

CATALOG NUMBER: 24FCZ2-35-UNV-L82765-RDP-CA08-W2A-U-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.7	3.0
10°-20°	183.4	8.6
20°-30°	280.4	13.1
30°-40°	342.8	16.0
40°-50°	365.4	17.1
50°-60°	349.4	16.4
60°-70°	295.9	13.9
70°-80°	198.9	9.3
80°-90°	56.1	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	527.5	24.7
0°-40°	870.3	40.7
0°-60°	1585.1	74.2
0°-90°	2136.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2136.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	672	672	672	672	672	
5°	672	671	668	671	671	64
15°	648	648	647	653	652	183
25°	602	604	608	613	614	277
35°	534	538	547	557	559	335
45°	448	456	472	492	500	346
55°	346	359	391	422	436	309
65°	229	252	304	344	360	227
75°	108	147	206	240	248	116
85°	21	43	53	57	59	26
90°	0	0	0	0	0	



TEST NUMBER: P309952

CATALOG NUMBER: 24FCZ2-35-UNV-L82765-RDP-CA08-W2A-U-3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	671.7	671.7	671.7	671.7	671.7
2.5°	672.8	672.8	669.6	671.7	671.7
5°	671.7	670.7	667.5	670.7	670.7
7.5°	668.5	667.5	665.4	668.5	667.5
10°	662.2	662.2	660.1	663.2	663.2
12.5°	656.9	655.8	654.8	659.0	657.9
15°	648.4	648.4	647.3	652.6	651.6
17.5°	637.8	638.9	639.9	644.2	645.2
20°	626.2	628.3	629.3	635.7	635.7
22.5°	615.6	616.6	618.7	625.1	625.1
25°	601.8	603.9	608.1	613.4	614.5
27.5°	588.0	589.1	594.4	601.8	602.8
30°	570.0	573.2	579.5	588.0	589.1
32.5°	554.1	557.3	564.7	573.2	575.3
35°	534.0	538.2	546.7	557.3	559.4
37.5°	516.0	519.1	529.7	541.4	544.6
40°	493.7	500.1	510.7	524.4	529.7
42.5°	471.5	477.8	490.5	508.6	514.9
45°	448.2	455.6	471.5	491.6	500.1
47.5°	424.9	433.3	451.3	474.6	484.2
50°	398.4	409.0	431.2	457.7	468.3
52.5°	372.9	385.7	410.0	439.7	453.5
55°	346.5	359.2	390.9	421.7	436.5
57.5°	316.8	333.7	368.7	403.7	419.6
60°	289.2	305.1	347.5	385.7	401.5
62.5°	259.6	280.8	326.3	366.6	382.5
65°	228.8	252.2	304.1	344.3	360.2
67.5°	201.3	226.7	281.8	322.1	338.0
70°	168.5	200.2	257.5	297.7	313.6
72.5°	137.7	172.7	232.0	271.2	286.1
75°	108.1	147.3	205.5	240.5	247.9
77.5°	80.5	121.8	178.0	192.8	187.5
80°	57.2	97.5	138.8	131.4	134.6
82.5°	37.1	74.2	85.8	97.5	100.7
85°	21.2	43.4	53.0	57.2	59.3
87.5°	9.5	15.9	21.2	21.2	20.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)