

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P310062

Luminaire Tested: **24FCZ2-40-UNV-L82765-RDP-CP125-W2A-U-4500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P310062
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-40-UNV-L82765-RDP-CP125-W2A-U-4500K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS WITH INSERT, 0.125" POLYCARB SHEET
Light Source: (168) 4500K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2470.0 lumens
Efficiency: N/A
Efficacy: 74.2 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 33.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P310062

CATALOG NUMBER: 24FCZ2-40-UNV-L82765-RDP-CP125-W2A-U-4500K

Luminous Intensity Polar Plot





TEST NUMBER: P310062

CATALOG NUMBER: 24FCZ2-40-UNV-L82765-RDP-CP125-W2A-U-4500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67
3	88	77	68	62	86	76	67	61	72	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1045	1045	1045
5°	1049	1042	1047
10°	1046	1043	1048
15°	1044	1043	1050
20°	1037	1042	1053
25°	1033	1044	1055
30°	1024	1041	1058
35°	1014	1038	1063
40°	1003	1037	1076
45°	986	1037	1100
50°	964	1044	1133
55°	940	1061	1184
60°	900	1081	1249
65°	842	1119	1326
70°	766	1171	1426
75°	650	1236	1490
80°	513	1244	1206
85°	378	946	1059



TEST NUMBER: P310062

CATALOG NUMBER: 24FCZ2-40-UNV-L82765-RDP-CP125-W2A-U-4500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.7	3.0
10°-20°	212.1	8.6
20°-30°	324.3	13.1
30°-40°	396.4	16.0
40°-50°	422.5	17.1
50°-60°	404.0	16.4
60°-70°	342.2	13.9
70°-80°	230.0	9.3
80°-90°	64.9	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	610.0	24.7
0°-40°	1006.4	40.7
0°-60°	1832.9	74.2
0°-90°	2470.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2470.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	777	777	777	777	777	
5°	777	776	772	776	776	74
15°	750	750	749	755	754	211
25°	696	698	703	709	711	321
35°	618	622	632	644	647	387
45°	518	527	545	568	578	400
55°	401	415	452	488	505	357
65°	265	292	352	398	417	263
75°	125	170	238	278	287	134
85°	24	50	61	66	69	30
90°	0	0	0	0	0	



TEST NUMBER: P310062

CATALOG NUMBER: 24FCZ2-40-UNV-L82765-RDP-CP125-W2A-U-4500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	776.7	776.7	776.7	776.7	776.7
2.5°	778.0	778.0	774.3	776.7	776.7
5°	776.7	775.5	771.8	775.5	775.5
7.5°	773.1	771.8	769.4	773.1	771.8
10°	765.7	765.7	763.3	766.9	766.9
12.5°	759.6	758.4	757.1	762.0	760.8
15°	749.8	749.8	748.6	754.7	753.5
17.5°	737.5	738.8	740.0	744.9	746.1
20°	724.1	726.5	727.7	735.1	735.1
22.5°	711.8	713.0	715.5	722.8	722.8
25°	695.9	698.3	703.2	709.4	710.6
27.5°	680.0	681.2	687.3	695.9	697.1
30°	659.1	662.8	670.2	680.0	681.2
32.5°	640.8	644.4	653.0	662.8	665.3
35°	617.5	622.4	632.2	644.4	646.9
37.5°	596.6	600.3	612.6	626.1	629.7
40°	570.9	578.3	590.5	606.4	612.6
42.5°	545.2	552.5	567.2	588.1	595.4
45°	518.2	526.8	545.2	568.5	578.3
47.5°	491.3	501.1	521.9	548.9	559.9
50°	460.7	472.9	498.6	529.3	541.5
52.5°	431.3	446.0	474.1	508.4	524.4
55°	400.6	415.3	452.1	487.6	504.8
57.5°	366.3	385.9	426.4	466.8	485.2
60°	334.5	352.8	401.8	446.0	464.3
62.5°	300.2	324.7	377.3	423.9	442.3
65°	264.6	291.6	351.6	398.2	416.6
67.5°	232.8	262.2	325.9	372.4	390.8
70°	194.8	231.6	297.7	344.3	362.6
72.5°	159.3	199.7	268.3	313.6	330.8
75°	125.0	170.3	237.7	278.1	286.7
77.5°	93.1	140.9	205.8	223.0	216.9
80°	66.2	112.7	160.5	151.9	155.6
82.5°	42.9	85.8	99.2	112.7	116.4
85°	24.5	50.2	61.3	66.2	68.6
87.5°	11.0	18.4	24.5	24.5	23.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)