

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P310006

Luminaire Tested: **24FCZ2-40HE-UNV-L82765-RDP-CA125-W2A-U-3500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P310006
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-40HE-UNV-L82765-RDP-CA125-W2A-U-3500K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS WITH INSERT, 0.125" ACRYLIC SHEET
Light Source: (336) 3500K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2437.0 lumens
Efficiency: N/A
Efficacy: 79.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 30.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P310006

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-RDP-CA125-W2A-U-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P310006

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-RDP-CA125-W2A-U-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67
3	88	77	68	62	86	76	67	61	72	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1031	1031	1031
5°	1035	1029	1034
10°	1032	1029	1034
15°	1031	1029	1036
20°	1023	1028	1039
25°	1019	1030	1041
30°	1010	1027	1044
35°	1001	1024	1048
40°	989	1023	1062
45°	973	1024	1086
50°	951	1030	1118
55°	927	1046	1168
60°	888	1067	1233
65°	831	1104	1309
70°	756	1155	1408
75°	641	1219	1471
80°	506	1227	1189
85°	374	932	1045



TEST NUMBER: P310006

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-RDP-CA125-W2A-U-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.7	3.0
10°-20°	209.2	8.6
20°-30°	319.9	13.1
30°-40°	391.1	16.0
40°-50°	416.9	17.1
50°-60°	398.6	16.4
60°-70°	337.6	13.9
70°-80°	226.9	9.3
80°-90°	64.0	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	601.9	24.7
0°-40°	993.0	40.7
0°-60°	1808.4	74.2
0°-90°	2437.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2437.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	766	766	766	766	766	
5°	766	765	762	765	765	73
15°	740	740	739	745	743	209
25°	687	689	694	700	701	316
35°	609	614	624	636	638	382
45°	511	520	538	561	570	394
55°	395	410	446	481	498	352
65°	261	288	347	393	411	259
75°	123	168	234	274	283	132
85°	24	50	60	65	68	30
90°	0	0	0	0	0	



TEST NUMBER: P310006

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-RDP-CA125-W2A-U-3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	766.4	766.4	766.4	766.4	766.4
2.5°	767.6	767.6	763.9	766.4	766.4
5°	766.4	765.2	761.5	765.2	765.2
7.5°	762.7	761.5	759.1	762.7	761.5
10°	755.5	755.5	753.1	756.7	756.7
12.5°	749.4	748.2	747.0	751.9	750.7
15°	739.8	739.8	738.6	744.6	743.4
17.5°	727.7	728.9	730.1	734.9	736.1
20°	714.4	716.8	718.0	725.3	725.3
22.5°	702.3	703.5	705.9	713.2	713.2
25°	686.6	689.0	693.8	699.9	701.1
27.5°	670.9	672.1	678.1	686.6	687.8
30°	650.3	654.0	661.2	670.9	672.1
32.5°	632.2	635.8	644.3	654.0	656.4
35°	609.2	614.1	623.7	635.8	638.2
37.5°	588.7	592.3	604.4	617.7	621.3
40°	563.3	570.5	582.6	598.3	604.4
42.5°	537.9	545.2	559.7	580.2	587.5
45°	511.3	519.8	537.9	560.9	570.5
47.5°	484.7	494.4	514.9	541.5	552.4
50°	454.5	466.6	492.0	522.2	534.3
52.5°	425.5	440.0	467.8	501.6	517.4
55°	395.3	409.8	446.0	481.1	498.0
57.5°	361.4	380.8	420.7	460.5	478.7
60°	330.0	348.1	396.5	440.0	458.1
62.5°	296.2	320.3	372.3	418.2	436.4
65°	261.1	287.7	346.9	392.9	411.0
67.5°	229.7	258.7	321.5	367.5	385.6
70°	192.2	228.5	293.7	339.7	357.8
72.5°	157.1	197.0	264.7	309.4	326.4
75°	123.3	168.0	234.5	274.4	282.9
77.5°	91.9	139.0	203.1	220.0	214.0
80°	65.3	111.2	158.4	149.9	153.5
82.5°	42.3	84.6	97.9	111.2	114.8
85°	24.2	49.6	60.4	65.3	67.7
87.5°	10.9	18.1	24.2	24.2	23.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)