

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P310228

Luminaire Tested: **24FCZ2-50-UNV-L82765-RDP-CA08-W2A-U-6500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P310228  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: 24FCZ2-50-UNV-L82765-RDP-CA08-W2A-U-6500K  
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS WITH INSERT, 0.08" ACRYLIC SHEET  
Light Source: (168) 6500K TUNABLE CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3215.0 lumens  
Efficiency: N/A  
Efficacy: 72.1 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 44.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P310228

CATALOG NUMBER: 24FCZ2-50-UNV-L82765-RDP-CA08-W2A-U-6500K

### Luminous Intensity Polar Plot





TEST NUMBER: P310228

CATALOG NUMBER: 24FCZ2-50-UNV-L82765-RDP-CA08-W2A-U-6500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67
3	88	77	68	62	86	76	67	61	72	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1360	1360	1360
5°	1365	1357	1363
10°	1362	1357	1364
15°	1359	1357	1366
20°	1350	1356	1370
25°	1345	1359	1373
30°	1333	1355	1377
35°	1320	1352	1383
40°	1305	1350	1400
45°	1283	1350	1432
50°	1255	1358	1475
55°	1223	1380	1541
60°	1171	1408	1626
65°	1097	1457	1726
70°	998	1524	1857
75°	846	1608	1940
80°	667	1619	1569
85°	492	1230	1379



TEST NUMBER: P310228

CATALOG NUMBER: 24FCZ2-50-UNV-L82765-RDP-CA08-W2A-U-6500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.9	3.0
10°-20°	276.0	8.6
20°-30°	422.1	13.1
30°-40°	516.0	16.0
40°-50°	549.9	17.1
50°-60°	525.8	16.4
60°-70°	445.5	13.9
70°-80°	299.4	9.3
80°-90°	84.4	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	794.0	24.7
0°-40°	1310.0	40.7
0°-60°	2385.7	74.2
0°-90°	3215.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3215.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1011	1011	1011	1011	1011	
5°	1011	1009	1005	1009	1009	96
15°	976	976	974	982	981	275
25°	906	909	915	923	925	417
35°	804	810	823	839	842	503
45°	674	686	710	740	753	520
55°	522	541	588	635	657	464
65°	344	380	458	518	542	342
75°	163	222	309	362	373	174
85°	32	65	80	86	89	39
90°	0	0	0	0	0	



TEST NUMBER: P310228

CATALOG NUMBER: 24FCZ2-50-UNV-L82765-RDP-CA08-W2A-U-6500K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1011.0	1011.0	1011.0	1011.0	1011.0
2.5°	1012.6	1012.6	1007.8	1011.0	1011.0
5°	1011.0	1009.4	1004.6	1009.4	1009.4
7.5°	1006.2	1004.6	1001.5	1006.2	1004.6
10°	996.7	996.7	993.5	998.3	998.3
12.5°	988.7	987.1	985.5	991.9	990.3
15°	975.9	975.9	974.3	982.3	980.7
17.5°	960.0	961.6	963.2	969.6	971.2
20°	942.5	945.6	947.2	956.8	956.8
22.5°	926.5	928.1	931.3	940.9	940.9
25°	905.8	909.0	915.3	923.3	924.9
27.5°	885.0	886.6	894.6	905.8	907.4
30°	857.9	862.7	872.3	885.0	886.6
32.5°	834.0	838.8	850.0	862.7	865.9
35°	803.7	810.1	822.9	838.8	842.0
37.5°	776.6	781.4	797.3	814.9	819.7
40°	743.1	752.7	768.6	789.4	797.3
42.5°	709.6	719.2	738.3	765.4	775.0
45°	674.5	685.7	709.6	739.9	752.7
47.5°	639.5	652.2	679.3	714.4	728.8
50°	599.6	615.5	649.0	688.9	704.8
52.5°	561.3	580.5	617.1	661.8	682.5
55°	521.5	540.6	588.4	634.7	657.0
57.5°	476.8	502.3	554.9	607.6	631.5
60°	435.3	459.3	523.1	580.5	604.4
62.5°	390.7	422.6	491.2	551.8	575.7
65°	344.5	379.5	457.7	518.3	542.2
67.5°	303.0	341.3	424.2	484.8	508.7
70°	253.6	301.4	387.5	448.1	472.0
72.5°	207.3	259.9	349.2	408.2	430.6
75°	162.7	221.7	309.4	362.0	373.2
77.5°	121.2	183.4	267.9	290.2	282.3
80°	86.1	146.7	208.9	197.7	202.5
82.5°	55.8	111.6	129.2	146.7	151.5
85°	31.9	65.4	79.7	86.1	89.3
87.5°	14.4	23.9	31.9	31.9	30.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)