

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P310246

Luminaire Tested: **24FCZ2-50-UNV-L82765-RDP-CP125-W2A-U-6500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P310246  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: 24FCZ2-50-UNV-L82765-RDP-CP125-W2A-U-6500K  
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS WITH INSERT, 0.125" POLYCARB SHEET  
Light Source: (168) 6500K TUNABLE CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3141.0 lumens  
Efficiency: N/A  
Efficacy: 70.4 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 44.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P310246

CATALOG NUMBER: 24FCZ2-50-UNV-L82765-RDP-CP125-W2A-U-6500K

### Luminous Intensity Polar Plot





TEST NUMBER: P310246

CATALOG NUMBER: 24FCZ2-50-UNV-L82765-RDP-CP125-W2A-U-6500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67
3	88	77	68	62	86	76	67	61	72	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1329	1329	1329
5°	1334	1326	1332
10°	1330	1326	1332
15°	1328	1326	1335
20°	1318	1325	1338
25°	1314	1328	1341
30°	1302	1324	1346
35°	1290	1320	1351
40°	1275	1319	1368
45°	1254	1319	1399
50°	1226	1327	1441
55°	1195	1349	1506
60°	1144	1375	1589
65°	1071	1423	1686
70°	974	1489	1814
75°	826	1571	1895
80°	652	1581	1533
85°	482	1203	1346



TEST NUMBER: P310246

CATALOG NUMBER: 24FCZ2-50-UNV-L82765-RDP-CP125-W2A-U-6500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	93.7	3.0
10°-20°	269.7	8.6
20°-30°	412.4	13.1
30°-40°	504.1	16.0
40°-50°	537.3	17.1
50°-60°	513.7	16.4
60°-70°	435.2	13.9
70°-80°	292.5	9.3
80°-90°	82.5	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	775.7	24.7
0°-40°	1279.8	40.7
0°-60°	2330.8	74.2
0°-90°	3141.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3141.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	988	988	988	988	988	
5°	988	986	982	986	986	94
15°	954	954	952	960	958	269
25°	885	888	894	902	904	408
35°	785	792	804	820	823	492
45°	659	670	693	723	735	508
55°	510	528	575	620	642	454
65°	336	371	447	506	530	334
75°	159	217	302	354	365	170
85°	31	64	78	84	87	39
90°	0	0	0	0	0	



TEST NUMBER: P310246

CATALOG NUMBER: 24FCZ2-50-UNV-L82765-RDP-CP125-W2A-U-6500K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	987.8	987.8	987.8	987.8	987.8
2.5°	989.3	989.3	984.6	987.8	987.8
5°	987.8	986.2	981.5	986.2	986.2
7.5°	983.1	981.5	978.4	983.1	981.5
10°	973.7	973.7	970.6	975.3	975.3
12.5°	965.9	964.4	962.8	969.1	967.5
15°	953.5	953.5	951.9	959.7	958.2
17.5°	937.9	939.5	941.0	947.2	948.8
20°	920.8	923.9	925.4	934.8	934.8
22.5°	905.2	906.7	909.9	919.2	919.2
25°	884.9	888.0	894.3	902.1	903.6
27.5°	864.7	866.2	874.0	884.9	886.5
30°	838.2	842.9	852.2	864.7	866.2
32.5°	814.8	819.5	830.4	842.9	846.0
35°	785.2	791.5	803.9	819.5	822.6
37.5°	758.7	763.4	779.0	796.1	800.8
40°	726.0	735.4	750.9	771.2	779.0
42.5°	693.3	702.6	721.3	747.8	757.2
45°	659.0	669.9	693.3	722.9	735.4
47.5°	624.7	637.2	663.7	698.0	712.0
50°	585.8	601.4	634.1	673.0	688.6
52.5°	548.4	567.1	602.9	646.6	666.8
55°	509.5	528.2	574.9	620.1	641.9
57.5°	465.8	490.8	542.2	593.6	617.0
60°	425.3	448.7	511.0	567.1	590.5
62.5°	381.7	412.9	479.9	539.1	562.4
65°	336.5	370.8	447.1	506.3	529.7
67.5°	296.0	333.4	414.4	473.6	497.0
70°	247.7	294.5	378.6	437.8	461.2
72.5°	202.5	253.9	341.2	398.8	420.7
75°	158.9	216.6	302.2	353.7	364.6
77.5°	118.4	179.2	261.7	283.6	275.8
80°	84.1	143.3	204.1	193.2	197.9
82.5°	54.5	109.1	126.2	143.3	148.0
85°	31.2	63.9	77.9	84.1	87.2
87.5°	14.0	23.4	31.2	31.2	29.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)