

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P310192

Luminaire Tested: **24FCZ2-50HE-UNV-L82765-RDP-CA125-W2A-U-6500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P310192
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-50HE-UNV-L82765-RDP-CA125-W2A-U-6500K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS WITH INSERT, 0.125" ACRYLIC SHEET
Light Source: (336) 6500K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3219.0 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 40.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P310192

CATALOG NUMBER: 24FCZ2-50HE-UNV-L82765-RDP-CA125-W2A-U-6500K

Luminous Intensity Polar Plot





TEST NUMBER: P310192

CATALOG NUMBER: 24FCZ2-50HE-UNV-L82765-RDP-CA125-W2A-U-6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67
3	88	77	68	62	86	76	67	61	72	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1362	1362	1362
5°	1367	1359	1365
10°	1363	1359	1366
15°	1361	1359	1368
20°	1351	1358	1372
25°	1346	1361	1375
30°	1335	1357	1379
35°	1322	1353	1385
40°	1307	1352	1402
45°	1285	1352	1434
50°	1257	1360	1477
55°	1225	1382	1543
60°	1173	1409	1628
65°	1098	1459	1728
70°	999	1526	1859
75°	847	1611	1942
80°	668	1621	1571
85°	492	1232	1380



TEST NUMBER: P310192

CATALOG NUMBER: 24FCZ2-50HE-UNV-L82765-RDP-CA125-W2A-U-6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.0	3.0
10°-20°	276.4	8.6
20°-30°	422.6	13.1
30°-40°	516.6	16.0
40°-50°	550.6	17.1
50°-60°	526.5	16.4
60°-70°	446.0	13.9
70°-80°	299.7	9.3
80°-90°	84.5	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	795.0	24.7
0°-40°	1311.6	40.7
0°-60°	2388.7	74.2
0°-90°	3219.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3219.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1012	1012	1012	1012	1012	
5°	1012	1011	1006	1011	1011	96
15°	977	977	976	984	982	276
25°	907	910	916	924	926	418
35°	805	811	824	840	843	504
45°	675	687	710	741	754	521
55°	522	541	589	636	658	465
65°	345	380	458	519	543	342
75°	163	222	310	362	374	174
85°	32	66	80	86	89	40
90°	0	0	0	0	0	



TEST NUMBER: P310192

CATALOG NUMBER: 24FCZ2-50HE-UNV-L82765-RDP-CA125-W2A-U-6500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1012.3	1012.3	1012.3	1012.3	1012.3
2.5°	1013.9	1013.9	1009.1	1012.3	1012.3
5°	1012.3	1010.7	1005.9	1010.7	1010.7
7.5°	1007.5	1005.9	1002.7	1007.5	1005.9
10°	997.9	997.9	994.7	999.5	999.5
12.5°	989.9	988.3	986.7	993.1	991.5
15°	977.2	977.2	975.6	983.5	981.9
17.5°	961.2	962.8	964.4	970.8	972.4
20°	943.6	946.8	948.4	958.0	958.0
22.5°	927.7	929.3	932.5	942.0	942.0
25°	906.9	910.1	916.5	924.5	926.1
27.5°	886.1	887.7	895.7	906.9	908.5
30°	859.0	863.8	873.4	886.1	887.7
32.5°	835.1	839.8	851.0	863.8	867.0
35°	804.7	811.1	823.9	839.8	843.0
37.5°	777.6	782.4	798.3	815.9	820.7
40°	744.0	753.6	769.6	790.3	798.3
42.5°	710.5	720.1	739.3	766.4	776.0
45°	675.4	686.6	710.5	740.9	753.6
47.5°	640.3	653.0	680.2	715.3	729.7
50°	600.3	616.3	649.8	689.8	705.7
52.5°	562.0	581.2	617.9	662.6	683.4
55°	522.1	541.3	589.2	635.5	657.8
57.5°	477.4	502.9	555.6	608.3	632.3
60°	435.9	459.8	523.7	581.2	605.1
62.5°	391.2	423.1	491.8	552.4	576.4
65°	344.9	380.0	458.2	518.9	542.9
67.5°	303.4	341.7	424.7	485.4	509.3
70°	253.9	301.8	388.0	448.7	472.6
72.5°	207.6	260.3	349.7	408.7	431.1
75°	162.9	221.9	309.8	362.4	373.6
77.5°	121.3	183.6	268.2	290.6	282.6
80°	86.2	146.9	209.2	198.0	202.8
82.5°	55.9	111.8	129.3	146.9	151.7
85°	31.9	65.5	79.8	86.2	89.4
87.5°	14.4	23.9	31.9	31.9	30.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)