

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P311356

Luminaire Tested: **24FCZ2-40HE-UNV-L82765-S-CA125-W2A-U-3500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P311356
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-40HE-UNV-L82765-S-CA125-W2A-U-3500K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS, 0.125" ACRYLIC SHEET
Light Source: (336) 3500K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3808.0 lumens
Efficiency: N/A
Efficacy: 124.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 30.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P311356

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-S-CA125-W2A-U-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P311356

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-S-CA125-W2A-U-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42
6	70	56	47	40	68	55	47	40	53	46	40	52	45	40	50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1800	1800	1800
5°	1799	1794	1805
10°	1791	1791	1805
15°	1774	1783	1801
20°	1751	1768	1796
25°	1719	1751	1785
30°	1680	1731	1770
35°	1643	1703	1756
40°	1587	1674	1736
45°	1535	1641	1717
50°	1476	1610	1696
55°	1410	1580	1680
60°	1344	1556	1676
65°	1259	1529	1687
70°	1166	1537	1732
75°	1044	1566	1830
80°	844	1659	1790
85°	634	1456	1419



TEST NUMBER: P311356

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-S-CA125-W2A-U-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.6	3.3
10°-20°	361.9	9.5
20°-30°	544.0	14.3
30°-40°	648.0	17.0
40°-50°	663.2	17.4
50°-60°	597.0	15.7
60°-70°	468.9	12.3
70°-80°	304.3	8.0
80°-90°	94.1	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1032.5	27.1
0°-40°	1680.5	44.1
0°-60°	2940.7	77.2
0°-90°	3808.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3808.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1338	1338	1338	1338	1338	
5°	1332	1334	1328	1335	1337	127
15°	1274	1277	1280	1291	1293	359
25°	1158	1167	1179	1199	1202	533
35°	1000	1012	1037	1062	1069	624
45°	807	826	862	895	902	622
55°	601	628	674	709	716	539
65°	396	426	480	520	530	394
75°	201	240	301	342	352	212
85°	41	76	94	92	92	50
90°	0	0	0	0	0	



TEST NUMBER: P311356

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-S-CA125-W2A-U-3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1337.8	1337.8	1337.8	1337.8	1337.8
2.5°	1339.0	1339.0	1332.9	1339.0	1340.2
5°	1331.7	1334.1	1328.1	1335.4	1336.6
7.5°	1324.5	1324.5	1320.8	1328.1	1329.3
10°	1311.2	1312.4	1311.2	1319.6	1320.8
12.5°	1294.2	1296.7	1297.9	1306.3	1307.5
15°	1273.7	1277.3	1279.7	1290.6	1293.0
17.5°	1250.7	1254.3	1260.4	1272.5	1274.9
20°	1222.9	1227.7	1235.0	1250.7	1254.3
22.5°	1192.6	1197.5	1209.6	1224.1	1230.1
25°	1157.6	1167.2	1179.3	1198.7	1202.3
27.5°	1122.5	1130.9	1146.7	1167.2	1172.1
30°	1081.3	1094.7	1114.0	1134.6	1139.4
32.5°	1041.4	1054.7	1077.7	1099.5	1105.5
35°	1000.3	1012.4	1036.6	1062.0	1069.3
37.5°	953.1	968.9	995.5	1020.9	1028.1
40°	903.5	922.9	953.1	979.7	988.2
42.5°	856.4	876.9	907.2	936.2	945.9
45°	806.8	826.1	862.4	895.1	902.3
47.5°	756.0	777.7	816.5	849.1	861.2
50°	705.2	728.2	769.3	803.1	810.4
52.5°	654.4	678.6	722.1	758.4	762.0
55°	601.2	627.8	673.7	708.8	716.1
57.5°	552.8	575.8	625.3	661.6	670.1
60°	499.5	524.9	578.2	612.0	622.9
62.5°	448.7	475.4	531.0	564.9	574.5
65°	395.5	425.8	480.2	520.1	529.8
67.5°	349.6	378.6	436.7	475.4	485.0
70°	296.3	329.0	390.7	430.6	440.3
72.5°	250.4	284.2	345.9	384.6	399.2
75°	200.8	239.5	301.2	342.3	352.0
77.5°	152.4	197.2	260.1	291.5	291.5
80°	108.9	156.0	214.1	228.6	231.0
82.5°	71.4	117.3	158.5	157.2	157.2
85°	41.1	76.2	94.3	91.9	91.9
87.5°	15.7	31.4	33.9	33.9	32.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)