

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P310672

Luminaire Tested: **24FCZ2-40HE-UNV-L82765-CA08-W2A-U-3500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P310672  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-15)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: 24FCZ2-40HE-UNV-L82765-CA08-W2A-U-3500K  
Description: 2'X4' TROFFER LED MODULE, RIBBED LENS, 0.08" ACRYLIC SHEET  
Light Source: (336) 3500K TUNABLE CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment: 

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3637.0 lumens  
Efficiency: N/A  
Efficacy: 119.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.29 / 1.38  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 30.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P310672

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-CA08-W2A-U-3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P310672

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-CA08-W2A-U-3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	92	89	92	89	87	88	86	84	82
2	98	89	81	75	95	87	80	74	83	78	73	80	75	71	77	73	69	67
3	89	77	69	62	86	76	68	61	73	66	60	70	64	59	67	62	58	56
4	81	68	59	52	79	67	58	52	64	57	51	62	56	50	60	54	50	47
5	74	61	52	45	72	60	51	44	58	50	44	56	49	43	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	64	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	37	31	57	45	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	25	35	29	24	23

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1614	1614	1614
5°	1617	1607	1617
10°	1607	1602	1616
15°	1593	1597	1617
20°	1574	1586	1616
25°	1550	1575	1614
30°	1520	1562	1612
35°	1490	1546	1613
40°	1456	1534	1623
45°	1421	1525	1637
50°	1379	1521	1662
55°	1345	1523	1696
60°	1292	1536	1753
65°	1233	1552	1817
70°	1168	1600	1918
75°	1041	1669	2095
80°	888	1767	2141
85°	633	1751	2049



TEST NUMBER: P310672

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-CA08-W2A-U-3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	113.5	3.1
10°-20°	324.6	8.9
20°-30°	490.2	13.5
30°-40°	590.9	16.2
40°-50°	620.3	17.1
50°-60°	580.3	16.0
60°-70°	479.2	13.2
70°-80°	326.6	9.0
80°-90°	111.4	3.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	928.3	25.5
0°-40°	1519.2	41.8
0°-60°	2719.8	74.8
0°-90°	3637.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3637.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1200	1200	1200	1200	1200	
5°	1197	1196	1190	1197	1197	114
15°	1144	1145	1146	1158	1161	322
25°	1044	1049	1061	1081	1087	480
35°	907	917	941	973	982	567
45°	747	763	801	845	860	576
55°	573	596	649	702	723	512
65°	387	420	488	549	571	384
75°	200	246	321	381	403	214
85°	41	81	113	128	133	51
90°	0	0	0	0	0	



TEST NUMBER: P310672

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-CA08-W2A-U-3500K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1199.5	1199.5	1199.5	1199.5	1199.5
2.5°	1200.7	1199.5	1193.4	1199.5	1198.2
5°	1197.0	1195.8	1189.8	1197.0	1197.0
7.5°	1188.6	1188.6	1182.6	1191.0	1192.2
10°	1176.5	1176.5	1172.9	1182.6	1182.6
12.5°	1162.0	1162.0	1162.0	1171.7	1172.9
15°	1143.9	1145.1	1146.4	1158.4	1160.8
17.5°	1122.2	1124.6	1128.3	1142.7	1145.1
20°	1099.3	1101.7	1107.7	1124.6	1128.3
22.5°	1070.3	1076.4	1084.8	1104.1	1107.7
25°	1043.8	1048.6	1060.7	1081.2	1087.2
27.5°	1011.2	1018.4	1034.1	1055.9	1064.3
30°	978.6	985.9	1005.2	1030.5	1037.8
32.5°	943.6	954.5	975.0	1001.6	1010.0
35°	907.4	917.1	941.2	972.6	982.2
37.5°	867.6	880.9	907.4	941.2	953.3
40°	829.0	843.5	873.6	909.8	924.3
42.5°	790.4	804.9	838.7	879.7	894.2
45°	746.9	762.6	801.2	844.7	860.4
47.5°	703.5	722.8	765.0	810.9	827.8
50°	658.9	680.6	726.4	774.7	794.0
52.5°	619.0	639.5	687.8	739.7	757.8
55°	573.2	596.1	649.2	702.3	722.8
57.5°	526.1	551.5	608.2	666.1	686.6
60°	480.3	508.0	570.8	628.7	651.6
62.5°	435.6	463.4	528.5	588.9	611.8
65°	387.3	419.9	487.5	549.0	570.8
67.5°	341.5	376.5	447.7	508.0	529.7
70°	296.8	330.6	406.7	465.8	487.5
72.5°	248.6	287.2	363.2	424.8	447.7
75°	200.3	246.2	321.0	381.3	403.0
77.5°	155.7	202.7	277.5	327.0	337.9
80°	114.6	162.9	228.1	263.1	276.3
82.5°	73.6	121.9	173.8	199.1	210.0
85°	41.0	80.8	113.4	127.9	132.7
87.5°	16.9	35.0	45.9	51.9	51.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)