

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P310829

Luminaire Tested: **24FCZ2-45-UNV-L82765-CP125-W2A-U-5500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P310829
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-15)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-45-UNV-L82765-CP125-W2A-U-5500K
Description: 2'X4' TROFFER LED MODULE, RIBBED LENS, 0.125" POLYCARB SHEET
Light Source: (168) 5500K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4210.0 lumens
Efficiency: N/A
Efficacy: 108.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.29 / 1.38
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P310829

CATALOG NUMBER: 24FCZ2-45-UNV-L82765-CP125-W2A-U-5500K

Luminous Intensity Polar Plot





TEST NUMBER: P310829

CATALOG NUMBER: 24FCZ2-45-UNV-L82765-CP125-W2A-U-5500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	92	89	92	89	87	88	86	84	82
2	98	89	81	75	95	87	80	74	83	78	73	80	75	71	77	73	69	67
3	89	77	69	62	86	76	68	61	73	66	60	70	64	59	67	62	58	56
4	81	68	59	52	79	67	58	52	64	57	51	62	56	50	60	54	50	47
5	74	61	52	45	72	60	51	44	58	50	44	56	49	43	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	64	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	37	31	57	45	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	25	35	29	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1868	1868	1868
5°	1871	1860	1871
10°	1861	1855	1870
15°	1845	1848	1872
20°	1822	1836	1870
25°	1794	1823	1868
30°	1760	1808	1866
35°	1725	1790	1868
40°	1685	1776	1879
45°	1645	1765	1895
50°	1596	1760	1924
55°	1556	1763	1963
60°	1496	1778	2030
65°	1428	1797	2103
70°	1352	1852	2220
75°	1206	1931	2425
80°	1028	2046	2479
85°	733	2027	2371



TEST NUMBER: P310829

CATALOG NUMBER: 24FCZ2-45-UNV-L82765-CP125-W2A-U-5500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.4	3.1
10°-20°	375.7	8.9
20°-30°	567.5	13.5
30°-40°	683.9	16.2
40°-50°	718.0	17.1
50°-60°	671.7	16.0
60°-70°	554.7	13.2
70°-80°	378.0	9.0
80°-90°	128.9	3.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1074.6	25.5
0°-40°	1758.5	41.8
0°-60°	3148.3	74.8
0°-90°	4210.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4210.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1388	1388	1388	1388	1388	
5°	1386	1384	1377	1386	1386	131
15°	1324	1326	1327	1341	1344	373
25°	1208	1214	1228	1252	1258	556
35°	1050	1062	1090	1126	1137	656
45°	865	883	928	978	996	667
55°	664	690	752	813	837	592
65°	448	486	564	636	661	445
75°	232	285	372	441	466	247
85°	48	94	131	148	154	59
90°	0	0	0	0	0	



TEST NUMBER: P310829

CATALOG NUMBER: 24FCZ2-45-UNV-L82765-CP125-W2A-U-5500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1388.4	1388.4	1388.4	1388.4	1388.4
2.5°	1389.8	1388.4	1381.4	1388.4	1387.0
5°	1385.6	1384.2	1377.2	1385.6	1385.6
7.5°	1375.9	1375.9	1368.9	1378.6	1380.0
10°	1361.9	1361.9	1357.7	1368.9	1368.9
12.5°	1345.1	1345.1	1345.1	1356.3	1357.7
15°	1324.2	1325.6	1327.0	1340.9	1343.7
17.5°	1299.0	1301.8	1306.0	1322.8	1325.6
20°	1272.5	1275.3	1282.3	1301.8	1306.0
22.5°	1239.0	1245.9	1255.7	1278.1	1282.3
25°	1208.2	1213.8	1227.8	1251.5	1258.5
27.5°	1170.5	1178.9	1197.1	1222.2	1232.0
30°	1132.8	1141.2	1163.5	1192.9	1201.2
32.5°	1092.3	1104.9	1128.6	1159.3	1169.1
35°	1050.4	1061.6	1089.5	1125.8	1137.0
37.5°	1004.3	1019.7	1050.4	1089.5	1103.5
40°	959.6	976.4	1011.3	1053.2	1070.0
42.5°	914.9	931.7	970.8	1018.3	1035.0
45°	864.6	882.8	927.5	977.8	995.9
47.5°	814.3	836.7	885.6	938.7	958.2
50°	762.7	787.8	840.9	896.7	919.1
52.5°	716.6	740.3	796.2	856.2	877.2
55°	663.5	690.0	751.5	812.9	836.7
57.5°	609.0	638.3	704.0	771.0	794.8
60°	555.9	588.1	660.7	727.7	754.3
62.5°	504.2	536.4	611.8	681.6	708.2
65°	448.4	486.1	564.3	635.5	660.7
67.5°	395.3	435.8	518.2	588.1	613.2
70°	343.6	382.7	470.7	539.2	564.3
72.5°	287.7	332.4	420.4	491.7	518.2
75°	231.9	284.9	371.5	441.4	466.5
77.5°	180.2	234.7	321.3	378.5	391.1
80°	132.7	188.6	264.0	304.5	319.9
82.5°	85.2	141.1	201.1	230.5	243.0
85°	47.5	93.6	131.3	148.1	153.6
87.5°	19.6	40.5	53.1	60.1	60.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)