

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P310976

Luminaire Tested: **24FCZ2-55HE-UNV-L82765-CP250-W2A-U-2700K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P310976
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-15)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-55HE-UNV-L82765-CP250-W2A-U-2700K
Description: 2'X4' TROFFER LED MODULE, RIBBED LENS, 0.250" POLYCARB SHEET
Light Source: (336) 2700K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4321.0 lumens
Efficiency: N/A
Efficacy: 100.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.29 / 1.38
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 43.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P310976

CATALOG NUMBER: 24FCZ2-55HE-UNV-L82765-CP250-W2A-U-2700K

Luminous Intensity Polar Plot





TEST NUMBER: P310976

CATALOG NUMBER: 24FCZ2-55HE-UNV-L82765-CP250-W2A-U-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	92	89	92	89	87	88	86	84	82
2	98	89	81	75	95	87	80	74	83	78	73	80	75	71	77	73	69	67
3	89	77	69	62	86	76	68	61	73	66	60	70	64	59	67	62	58	56
4	81	68	59	52	79	67	58	52	64	57	51	62	56	50	60	54	50	47
5	74	61	52	45	72	60	51	44	58	50	44	56	49	43	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	64	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	37	31	57	45	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	25	35	29	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1917	1917	1917
5°	1921	1909	1921
10°	1910	1904	1920
15°	1893	1897	1921
20°	1870	1884	1919
25°	1841	1871	1918
30°	1806	1855	1915
35°	1771	1837	1917
40°	1730	1823	1929
45°	1689	1811	1945
50°	1639	1806	1975
55°	1597	1809	2014
60°	1535	1825	2083
65°	1465	1844	2159
70°	1388	1900	2279
75°	1237	1982	2489
80°	1055	2100	2544
85°	752	2081	2435



TEST NUMBER: P310976

CATALOG NUMBER: 24FCZ2-55HE-UNV-L82765-CP250-W2A-U-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.9	3.1
10°-20°	385.6	8.9
20°-30°	582.4	13.5
30°-40°	702.0	16.2
40°-50°	736.9	17.1
50°-60°	689.5	16.0
60°-70°	569.4	13.2
70°-80°	388.0	9.0
80°-90°	132.3	3.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1102.9	25.5
0°-40°	1804.9	41.8
0°-60°	3231.3	74.8
0°-90°	4321.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4321.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1425	1425	1425	1425	1425	
5°	1422	1421	1414	1422	1422	135
15°	1359	1360	1362	1376	1379	383
25°	1240	1246	1260	1284	1292	571
35°	1078	1090	1118	1156	1167	674
45°	887	906	952	1004	1022	684
55°	681	708	771	834	859	608
65°	460	499	579	652	678	456
75°	238	292	381	453	479	254
85°	49	96	135	152	158	61
90°	0	0	0	0	0	



TEST NUMBER: P310976

CATALOG NUMBER: 24FCZ2-55HE-UNV-L82765-CP250-W2A-U-2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1425.0	1425.0	1425.0	1425.0	1425.0
2.5°	1426.5	1425.0	1417.9	1425.0	1423.6
5°	1422.2	1420.7	1413.6	1422.2	1422.2
7.5°	1412.1	1412.1	1405.0	1415.0	1416.4
10°	1397.8	1397.8	1393.5	1405.0	1405.0
12.5°	1380.6	1380.6	1380.6	1392.1	1393.5
15°	1359.1	1360.5	1361.9	1376.3	1379.2
17.5°	1333.3	1336.1	1340.4	1357.6	1360.5
20°	1306.0	1308.9	1316.1	1336.1	1340.4
22.5°	1271.6	1278.8	1288.8	1311.8	1316.1
25°	1240.1	1245.8	1260.2	1284.5	1291.7
27.5°	1201.4	1210.0	1228.6	1254.4	1264.5
30°	1162.7	1171.3	1194.2	1224.3	1232.9
32.5°	1121.1	1134.0	1158.4	1189.9	1199.9
35°	1078.1	1089.6	1118.2	1155.5	1167.0
37.5°	1030.8	1046.5	1078.1	1118.2	1132.6
40°	984.9	1002.1	1037.9	1081.0	1098.2
42.5°	939.0	956.2	996.4	1045.1	1062.3
45°	887.4	906.1	951.9	1003.5	1022.2
47.5°	835.8	858.7	908.9	963.4	983.5
50°	782.8	808.6	863.0	920.4	943.3
52.5°	735.5	759.8	817.2	878.8	900.3
55°	681.0	708.2	771.3	834.4	858.7
57.5°	625.1	655.2	722.5	791.4	815.7
60°	570.6	603.6	678.1	746.9	774.2
62.5°	517.5	550.5	627.9	699.6	726.9
65°	460.2	498.9	579.2	652.3	678.1
67.5°	405.7	447.3	531.9	603.6	629.4
70°	352.7	392.8	483.1	553.4	579.2
72.5°	295.3	341.2	431.5	504.6	531.9
75°	238.0	292.5	381.3	453.0	478.8
77.5°	184.9	240.8	329.7	388.5	401.4
80°	136.2	193.5	271.0	312.5	328.3
82.5°	87.5	144.8	206.4	236.5	249.5
85°	48.7	96.1	134.8	152.0	157.7
87.5°	20.1	41.6	54.5	61.6	61.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)