

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P311806

Luminaire Tested: **24FCZ2-75HE-UNV-L82765-S-CA125-W2A-U-3500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P311806  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: 24FCZ2-75HE-UNV-L82765-S-CA125-W2A-U-3500K  
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS, 0.125" ACRYLIC SHEET  
Light Source: (336) 3500K TUNABLE CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment: 

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7047.0 lumens  
Efficiency: N/A  
Efficacy: 111.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 63.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P311806

CATALOG NUMBER: 24FCZ2-75HE-UNV-L82765-S-CA125-W2A-U-3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P311806

CATALOG NUMBER: 24FCZ2-75HE-UNV-L82765-S-CA125-W2A-U-3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42
6	70	56	47	40	68	55	47	40	53	46	40	52	45	40	50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3331	3331	3331
5°	3329	3320	3341
10°	3315	3315	3340
15°	3283	3299	3333
20°	3240	3272	3324
25°	3180	3240	3303
30°	3109	3203	3276
35°	3041	3151	3250
40°	2937	3098	3212
45°	2841	3037	3177
50°	2732	2980	3139
55°	2610	2925	3108
60°	2488	2879	3102
65°	2330	2829	3121
70°	2157	2844	3205
75°	1932	2898	3386
80°	1561	3070	3312
85°	1175	2695	2626



TEST NUMBER: P311806

CATALOG NUMBER: 24FCZ2-75HE-UNV-L82765-S-CA125-W2A-U-3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	234.4	3.3
10°-20°	669.7	9.5
20°-30°	1006.7	14.3
30°-40°	1199.1	17.0
40°-50°	1227.2	17.4
50°-60°	1104.9	15.7
60°-70°	867.7	12.3
70°-80°	563.2	8.0
80°-90°	174.2	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1910.7	27.1
0°-40°	3109.9	44.1
0°-60°	5442.0	77.2
0°-90°	7047.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7047.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2476	2476	2476	2476	2476	
5°	2464	2469	2458	2471	2473	234
15°	2357	2364	2368	2388	2393	665
25°	2142	2160	2182	2218	2225	987
35°	1851	1874	1918	1965	1979	1155
45°	1493	1529	1596	1656	1670	1151
55°	1112	1162	1247	1312	1325	997
65°	732	788	889	962	980	729
75°	372	443	557	634	651	393
85°	76	141	175	170	170	92
90°	0	0	0	0	0	



TEST NUMBER: P311806

CATALOG NUMBER: 24FCZ2-75HE-UNV-L82765-S-CA125-W2A-U-3500K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2475.7	2475.7	2475.7	2475.7	2475.7
2.5°	2477.9	2477.9	2466.7	2477.9	2480.1
5°	2464.5	2468.9	2457.8	2471.2	2473.4
7.5°	2451.0	2451.0	2444.3	2457.8	2460.0
10°	2426.4	2428.7	2426.4	2442.1	2444.3
12.5°	2395.1	2399.6	2401.8	2417.5	2419.7
15°	2357.0	2363.7	2368.2	2388.4	2392.8
17.5°	2314.5	2321.2	2332.4	2354.8	2359.3
20°	2263.0	2272.0	2285.4	2314.5	2321.2
22.5°	2207.1	2216.0	2238.4	2265.2	2276.4
25°	2142.1	2160.0	2182.4	2218.2	2225.0
27.5°	2077.2	2092.9	2122.0	2160.0	2169.0
30°	2001.1	2025.7	2061.6	2099.6	2108.6
32.5°	1927.3	1951.9	1994.4	2034.7	2045.9
35°	1851.1	1873.5	1918.3	1965.3	1978.7
37.5°	1763.8	1792.9	1842.2	1889.2	1902.6
40°	1672.1	1707.9	1763.8	1813.1	1828.8
42.5°	1584.8	1622.8	1678.8	1732.5	1750.4
45°	1493.0	1528.8	1596.0	1656.4	1669.8
47.5°	1399.0	1439.3	1510.9	1571.3	1593.7
50°	1305.0	1347.5	1423.6	1486.3	1499.7
52.5°	1211.0	1255.7	1336.3	1403.5	1410.2
55°	1112.5	1161.7	1246.8	1311.7	1325.1
57.5°	1022.9	1065.5	1157.2	1224.4	1240.1
60°	924.5	971.5	1069.9	1132.6	1152.8
62.5°	830.4	879.7	982.7	1045.3	1063.2
65°	732.0	787.9	888.6	962.5	980.4
67.5°	646.9	700.6	808.1	879.7	897.6
70°	548.4	608.8	723.0	796.9	814.8
72.5°	463.3	526.0	640.2	711.8	738.7
75°	371.6	443.2	557.4	633.5	651.4
77.5°	282.0	364.9	481.3	539.5	539.5
80°	201.5	288.8	396.2	423.1	427.5
82.5°	132.1	217.1	293.2	291.0	291.0
85°	76.1	141.0	174.6	170.1	170.1
87.5°	29.1	58.2	62.7	62.7	60.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)