

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P311329

Luminaire Tested: **24FCZ2-35-UNV-L82765-S-CP187-W2A-U-3500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P311329  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: 24FCZ2-35-UNV-L82765-S-CP187-W2A-U-3500K  
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS, 0.187" POLYCARB SHEET  
Light Source: (168) 3500K TUNABLE CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment: 

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3123.0 lumens  
Efficiency: N/A  
Efficacy: 111.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.27 / 1.35  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P311329

CATALOG NUMBER: 24FCZ2-35-UNV-L82765-S-CP187-W2A-U-3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P311329

CATALOG NUMBER: 24FCZ2-35-UNV-L82765-S-CP187-W2A-U-3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42
6	70	56	47	40	68	55	47	40	53	46	40	52	45	40	50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1476	1476	1476
5°	1475	1471	1480
10°	1469	1469	1480
15°	1455	1462	1477
20°	1436	1450	1473
25°	1409	1436	1464
30°	1378	1419	1452
35°	1348	1396	1440
40°	1302	1373	1423
45°	1259	1346	1408
50°	1211	1321	1391
55°	1156	1296	1378
60°	1102	1276	1375
65°	1033	1254	1383
70°	956	1260	1421
75°	856	1284	1501
80°	692	1361	1468
85°	520	1195	1164



TEST NUMBER: P311329

CATALOG NUMBER: 24FCZ2-35-UNV-L82765-S-CP187-W2A-U-3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	103.9	3.3
10°-20°	296.8	9.5
20°-30°	446.1	14.3
30°-40°	531.4	17.0
40°-50°	543.9	17.4
50°-60°	489.6	15.7
60°-70°	384.5	12.3
70°-80°	249.6	8.0
80°-90°	77.2	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	846.8	27.1
0°-40°	1378.2	44.1
0°-60°	2411.7	77.2
0°-90°	3123.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3123.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1097	1097	1097	1097	1097	
5°	1092	1094	1089	1095	1096	104
15°	1045	1048	1050	1058	1060	295
25°	949	957	967	983	986	437
35°	820	830	850	871	877	512
45°	662	678	707	734	740	510
55°	493	515	552	581	587	442
65°	324	349	394	427	434	323
75°	165	196	247	281	289	174
85°	34	62	77	75	75	41
90°	0	0	0	0	0	



TEST NUMBER: P311329

CATALOG NUMBER: 24FCZ2-35-UNV-L82765-S-CP187-W2A-U-3500K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1097.1	1097.1	1097.1	1097.1	1097.1
2.5°	1098.1	1098.1	1093.2	1098.1	1099.1
5°	1092.2	1094.2	1089.2	1095.1	1096.1
7.5°	1086.2	1086.2	1083.2	1089.2	1090.2
10°	1075.3	1076.3	1075.3	1082.3	1083.2
12.5°	1061.4	1063.4	1064.4	1071.3	1072.3
15°	1044.6	1047.5	1049.5	1058.4	1060.4
17.5°	1025.7	1028.7	1033.6	1043.6	1045.5
20°	1002.9	1006.9	1012.8	1025.7	1028.7
22.5°	978.1	982.1	992.0	1003.9	1008.8
25°	949.3	957.3	967.2	983.1	986.0
27.5°	920.6	927.5	940.4	957.3	961.2
30°	886.8	897.7	913.6	930.5	934.4
32.5°	854.1	865.0	883.9	901.7	906.7
35°	820.4	830.3	850.1	871.0	876.9
37.5°	781.7	794.6	816.4	837.2	843.2
40°	741.0	756.9	781.7	803.5	810.4
42.5°	702.3	719.2	744.0	767.8	775.7
45°	661.7	677.5	707.3	734.1	740.0
47.5°	620.0	637.8	669.6	696.4	706.3
50°	578.3	597.2	630.9	658.7	664.6
52.5°	536.7	556.5	592.2	622.0	624.9
55°	493.0	514.8	552.5	581.3	587.3
57.5°	453.3	472.2	512.9	542.6	549.6
60°	409.7	430.5	474.2	501.9	510.9
62.5°	368.0	389.8	435.5	463.3	471.2
65°	324.4	349.2	393.8	426.6	434.5
67.5°	286.7	310.5	358.1	389.8	397.8
70°	243.0	269.8	320.4	353.1	361.1
72.5°	205.3	233.1	283.7	315.4	327.4
75°	164.7	196.4	247.0	280.7	288.7
77.5°	125.0	161.7	213.3	239.1	239.1
80°	89.3	128.0	175.6	187.5	189.5
82.5°	58.5	96.2	129.9	129.0	129.0
85°	33.7	62.5	77.4	75.4	75.4
87.5°	12.9	25.8	27.8	27.8	26.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)