

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P312009

Luminaire Tested: **14FCZ2-20-UNV-L83050-RDP-CP187-W2A-U-5000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P312009  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-43)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: 14FCZ2-20-UNV-L83050-RDP-CP187-W2A-U-5000K  
Description: 1'X4' TROFFER LED MODULE, SMOOTH LENS WITH INSERT , 0.187" POLYCARB SHEET  
Light Source: (168) 5000K TUNABLE CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1279.0 lumens  
Efficiency: N/A  
Efficacy: 73.9 lumens/watt  
Spacing Criteria (0/90/45): 1.25 / 1.28 / 1.4  
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 17.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P312009

CATALOG NUMBER: 14FCZ2-20-UNV-L83050-RDP-CP187-W2A-U-5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P312009

CATALOG NUMBER: 14FC22-20-UNV-L83050-RDP-CP187-W2A-U-5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	100	96	106	102	98	94	97	94	91	93	91	88	90	88	86	84
2	99	90	83	77	96	88	82	76	85	79	75	81	77	73	78	75	71	69
3	90	79	71	64	87	77	70	63	74	68	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	53	66	58	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40	51	44	39	50	44	39	37
7	64	50	42	35	62	50	41	35	48	40	35	47	40	35	45	39	34	32
8	60	46	37	31	58	45	37	31	44	36	31	43	36	31	41	35	31	29
9	56	42	34	28	54	42	34	28	40	33	28	39	33	28	38	32	28	26
10	52	39	31	25	51	38	31	25	37	30	25	36	30	25	35	29	25	23

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1153	1153	1153
5°	1157	1146	1152
10°	1154	1146	1151
15°	1149	1143	1152
20°	1141	1141	1149
25°	1135	1135	1150
30°	1126	1133	1151
35°	1112	1128	1155
40°	1094	1126	1165
45°	1075	1125	1185
50°	1045	1129	1212
55°	1007	1143	1246
60°	956	1156	1274
65°	884	1170	1291
70°	786	1179	1155
75°	633	1059	924
80°	496	742	603
85°	340	216	154



TEST NUMBER: P312009

CATALOG NUMBER: 14FCZ2-20-UNV-L83050-RDP-CP187-W2A-U-5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	40.5	3.2
10°-20°	116.3	9.1
20°-30°	177.1	13.8
30°-40°	215.7	16.9
40°-50°	228.9	17.9
50°-60°	216.0	16.9
60°-70°	174.4	13.6
70°-80°	94.6	7.4
80°-90°	15.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	334.0	26.1
0°-40°	549.7	43.0
0°-60°	994.7	77.8
0°-90°	1279.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1279.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	428	428	428	428	428	
5°	428	427	424	427	426	41
15°	412	411	410	413	413	116
25°	382	381	382	386	387	176
35°	338	340	344	350	352	212
45°	283	287	296	306	312	218
55°	215	224	244	260	266	192
65°	139	156	184	199	203	138
75°	61	89	102	92	89	67
85°	11	12	7	6	5	14
90°	0	0	0	0	0	



TEST NUMBER: P312009

CATALOG NUMBER: 14FC22-20-UNV-L83050-RDP-CP187-W2A-U-5000K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	428.4	428.4	428.4	428.4	428.4
2.5°	430.4	428.4	425.4	428.4	427.4
5°	428.4	427.4	424.4	427.4	426.4
7.5°	425.4	425.4	422.4	424.4	424.4
10°	422.4	421.4	419.4	422.4	421.4
12.5°	417.4	416.4	415.4	418.4	417.4
15°	412.4	411.4	410.4	413.4	413.4
17.5°	406.4	405.4	404.4	408.4	408.4
20°	398.4	398.4	398.4	402.4	401.4
22.5°	390.4	390.4	391.4	395.4	394.4
25°	382.4	381.4	382.4	386.4	387.4
27.5°	372.5	373.5	374.4	378.4	379.4
30°	362.5	363.5	364.5	369.5	370.5
32.5°	350.5	352.5	354.5	360.5	360.5
35°	338.5	340.5	343.5	350.5	351.5
37.5°	325.5	327.5	331.5	339.5	341.5
40°	311.5	314.5	320.5	328.5	331.5
42.5°	297.6	301.6	308.5	317.5	321.5
45°	282.6	286.6	295.6	306.5	311.5
47.5°	266.6	271.6	282.6	296.6	300.6
50°	249.6	256.6	269.6	284.6	289.6
52.5°	232.7	240.6	256.6	272.6	277.6
55°	214.7	223.7	243.6	259.6	265.6
57.5°	196.7	206.7	229.7	246.6	252.6
60°	177.7	189.7	214.7	231.7	236.7
62.5°	158.8	172.7	199.7	216.7	220.7
65°	138.8	155.8	183.7	198.7	202.7
67.5°	119.8	139.8	167.8	178.7	178.7
70°	99.9	121.8	149.8	152.8	146.8
72.5°	79.9	104.8	129.8	118.8	113.8
75°	60.9	88.9	101.9	91.9	88.9
77.5°	45.9	71.9	71.9	65.9	63.9
80°	32.0	54.9	47.9	41.9	38.9
82.5°	21.0	31.0	25.0	20.0	17.0
85°	11.0	12.0	7.0	6.0	5.0
87.5°	4.0	2.0	1.0	2.0	1.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)