

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P311593

Luminaire Tested: **24FCZ2-50-UNV-L82765-S-CP125-W2A-U-5000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P311593
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-50-UNV-L82765-S-CP125-W2A-U-5000K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS, 0.125" POLYCARB SHEET
Light Source: (168) 5000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4834.0 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 43.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P311593

CATALOG NUMBER: 24FCZ2-50-UNV-L82765-S-CP125-W2A-U-5000K

Luminous Intensity Polar Plot





TEST NUMBER: P311593

CATALOG NUMBER: 24FCZ2-50-UNV-L82765-S-CP125-W2A-U-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42
6	70	56	47	40	68	55	47	40	53	46	40	52	45	40	50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2285	2285	2285
5°	2283	2277	2292
10°	2274	2274	2291
15°	2252	2263	2286
20°	2223	2245	2280
25°	2181	2223	2266
30°	2133	2197	2247
35°	2086	2161	2229
40°	2015	2125	2203
45°	1949	2083	2180
50°	1874	2044	2153
55°	1790	2006	2132
60°	1706	1975	2128
65°	1599	1941	2141
70°	1480	1951	2199
75°	1325	1987	2323
80°	1071	2106	2273
85°	806	1849	1802



TEST NUMBER: P311593

CATALOG NUMBER: 24FCZ2-50-UNV-L82765-S-CP125-W2A-U-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.8	3.3
10°-20°	459.4	9.5
20°-30°	690.6	14.3
30°-40°	822.6	17.0
40°-50°	841.8	17.4
50°-60°	757.9	15.7
60°-70°	595.2	12.3
70°-80°	386.3	8.0
80°-90°	119.5	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1310.7	27.1
0°-40°	2133.3	44.1
0°-60°	3733.0	77.2
0°-90°	4834.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4834.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1698	1698	1698	1698	1698	
5°	1690	1694	1686	1695	1697	161
15°	1617	1621	1624	1638	1641	456
25°	1469	1482	1497	1522	1526	677
35°	1270	1285	1316	1348	1357	792
45°	1024	1049	1095	1136	1146	790
55°	763	797	855	900	909	684
65°	502	540	610	660	672	500
75°	255	304	382	434	447	270
85°	52	97	120	117	117	63
90°	0	0	0	0	0	



TEST NUMBER: P311593

CATALOG NUMBER: 24FCZ2-50-UNV-L82765-S-CP125-W2A-U-5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1698.2	1698.2	1698.2	1698.2	1698.2
2.5°	1699.8	1699.8	1692.1	1699.8	1701.3
5°	1690.5	1693.6	1685.9	1695.1	1696.7
7.5°	1681.3	1681.3	1676.7	1685.9	1687.5
10°	1664.4	1666.0	1664.4	1675.2	1676.7
12.5°	1642.9	1646.0	1647.5	1658.3	1659.8
15°	1616.8	1621.4	1624.5	1638.3	1641.4
17.5°	1587.7	1592.3	1599.9	1615.3	1618.4
20°	1552.3	1558.5	1567.7	1587.7	1592.3
22.5°	1514.0	1520.1	1535.5	1553.9	1561.6
25°	1469.4	1481.7	1497.1	1521.6	1526.2
27.5°	1424.9	1435.7	1455.6	1481.7	1487.9
30°	1372.7	1389.6	1414.2	1440.3	1446.4
32.5°	1322.0	1338.9	1368.1	1395.7	1403.4
35°	1269.8	1285.2	1315.9	1348.1	1357.3
37.5°	1209.9	1229.9	1263.7	1295.9	1305.1
40°	1147.0	1171.6	1209.9	1243.7	1254.5
42.5°	1087.1	1113.2	1151.6	1188.4	1200.7
45°	1024.2	1048.7	1094.8	1136.2	1145.5
47.5°	959.7	987.3	1036.4	1077.9	1093.2
50°	895.2	924.3	976.6	1019.5	1028.8
52.5°	830.7	861.4	916.7	962.7	967.3
55°	763.1	796.9	855.2	899.8	909.0
57.5°	701.7	730.9	793.8	839.9	850.6
60°	634.1	666.4	733.9	776.9	790.8
62.5°	569.7	603.4	674.1	717.1	729.3
65°	502.1	540.5	609.6	660.2	672.5
67.5°	443.7	480.6	554.3	603.4	615.7
70°	376.2	417.6	496.0	546.6	558.9
72.5°	317.8	360.8	439.1	488.3	506.7
75°	254.9	304.0	382.3	434.5	446.8
77.5°	193.5	250.3	330.1	370.0	370.0
80°	138.2	198.1	271.8	290.2	293.3
82.5°	90.6	148.9	201.1	199.6	199.6
85°	52.2	96.7	119.8	116.7	116.7
87.5°	20.0	39.9	43.0	43.0	41.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)