

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P311746

Luminaire Tested: **24FCZ2-65HE-UNV-L82765-S-CP250-W2A-U-5000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P311746  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: 24FCZ2-65HE-UNV-L82765-S-CP250-W2A-U-5000K  
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS, 0.250" POLYCARB SHEET  
Light Source: (336) 5000K TUNABLE CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment: 

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6000.0 lumens  
Efficiency: N/A  
Efficacy: 111.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 53.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P311746

CATALOG NUMBER: 24FCZ2-65HE-UNV-L82765-S-CP250-W2A-U-5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P311746

CATALOG NUMBER: 24FCZ2-65HE-UNV-L82765-S-CP250-W2A-U-5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42
6	70	56	47	40	68	55	47	40	53	46	40	52	45	40	50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2836	2836	2836
5°	2834	2826	2844
10°	2823	2823	2843
15°	2795	2809	2838
20°	2759	2786	2830
25°	2708	2759	2812
30°	2647	2727	2789
35°	2589	2683	2767
40°	2500	2638	2735
45°	2419	2586	2705
50°	2326	2537	2673
55°	2222	2490	2647
60°	2118	2451	2641
65°	1984	2409	2658
70°	1837	2422	2729
75°	1645	2467	2883
80°	1329	2614	2820
85°	1000	2296	2235



TEST NUMBER: P311746

CATALOG NUMBER: 24FCZ2-65HE-UNV-L82765-S-CP250-W2A-U-5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	199.5	3.3
10°-20°	570.2	9.5
20°-30°	857.1	14.3
30°-40°	1021.0	17.0
40°-50°	1044.9	17.4
50°-60°	940.7	15.7
60°-70°	738.8	12.3
70°-80°	479.5	8.0
80°-90°	148.3	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1626.9	27.1
0°-40°	2647.8	44.1
0°-60°	4633.5	77.2
0°-90°	6000.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6000.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2108	2108	2108	2108	2108	
5°	2098	2102	2093	2104	2106	199
15°	2007	2012	2016	2034	2037	566
25°	1824	1839	1858	1889	1894	840
35°	1576	1595	1633	1673	1685	983
45°	1271	1302	1359	1410	1422	980
55°	947	989	1062	1117	1128	849
65°	623	671	757	820	835	620
75°	316	377	474	539	555	335
85°	65	120	149	145	145	78
90°	0	0	0	0	0	



TEST NUMBER: P311746

CATALOG NUMBER: 24FCZ2-65HE-UNV-L82765-S-CP250-W2A-U-5000K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2107.8	2107.8	2107.8	2107.8	2107.8
2.5°	2109.7	2109.7	2100.2	2109.7	2111.7
5°	2098.3	2102.1	2092.6	2104.0	2105.9
7.5°	2086.9	2086.9	2081.2	2092.6	2094.5
10°	2065.9	2067.8	2065.9	2079.3	2081.2
12.5°	2039.2	2043.0	2044.9	2058.3	2060.2
15°	2006.8	2012.5	2016.4	2033.5	2037.3
17.5°	1970.6	1976.3	1985.9	2004.9	2008.7
20°	1926.8	1934.4	1945.8	1970.6	1976.3
22.5°	1879.1	1886.8	1905.8	1928.7	1938.2
25°	1823.9	1839.1	1858.2	1888.7	1894.4
27.5°	1768.6	1781.9	1806.7	1839.1	1846.7
30°	1703.8	1724.8	1755.3	1787.7	1795.3
32.5°	1640.9	1661.9	1698.1	1732.4	1741.9
35°	1576.1	1595.2	1633.3	1673.3	1684.7
37.5°	1501.8	1526.6	1568.5	1608.5	1619.9
40°	1423.6	1454.1	1501.8	1543.7	1557.1
42.5°	1349.3	1381.7	1429.4	1475.1	1490.4
45°	1271.2	1301.7	1358.9	1410.3	1421.7
47.5°	1191.1	1225.4	1286.4	1337.9	1356.9
50°	1111.1	1147.3	1212.1	1265.5	1276.9
52.5°	1031.0	1069.2	1137.8	1195.0	1200.7
55°	947.2	989.1	1061.5	1116.8	1128.2
57.5°	871.0	907.2	985.3	1042.5	1055.8
60°	787.1	827.1	911.0	964.3	981.5
62.5°	707.1	749.0	836.7	890.0	905.3
65°	623.2	670.8	756.6	819.5	834.8
67.5°	550.8	596.5	688.0	749.0	764.2
70°	466.9	518.4	615.6	678.5	693.7
72.5°	394.5	447.9	545.1	606.1	628.9
75°	316.4	377.4	474.5	539.3	554.6
77.5°	240.1	310.6	409.8	459.3	459.3
80°	171.5	245.9	337.3	360.2	364.0
82.5°	112.4	184.9	249.7	247.8	247.8
85°	64.8	120.1	148.7	144.8	144.8
87.5°	24.8	49.6	53.4	53.4	51.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)