

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P312829

Luminaire Tested: **22FCZ2-34HE-UNV-L83050-CP125-W2A-U-5000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P312829  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-33)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: 22FCZ2-34HE-UNV-L83050-CP125-W2A-U-5000K  
Description: 2'X2' TROFFER LED MODULE, RIBBED LENS, 0.125" POLYCARB SHEET  
Light Source: (168) 5000K TUNABLE CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment: 

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3205.0 lumens  
Efficiency: N/A  
Efficacy: 110.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.28 / 1.37  
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 29  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P312829

CATALOG NUMBER: 22FCZ2-34HE-UNV-L83050-CP125-W2A-U-5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P312829

CATALOG NUMBER: 22FC22-34HE-UNV-L83050-CP125-W2A-U-5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	90	92	89	87	89	86	84	82
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	77	73	70	67
3	89	78	69	62	86	76	68	62	73	66	61	70	64	60	68	63	59	56
4	81	69	60	53	79	67	59	52	65	57	51	62	56	51	60	55	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	39	51	44	38	49	43	38	36
7	64	50	41	35	62	49	40	34	47	40	34	46	39	34	45	38	34	32
8	59	45	37	31	58	45	36	31	43	36	30	42	35	30	41	35	30	28
9	55	42	33	28	54	41	33	28	40	33	27	39	32	27	38	32	27	25
10	52	38	30	25	51	38	30	25	37	30	25	36	29	25	35	29	25	23

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2894	2894	2894
5°	2876	2896	2905
10°	2859	2888	2905
15°	2825	2868	2897
20°	2785	2846	2890
25°	2742	2828	2888
30°	2679	2783	2884
35°	2621	2751	2888
40°	2554	2716	2899
45°	2528	2691	2925
50°	2415	2671	2967
55°	2389	2663	3030
60°	2254	2658	3112
65°	2188	2676	3252
70°	2100	2740	3452
75°	1914	2823	3716
80°	1640	2924	3756
85°	1328	2794	3220



TEST NUMBER: P312829

CATALOG NUMBER: 22FCZ2-34HE-UNV-L83050-CP125-W2A-U-5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	101.7	3.2
10°-20°	290.3	9.1
20°-30°	436.9	13.6
30°-40°	524.3	16.4
40°-50°	548.0	17.1
50°-60°	510.7	15.9
60°-70°	418.9	13.1
70°-80°	282.3	8.8
80°-90°	91.9	2.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	828.9	25.9
0°-40°	1353.2	42.2
0°-60°	2411.9	75.3
0°-90°	3205.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3205.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1075	1075	1075	1075	1075	
5°	1065	1068	1072	1074	1075	101
15°	1014	1020	1029	1038	1040	287
25°	923	930	953	966	972	425
35°	798	808	838	867	879	499
45°	664	669	707	750	768	507
55°	509	518	568	621	646	451
65°	344	359	420	482	511	342
75°	184	204	272	333	357	194
85°	43	61	90	106	104	51
90°	0	0	0	0	0	



TEST NUMBER: P312829

CATALOG NUMBER: 22FCZ2-34HE-UNV-L83050-CP125-W2A-U-5000K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1075.3	1075.3	1075.3	1075.3	1075.3
2.5°	1069.2	1072.2	1076.8	1078.4	1078.4
5°	1064.6	1067.6	1072.2	1073.8	1075.3
7.5°	1056.9	1060.0	1066.1	1069.2	1070.7
10°	1046.2	1049.2	1056.9	1061.5	1063.0
12.5°	1032.4	1035.4	1044.6	1050.8	1052.3
15°	1013.9	1020.1	1029.3	1038.5	1040.0
17.5°	1001.7	1000.1	1012.4	1023.2	1026.2
20°	972.5	980.2	994.0	1006.3	1009.3
22.5°	948.0	954.1	972.5	986.3	992.5
25°	923.4	929.6	952.6	966.4	972.5
27.5°	892.8	902.0	923.4	943.4	951.1
30°	862.1	871.3	895.8	918.8	928.0
32.5°	831.4	842.1	868.2	892.8	903.5
35°	797.7	808.4	837.5	866.7	879.0
37.5°	762.4	776.2	806.9	839.1	852.9
40°	727.1	740.9	773.1	809.9	825.3
42.5°	698.0	704.1	740.9	780.8	796.1
45°	664.2	668.8	707.2	750.1	768.5
47.5°	615.1	632.0	673.4	721.0	739.4
50°	576.8	595.2	638.1	688.7	708.7
52.5°	544.6	556.8	604.4	655.0	678.0
55°	509.3	518.5	567.6	621.3	645.8
57.5°	466.3	483.2	532.3	587.5	612.0
60°	418.8	440.2	493.9	553.8	578.3
62.5°	388.1	400.4	458.7	518.5	546.1
65°	343.6	358.9	420.3	481.7	510.8
67.5°	306.8	322.1	385.0	446.4	475.5
70°	266.9	282.2	348.2	409.6	438.7
72.5°	220.9	242.4	311.4	372.8	403.4
75°	184.1	204.0	271.5	332.9	357.4
77.5°	142.7	168.7	231.6	282.2	300.7
80°	105.8	131.9	188.7	225.5	242.4
82.5°	72.1	98.2	141.1	168.7	177.9
85°	43.0	61.4	90.5	105.8	104.3
87.5°	19.9	26.1	36.8	36.8	35.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)