

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P313145

Luminaire Tested: **24FCZ2-40HE-UNV-L83050-HRP-CA125-W2A-U-3000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P313145
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-40HE-UNV-L83050-HRP-CA125-W2A-U-3000K
Description: 2'X4' TROFFER LED MODULE, HIGH EFFICIENCY RND PERF. LENS, 0.125" ACRYLIC SHEET
Light Source: (336) 3000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2724.0 lumens
Efficiency: N/A
Efficacy: 89.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 30.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P313145

CATALOG NUMBER: 24FCZ2-40HE-UNV-L83050-HRP-CA125-W2A-U-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P313145

CATALOG NUMBER: 24FCZ2-40HE-UNV-L83050-HRP-CA125-W2A-U-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	96	93	96	93	90	92	90	87	89	86	84	82
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	77	73	70	67
3	89	78	69	62	86	76	68	62	73	66	61	70	64	59	68	63	58	56
4	81	68	59	52	79	67	59	52	65	57	51	62	56	50	60	54	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	63	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	36	30	57	44	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	24	35	29	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1189	1189	1189
5°	1191	1186	1191
10°	1187	1186	1193
15°	1180	1183	1195
20°	1172	1181	1197
25°	1158	1175	1199
30°	1145	1171	1203
35°	1126	1165	1204
40°	1106	1158	1216
45°	1081	1157	1235
50°	1046	1155	1267
55°	1008	1164	1313
60°	951	1182	1372
65°	879	1209	1449
70°	767	1252	1543
75°	622	1316	1595
80°	459	1290	1290
85°	352	951	1074



TEST NUMBER: P313145

CATALOG NUMBER: 24FCZ2-40HE-UNV-L83050-HRP-CA125-W2A-U-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.7	3.1
10°-20°	240.4	8.8
20°-30°	366.0	13.4
30°-40°	444.4	16.3
40°-50°	469.5	17.2
50°-60°	443.1	16.3
60°-70°	368.4	13.5
70°-80°	242.4	8.9
80°-90°	66.1	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	690.2	25.3
0°-40°	1134.6	41.7
0°-60°	2047.2	75.2
0°-90°	2724.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2724.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	884	884	884	884	884	
5°	882	882	878	882	882	84
15°	847	848	850	858	858	239
25°	780	785	791	805	807	360
35°	685	693	709	728	733	429
45°	568	579	608	638	649	437
55°	430	448	496	543	560	383
65°	276	308	380	436	455	273
75°	120	174	253	300	307	129
85°	23	50	62	68	70	28
90°	0	0	0	0	0	



TEST NUMBER: P313145

CATALOG NUMBER: 24FCZ2-40HE-UNV-L83050-HRP-CA125-W2A-U-3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	883.8	883.8	883.8	883.8	883.8
2.5°	884.9	883.8	879.2	883.8	883.8
5°	881.5	881.5	878.1	881.5	881.5
7.5°	875.8	875.8	873.5	878.1	878.1
10°	869.0	869.0	867.8	873.5	873.5
12.5°	858.7	859.9	858.7	865.6	865.6
15°	847.3	848.5	849.6	857.6	857.6
17.5°	832.5	834.8	837.0	846.2	847.3
20°	818.8	819.9	824.5	834.8	835.9
22.5°	800.6	804.0	809.7	819.9	823.4
25°	780.0	784.6	791.4	805.1	807.4
27.5°	760.6	764.1	773.2	788.0	792.6
30°	736.7	742.4	753.8	768.6	774.3
32.5°	713.9	719.6	733.3	749.2	753.8
35°	685.4	693.4	709.3	727.6	733.3
37.5°	658.0	666.0	685.4	705.9	712.7
40°	629.5	638.6	659.1	683.1	692.2
42.5°	598.7	611.3	634.1	660.3	670.6
45°	567.9	579.3	607.8	637.5	648.9
47.5°	534.8	548.5	579.3	614.7	628.4
50°	499.5	516.6	551.9	590.7	605.5
52.5°	464.1	483.5	523.4	566.8	582.7
55°	429.9	448.2	496.1	542.8	559.9
57.5°	392.3	415.1	467.6	517.7	534.8
60°	353.5	378.6	439.1	491.5	509.8
62.5°	314.7	343.3	411.7	464.1	483.5
65°	276.0	307.9	379.8	435.6	455.0
67.5°	238.3	273.7	350.1	406.0	425.4
70°	195.0	239.5	318.2	372.9	392.3
72.5°	155.1	206.4	287.4	338.7	355.8
75°	119.7	174.5	253.2	299.9	306.8
77.5°	87.8	142.5	217.8	233.8	234.9
80°	59.3	114.0	166.5	164.2	166.5
82.5°	38.8	85.5	104.9	117.5	118.6
85°	22.8	50.2	61.6	68.4	69.6
87.5°	11.4	17.1	21.7	22.8	25.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)