

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P313274

Luminaire Tested: **24FCZ2-50-UNV-L83050-HRP-CA125-W2A-U-5000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P313274  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: 24FCZ2-50-UNV-L83050-HRP-CA125-W2A-U-5000K  
Description: 2'X4' TROFFER LED MODULE, HIGH EFFICIENCY RND PERF. LENS, 0.125" ACRYLIC SHEET  
Light Source: (168) 5000K TUNABLE CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3752.0 lumens  
Efficiency: N/A  
Efficacy: 83.7 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct


Input Watts (W): 44.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P313274

CATALOG NUMBER: 24FCZ2-50-UNV-L83050-HRP-CA125-W2A-U-5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P313274

CATALOG NUMBER: 24FCZ2-50-UNV-L83050-HRP-CA125-W2A-U-5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	96	93	96	93	90	92	90	87	89	86	84	82
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	77	73	70	67
3	89	78	69	62	86	76	68	62	73	66	61	70	64	59	68	63	58	56
4	81	68	59	52	79	67	59	52	65	57	51	62	56	50	60	54	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	63	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	36	30	57	44	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	24	35	29	24	23

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1638	1638	1638
5°	1640	1634	1640
10°	1635	1633	1644
15°	1626	1630	1645
20°	1615	1626	1649
25°	1595	1618	1651
30°	1576	1613	1657
35°	1551	1605	1659
40°	1523	1595	1675
45°	1488	1593	1701
50°	1440	1591	1746
55°	1389	1603	1809
60°	1310	1627	1889
65°	1210	1665	1995
70°	1057	1724	2126
75°	857	1813	2196
80°	633	1777	1777
85°	485	1309	1479



TEST NUMBER: P313274

CATALOG NUMBER: 24FCZ2-50-UNV-L83050-HRP-CA125-W2A-U-5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	115.3	3.1
10°-20°	331.2	8.8
20°-30°	504.1	13.4
30°-40°	612.1	16.3
40°-50°	646.7	17.2
50°-60°	610.3	16.3
60°-70°	507.4	13.5
70°-80°	333.8	8.9
80°-90°	91.0	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	950.6	25.3
0°-40°	1562.8	41.7
0°-60°	2819.8	75.2
0°-90°	3752.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3752.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1217	1217	1217	1217	1217	
5°	1214	1214	1210	1214	1214	115
15°	1167	1169	1170	1181	1181	329
25°	1074	1081	1090	1109	1112	496
35°	944	955	977	1002	1010	591
45°	782	798	837	878	894	602
55°	592	617	683	748	771	527
65°	380	424	523	600	627	376
75°	165	240	349	413	422	178
85°	31	69	85	94	96	38
90°	0	0	0	0	0	



TEST NUMBER: P313274

CATALOG NUMBER: 24FCZ2-50-UNV-L83050-HRP-CA125-W2A-U-5000K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1217.3	1217.3	1217.3	1217.3	1217.3
2.5°	1218.9	1217.3	1211.1	1217.3	1217.3
5°	1214.2	1214.2	1209.5	1214.2	1214.2
7.5°	1206.3	1206.3	1203.2	1209.5	1209.5
10°	1196.9	1196.9	1195.3	1203.2	1203.2
12.5°	1182.8	1184.4	1182.8	1192.2	1192.2
15°	1167.1	1168.6	1170.2	1181.2	1181.2
17.5°	1146.7	1149.8	1152.9	1165.5	1167.1
20°	1127.8	1129.4	1135.7	1149.8	1151.4
22.5°	1102.7	1107.4	1115.2	1129.4	1134.1
25°	1074.4	1080.7	1090.1	1109.0	1112.1
27.5°	1047.7	1052.4	1065.0	1085.4	1091.7
30°	1014.7	1022.6	1038.3	1058.7	1066.5
32.5°	983.3	991.1	1010.0	1032.0	1038.3
35°	944.0	955.0	977.0	1002.1	1010.0
37.5°	906.3	917.3	944.0	972.3	981.7
40°	867.1	879.6	907.9	940.9	953.5
42.5°	824.6	841.9	873.3	909.5	923.6
45°	782.2	797.9	837.2	878.1	893.8
47.5°	736.7	755.5	797.9	846.6	865.5
50°	688.0	711.6	760.2	813.7	834.1
52.5°	639.3	666.0	721.0	780.7	802.7
55°	592.2	617.3	683.3	747.7	771.2
57.5°	540.3	571.8	644.0	713.1	736.7
60°	486.9	521.5	604.7	677.0	702.1
62.5°	433.5	472.8	567.0	639.3	666.0
65°	380.1	424.1	523.1	600.0	626.7
67.5°	328.3	377.0	482.2	559.2	585.9
70°	268.6	329.9	438.2	513.6	540.3
72.5°	213.6	284.3	395.8	466.5	490.1
75°	164.9	240.3	348.7	413.1	422.5
77.5°	120.9	196.3	300.0	322.0	323.6
80°	81.7	157.1	229.3	226.2	229.3
82.5°	53.4	117.8	144.5	161.8	163.4
85°	31.4	69.1	84.8	94.2	95.8
87.5°	15.7	23.6	29.8	31.4	34.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)