

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P313065

Luminaire Tested: **24FCZ2-30-UNV-L83050-HRP-CA08-W2A-U-3000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P313065
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-30-UNV-L83050-HRP-CA08-W2A-U-3000K
Description: 2'X4' TROFFER LED MODULE, HIGH EFFICIENCY RND PERF. LENS, 0.08" ACRYLIC SHEET
Light Source: (168) 3000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2036.0 lumens
Efficiency: N/A
Efficacy: 87.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 23.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P313065
CATALOG NUMBER: 24FCZ2-30-UNV-L83050-HRP-CA08-W2A-U-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P313065

CATALOG NUMBER: 24FCZ2-30-UNV-L83050-HRP-CA08-W2A-U-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	96	93	96	93	90	92	90	87	89	86	84	82
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	77	73	70	67
3	89	78	69	62	86	76	68	62	73	66	61	70	64	59	68	63	58	56
4	81	68	59	52	79	67	59	52	65	57	51	62	56	50	60	54	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	63	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	36	30	57	44	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	24	35	29	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	889	889	889
5°	890	886	890
10°	887	886	892
15°	882	885	893
20°	876	882	895
25°	866	878	896
30°	855	875	899
35°	841	871	900
40°	826	865	909
45°	808	864	923
50°	781	863	947
55°	754	870	982
60°	711	883	1025
65°	657	904	1083
70°	574	935	1153
75°	465	984	1192
80°	343	964	964
85°	262	710	803



TEST NUMBER: P313065

CATALOG NUMBER: 24FCZ2-30-UNV-L83050-HRP-CA08-W2A-U-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.6	3.1
10°-20°	179.7	8.8
20°-30°	273.6	13.4
30°-40°	332.2	16.3
40°-50°	350.9	17.2
50°-60°	331.2	16.3
60°-70°	275.3	13.5
70°-80°	181.1	8.9
80°-90°	49.4	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	515.8	25.3
0°-40°	848.0	41.7
0°-60°	1530.1	75.2
0°-90°	2036.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2036.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	661	661	661	661	661	
5°	659	659	656	659	659	63
15°	633	634	635	641	641	179
25°	583	586	592	602	604	269
35°	512	518	530	544	548	321
45°	424	433	454	476	485	327
55°	321	335	371	406	418	286
65°	206	230	284	326	340	204
75°	90	130	189	224	229	96
85°	17	38	46	51	52	21
90°	0	0	0	0	0	



TEST NUMBER: P313065

CATALOG NUMBER: 24FCZ2-30-UNV-L83050-HRP-CA08-W2A-U-3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	660.6	660.6	660.6	660.6	660.6
2.5°	661.4	660.6	657.2	660.6	660.6
5°	658.9	658.9	656.3	658.9	658.9
7.5°	654.6	654.6	652.9	656.3	656.3
10°	649.5	649.5	648.6	652.9	652.9
12.5°	641.8	642.7	641.8	646.9	646.9
15°	633.3	634.2	635.0	641.0	641.0
17.5°	622.2	623.9	625.6	632.5	633.3
20°	612.0	612.8	616.3	623.9	624.8
22.5°	598.4	600.9	605.2	612.8	615.4
25°	583.0	586.4	591.5	601.8	603.5
27.5°	568.5	571.1	577.9	589.0	592.4
30°	550.6	554.9	563.4	574.5	578.8
32.5°	533.6	537.8	548.1	560.0	563.4
35°	512.3	518.2	530.2	543.8	548.1
37.5°	491.8	497.8	512.3	527.6	532.7
40°	470.5	477.3	492.7	510.6	517.4
42.5°	447.5	456.9	473.9	493.5	501.2
45°	424.5	433.0	454.3	476.5	485.0
47.5°	399.8	410.0	433.0	459.4	469.7
50°	373.3	386.1	412.5	441.5	452.6
52.5°	346.9	361.4	391.2	423.6	435.6
55°	321.3	335.0	370.8	405.7	418.5
57.5°	293.2	310.3	349.5	387.0	399.8
60°	264.2	283.0	328.2	367.4	381.0
62.5°	235.3	256.6	307.7	346.9	361.4
65°	206.3	230.1	283.8	325.6	340.1
67.5°	178.1	204.6	261.7	303.4	317.9
70°	145.8	179.0	237.8	278.7	293.2
72.5°	115.9	154.3	214.8	253.2	265.9
75°	89.5	130.4	189.2	224.2	229.3
77.5°	65.6	106.5	162.8	174.7	175.6
80°	44.3	85.2	124.4	122.7	124.4
82.5°	29.0	63.9	78.4	87.8	88.6
85°	17.0	37.5	46.0	51.1	52.0
87.5°	8.5	12.8	16.2	17.0	18.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)