

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P313070

Luminaire Tested: **24FCZ2-30-UNV-L83050-HRP-CA125-W2A-U-3000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P313070
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-30-UNV-L83050-HRP-CA125-W2A-U-3000K
Description: 2'X4' TROFFER LED MODULE, HIGH EFFICIENCY RND PERF. LENS, 0.125" ACRYLIC SHEET
Light Source: (168) 3000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2028.0 lumens
Efficiency: N/A
Efficacy: 86.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 23.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P313070

CATALOG NUMBER: 24FCZ2-30-UNV-L83050-HRP-CA125-W2A-U-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P313070

CATALOG NUMBER: 24FCZ2-30-UNV-L83050-HRP-CA125-W2A-U-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	96	93	96	93	90	92	90	87	89	86	84	82
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	77	73	70	67
3	89	78	69	62	86	76	68	62	73	66	61	70	64	59	68	63	58	56
4	81	68	59	52	79	67	59	52	65	57	51	62	56	50	60	54	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	63	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	36	30	57	44	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	24	35	29	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	885	885	885
5°	886	883	886
10°	884	883	888
15°	879	881	889
20°	873	879	891
25°	862	875	892
30°	852	872	896
35°	838	867	897
40°	823	862	905
45°	805	861	919
50°	778	860	944
55°	751	866	978
60°	708	880	1021
65°	654	900	1079
70°	571	932	1149
75°	463	980	1187
80°	342	961	961
85°	262	707	800



TEST NUMBER: P313070

CATALOG NUMBER: 24FCZ2-30-UNV-L83050-HRP-CA125-W2A-U-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.3	3.1
10°-20°	179.0	8.8
20°-30°	272.5	13.4
30°-40°	330.9	16.3
40°-50°	349.6	17.2
50°-60°	329.9	16.3
60°-70°	274.3	13.5
70°-80°	180.4	8.9
80°-90°	49.2	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	513.8	25.3
0°-40°	844.7	41.7
0°-60°	1524.1	75.2
0°-90°	2028.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2028.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	658	658	658	658	658	
5°	656	656	654	656	656	62
15°	631	632	632	638	638	178
25°	581	584	589	599	601	268
35°	510	516	528	542	546	319
45°	423	431	452	475	483	326
55°	320	334	369	404	417	285
65°	206	229	283	324	339	203
75°	89	130	188	223	228	96
85°	17	37	46	51	52	21
90°	0	0	0	0	0	



TEST NUMBER: P313070

CATALOG NUMBER: 24FCZ2-30-UNV-L83050-HRP-CA125-W2A-U-3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	658.0	658.0	658.0	658.0	658.0
2.5°	658.8	658.0	654.6	658.0	658.0
5°	656.3	656.3	653.7	656.3	656.3
7.5°	652.0	652.0	650.3	653.7	653.7
10°	646.9	646.9	646.1	650.3	650.3
12.5°	639.3	640.2	639.3	644.4	644.4
15°	630.8	631.7	632.5	638.5	638.5
17.5°	619.8	621.5	623.2	630.0	630.8
20°	609.6	610.4	613.8	621.5	622.3
22.5°	596.0	598.6	602.8	610.4	613.0
25°	580.7	584.1	589.2	599.4	601.1
27.5°	566.3	568.8	575.6	586.7	590.1
30°	548.5	552.7	561.2	572.2	576.5
32.5°	531.5	535.7	545.9	557.8	561.2
35°	510.3	516.2	528.1	541.7	545.9
37.5°	489.9	495.8	510.3	525.5	530.6
40°	468.7	475.4	490.7	508.6	515.4
42.5°	445.7	455.1	472.1	491.6	499.2
45°	422.8	431.3	452.5	474.6	483.1
47.5°	398.2	408.4	431.3	457.6	467.8
50°	371.9	384.6	410.9	439.8	450.8
52.5°	345.5	360.0	389.7	422.0	433.8
55°	320.1	333.7	369.3	404.1	416.9
57.5°	292.1	309.0	348.1	385.5	398.2
60°	263.2	281.9	326.9	365.9	379.5
62.5°	234.3	255.6	306.5	345.5	360.0
65°	205.5	229.2	282.7	324.3	338.8
67.5°	177.4	203.8	260.6	302.2	316.7
70°	145.2	178.3	236.9	277.6	292.1
72.5°	115.5	153.7	214.0	252.2	264.9
75°	89.1	129.9	188.5	223.3	228.4
77.5°	65.4	106.1	162.2	174.0	174.9
80°	44.1	84.9	124.0	122.3	124.0
82.5°	28.9	63.7	78.1	87.4	88.3
85°	17.0	37.4	45.8	50.9	51.8
87.5°	8.5	12.7	16.1	17.0	18.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)