

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P313304

Luminaire Tested: **24FCZ2-55HE-UNV-L83050-HRP-CP125-W2A-U-5000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P313304
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-55HE-UNV-L83050-HRP-CP125-W2A-U-5000K
Description: 2'X4' TROFFER LED MODULE, HIGH EFFICIENCY RND PERF. LENS, 0.125" POLYCARB SHEET
Light Source: (336) 5000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4082.0 lumens
Efficiency: N/A
Efficacy: 90.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 45.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P313304

CATALOG NUMBER: 24FCZ2-55HE-UNV-L83050-HRP-CP125-W2A-U-5000K

Luminous Intensity Polar Plot





TEST NUMBER: P313304

CATALOG NUMBER: 24FCZ2-55HE-UNV-L83050-HRP-CP125-W2A-U-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	96	93	96	93	90	92	90	87	89	86	84	82
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	77	73	70	67
3	89	78	69	62	86	76	68	62	73	66	61	70	64	59	68	63	58	56
4	81	68	59	52	79	67	59	52	65	57	51	62	56	50	60	54	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	63	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	36	30	57	44	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	24	35	29	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1782	1782	1782
5°	1784	1777	1784
10°	1779	1777	1788
15°	1769	1773	1790
20°	1757	1769	1794
25°	1735	1761	1796
30°	1715	1755	1803
35°	1687	1746	1805
40°	1657	1735	1822
45°	1619	1733	1850
50°	1567	1731	1899
55°	1511	1744	1968
60°	1426	1770	2056
65°	1317	1812	2171
70°	1149	1876	2313
75°	933	1972	2390
80°	689	1933	1933
85°	528	1425	1609



TEST NUMBER: P313304

CATALOG NUMBER: 24FCZ2-55HE-UNV-L83050-HRP-CP125-W2A-U-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.5	3.1
10°-20°	360.3	8.8
20°-30°	548.5	13.4
30°-40°	666.0	16.3
40°-50°	703.6	17.2
50°-60°	663.9	16.3
60°-70°	552.0	13.5
70°-80°	363.2	8.9
80°-90°	99.0	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1034.2	25.3
0°-40°	1700.2	41.7
0°-60°	3067.8	75.2
0°-90°	4082.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4082.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1324	1324	1324	1324	1324	
5°	1321	1321	1316	1321	1321	125
15°	1270	1271	1273	1285	1285	358
25°	1169	1176	1186	1206	1210	539
35°	1027	1039	1063	1090	1099	643
45°	851	868	911	955	972	655
55°	644	672	743	813	839	574
65°	414	461	569	653	682	409
75°	179	262	379	449	460	193
85°	34	75	92	102	104	42
90°	0	0	0	0	0	



TEST NUMBER: P313304

CATALOG NUMBER: 24FCZ2-55HE-UNV-L83050-HRP-CP125-W2A-U-5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1324.4	1324.4	1324.4	1324.4	1324.4
2.5°	1326.1	1324.4	1317.6	1324.4	1324.4
5°	1321.0	1321.0	1315.9	1321.0	1321.0
7.5°	1312.4	1312.4	1309.0	1315.9	1315.9
10°	1302.2	1302.2	1300.5	1309.0	1309.0
12.5°	1286.8	1288.5	1286.8	1297.1	1297.1
15°	1269.7	1271.4	1273.1	1285.1	1285.1
17.5°	1247.5	1250.9	1254.3	1268.0	1269.7
20°	1227.0	1228.7	1235.5	1250.9	1252.6
22.5°	1199.7	1204.8	1213.3	1228.7	1233.8
25°	1168.9	1175.7	1186.0	1206.5	1209.9
27.5°	1139.8	1145.0	1158.6	1180.9	1187.7
30°	1104.0	1112.5	1129.6	1151.8	1160.4
32.5°	1069.8	1078.3	1098.8	1122.8	1129.6
35°	1027.1	1039.0	1062.9	1090.3	1098.8
37.5°	986.0	998.0	1027.1	1057.8	1068.1
40°	943.3	957.0	987.8	1023.6	1037.3
42.5°	897.2	916.0	950.2	989.5	1004.8
45°	851.0	868.1	910.9	955.3	972.4
47.5°	801.5	822.0	868.1	921.1	941.6
50°	748.5	774.1	827.1	885.2	907.4
52.5°	695.5	724.6	784.4	849.3	873.3
55°	644.3	671.6	743.4	813.4	839.1
57.5°	587.9	622.0	700.7	775.8	801.5
60°	529.8	567.4	657.9	736.5	763.9
62.5°	471.7	514.4	616.9	695.5	724.6
65°	413.6	461.4	569.1	652.8	681.9
67.5°	357.2	410.1	524.6	608.4	637.4
70°	292.2	358.9	476.8	558.8	587.9
72.5°	232.4	309.3	430.6	507.5	533.2
75°	179.4	261.5	379.4	449.4	459.7
77.5°	131.6	213.6	326.4	350.3	352.0
80°	88.9	170.9	249.5	246.1	249.5
82.5°	58.1	128.2	157.2	176.0	177.7
85°	34.2	75.2	92.3	102.5	104.2
87.5°	17.1	25.6	32.5	34.2	37.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)