

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P313504

Luminaire Tested: **24FCZ2-35-UNV-L83050-RDP-CP125-W2A-U-5000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P313504  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: 24FCZ2-35-UNV-L83050-RDP-CP125-W2A-U-5000K  
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS WITH INSERT, 0.125" POLYCARB SHEET  
Light Source: (168) 5000K TUNABLE CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2265.0 lumens  
Efficiency: N/A  
Efficacy: 77.0 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct


Input Watts (W): 29.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P313504

CATALOG NUMBER: 24FCZ2-35-UNV-L83050-RDP-CP125-W2A-U-5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P313504

CATALOG NUMBER: 24FCZ2-35-UNV-L83050-RDP-CP125-W2A-U-5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67
3	88	77	68	62	86	76	67	61	72	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	958	958	958
5°	962	956	961
10°	959	956	961
15°	958	956	962
20°	951	955	965
25°	947	957	967
30°	939	955	970
35°	930	952	974
40°	919	951	987
45°	904	951	1009
50°	884	957	1039
55°	862	973	1086
60°	825	992	1146
65°	773	1026	1216
70°	703	1074	1308
75°	596	1133	1367
80°	470	1141	1106
85°	347	868	971



TEST NUMBER: P313504

CATALOG NUMBER: 24FCZ2-35-UNV-L83050-RDP-CP125-W2A-U-5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	67.6	3.0
10°-20°	194.5	8.6
20°-30°	297.4	13.1
30°-40°	363.5	16.0
40°-50°	387.4	17.1
50°-60°	370.4	16.4
60°-70°	313.8	13.9
70°-80°	210.9	9.3
80°-90°	59.5	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	559.4	24.7
0°-40°	922.9	40.7
0°-60°	1680.8	74.2
0°-90°	2265.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2265.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	712	712	712	712	712	
5°	712	711	708	711	711	68
15°	688	688	686	692	691	194
25°	638	640	645	650	652	294
35°	566	571	580	591	593	355
45°	475	483	500	521	530	367
55°	367	381	415	447	463	327
65°	243	267	322	365	382	241
75°	115	156	218	255	263	123
85°	22	46	56	61	63	28
90°	0	0	0	0	0	



TEST NUMBER: P313504

CATALOG NUMBER: 24FCZ2-35-UNV-L83050-RDP-CP125-W2A-U-5000K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	712.3	712.3	712.3	712.3	712.3
2.5°	713.4	713.4	710.0	712.3	712.3
5°	712.3	711.2	707.8	711.2	711.2
7.5°	708.9	707.8	705.5	708.9	707.8
10°	702.2	702.2	699.9	703.3	703.3
12.5°	696.5	695.4	694.3	698.8	697.7
15°	687.6	687.6	686.4	692.1	690.9
17.5°	676.3	677.5	678.6	683.1	684.2
20°	664.0	666.2	667.3	674.1	674.1
22.5°	652.7	653.9	656.1	662.8	662.8
25°	638.1	640.4	644.9	650.5	651.6
27.5°	623.5	624.6	630.3	638.1	639.3
30°	604.4	607.8	614.5	623.5	624.6
32.5°	587.6	590.9	598.8	607.8	610.0
35°	566.2	570.7	579.7	590.9	593.2
37.5°	547.1	550.5	561.7	574.1	577.5
40°	523.5	530.3	541.5	556.1	561.7
42.5°	499.9	506.7	520.2	539.3	546.0
45°	475.2	483.1	499.9	521.3	530.3
47.5°	450.5	459.5	478.6	503.3	513.4
50°	422.4	433.7	457.3	485.3	496.6
52.5°	395.5	408.9	434.8	466.2	480.8
55°	367.4	380.9	414.6	447.1	462.9
57.5°	335.9	353.9	391.0	428.0	444.9
60°	306.7	323.6	368.5	408.9	425.8
62.5°	275.2	297.7	346.0	388.7	405.6
65°	242.7	267.4	322.4	365.1	382.0
67.5°	213.5	240.4	298.8	341.5	358.4
70°	178.6	212.3	273.0	315.7	332.5
72.5°	146.1	183.1	246.0	287.6	303.3
75°	114.6	156.2	218.0	255.0	262.9
77.5°	85.4	129.2	188.7	204.5	198.9
80°	60.7	103.4	147.2	139.3	142.7
82.5°	39.3	78.6	91.0	103.4	106.7
85°	22.5	46.1	56.2	60.7	62.9
87.5°	10.1	16.9	22.5	22.5	21.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)