

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P313147

Luminaire Tested: **24FCZ2-40HE-UNV-L83050-HRP-CA125-W2A-U-4000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P313147
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-40HE-UNV-L83050-HRP-CA125-W2A-U-4000K
Description: 2'X4' TROFFER LED MODULE, HIGH EFFICIENCY RND PERF. LENS, 0.125" ACRYLIC SHEET
Light Source: (336) 4000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3027.0 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 31.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P313147

CATALOG NUMBER: 24FCZ2-40HE-UNV-L83050-HRP-CA125-W2A-U-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P313147

CATALOG NUMBER: 24FCZ2-40HE-UNV-L83050-HRP-CA125-W2A-U-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	96	93	96	93	90	92	90	87	89	86	84	82
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	77	73	70	67
3	89	78	69	62	86	76	68	62	73	66	61	70	64	59	68	63	58	56
4	81	68	59	52	79	67	59	52	65	57	51	62	56	50	60	54	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	63	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	36	30	57	44	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	24	35	29	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1321	1321	1321
5°	1323	1318	1323
10°	1319	1318	1326
15°	1312	1315	1327
20°	1303	1312	1330
25°	1287	1306	1332
30°	1272	1301	1337
35°	1251	1295	1338
40°	1229	1287	1351
45°	1201	1285	1372
50°	1162	1284	1409
55°	1121	1293	1460
60°	1057	1313	1524
65°	976	1344	1610
70°	852	1391	1715
75°	692	1462	1772
80°	511	1433	1433
85°	391	1056	1193



TEST NUMBER: P313147

CATALOG NUMBER: 24FCZ2-40HE-UNV-L83050-HRP-CA125-W2A-U-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.0	3.1
10°-20°	267.2	8.8
20°-30°	406.7	13.4
30°-40°	493.9	16.3
40°-50°	521.8	17.2
50°-60°	492.3	16.3
60°-70°	409.4	13.5
70°-80°	269.3	8.9
80°-90°	73.4	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	766.9	25.3
0°-40°	1260.8	41.7
0°-60°	2274.9	75.2
0°-90°	3027.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3027.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	982	982	982	982	982	
5°	980	980	976	980	980	93
15°	942	943	944	953	953	266
25°	867	872	880	895	897	400
35°	762	770	788	808	815	477
45°	631	644	675	708	721	486
55°	478	498	551	603	622	426
65°	307	342	422	484	506	303
75°	133	194	281	333	341	143
85°	25	56	68	76	77	31
90°	0	0	0	0	0	



TEST NUMBER: P313147

CATALOG NUMBER: 24FCZ2-40HE-UNV-L83050-HRP-CA125-W2A-U-4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	982.1	982.1	982.1	982.1	982.1
2.5°	983.4	982.1	977.0	982.1	982.1
5°	979.6	979.6	975.8	979.6	979.6
7.5°	973.2	973.2	970.7	975.8	975.8
10°	965.6	965.6	964.4	970.7	970.7
12.5°	954.2	955.5	954.2	961.8	961.8
15°	941.6	942.8	944.1	953.0	953.0
17.5°	925.1	927.6	930.2	940.3	941.6
20°	909.9	911.1	916.2	927.6	928.9
22.5°	889.6	893.4	899.7	911.1	914.9
25°	866.8	871.9	879.5	894.7	897.2
27.5°	845.3	849.1	859.2	875.7	880.7
30°	818.6	825.0	837.6	854.1	860.5
32.5°	793.3	799.6	814.8	832.6	837.6
35°	761.6	770.5	788.2	808.5	814.8
37.5°	731.2	740.1	761.6	784.4	792.0
40°	699.5	709.7	732.5	759.1	769.2
42.5°	665.3	679.2	704.6	733.7	745.1
45°	631.1	643.8	675.4	708.4	721.1
47.5°	594.3	609.5	643.8	683.0	698.3
50°	555.1	574.1	613.3	656.4	672.9
52.5°	515.8	537.3	581.7	629.8	647.6
55°	477.8	498.0	551.3	603.2	622.2
57.5°	435.9	461.3	519.6	575.3	594.3
60°	392.8	420.7	487.9	546.2	566.5
62.5°	349.8	381.4	457.5	515.8	537.3
65°	306.7	342.2	422.0	484.1	505.6
67.5°	264.9	304.1	389.0	451.1	472.7
70°	216.7	266.1	353.6	414.4	435.9
72.5°	172.3	229.4	319.3	376.4	395.4
75°	133.1	193.9	281.3	333.3	340.9
77.5°	97.6	158.4	242.0	259.8	261.1
80°	65.9	126.7	185.0	182.5	185.0
82.5°	43.1	95.0	116.6	130.5	131.8
85°	25.3	55.8	68.4	76.0	77.3
87.5°	12.7	19.0	24.1	25.3	27.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)