

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P313343

Luminaire Tested: **24FCZ2-65HE-UNV-L83050-HRP-CA08-W2A-U-4500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P313343  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: 24FCZ2-65HE-UNV-L83050-HRP-CA08-W2A-U-4500K  
Description: 2'X4' TROFFER LED MODULE, HIGH EFFICIENCY RND PERF. LENS, 0.08" ACRYLIC SHEET  
Light Source: (336) 4500K TUNABLE CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment: 

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4921.0 lumens  
Efficiency: N/A  
Efficacy: 89.1 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 55.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P313343

CATALOG NUMBER: 24FCZ2-65HE-UNV-L83050-HRP-CA08-W2A-U-4500K

### Luminous Intensity Polar Plot





TEST NUMBER: P313343

CATALOG NUMBER: 24FCZ2-65HE-UNV-L83050-HRP-CA08-W2A-U-4500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	96	93	96	93	90	92	90	87	89	86	84	82
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	77	73	70	67
3	89	78	69	62	86	76	68	62	73	66	61	70	64	59	68	63	58	56
4	81	68	59	52	79	67	59	52	65	57	51	62	56	50	60	54	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	63	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	36	30	57	44	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	24	35	29	24	23

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2148	2148	2148
5°	2151	2143	2151
10°	2145	2142	2156
15°	2132	2138	2158
20°	2118	2133	2162
25°	2092	2123	2165
30°	2068	2116	2173
35°	2034	2105	2176
40°	1997	2092	2196
45°	1952	2089	2230
50°	1889	2087	2290
55°	1822	2102	2373
60°	1718	2134	2478
65°	1587	2184	2617
70°	1386	2261	2788
75°	1124	2378	2881
80°	830	2331	2331
85°	636	1717	1941



TEST NUMBER: P313343

CATALOG NUMBER: 24FCZ2-65HE-UNV-L83050-HRP-CA08-W2A-U-4500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	151.2	3.1
10°-20°	434.3	8.8
20°-30°	661.2	13.4
30°-40°	802.9	16.3
40°-50°	848.2	17.2
50°-60°	800.4	16.3
60°-70°	665.5	13.5
70°-80°	437.8	8.9
80°-90°	119.3	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1246.8	25.3
0°-40°	2049.7	41.7
0°-60°	3698.3	75.2
0°-90°	4921.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4921.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1597	1597	1597	1597	1597	
5°	1592	1592	1586	1592	1592	151
15°	1531	1533	1535	1549	1549	432
25°	1409	1417	1430	1454	1459	650
35°	1238	1253	1281	1314	1325	775
45°	1026	1047	1098	1152	1172	790
55°	777	810	896	981	1012	692
65°	499	556	686	787	822	493
75°	216	315	457	542	554	233
85°	41	91	111	124	126	50
90°	0	0	0	0	0	



TEST NUMBER: P313343

CATALOG NUMBER: 24FCZ2-65HE-UNV-L83050-HRP-CA08-W2A-U-4500K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1596.6	1596.6	1596.6	1596.6	1596.6
2.5°	1598.7	1596.6	1588.4	1596.6	1596.6
5°	1592.5	1592.5	1586.3	1592.5	1592.5
7.5°	1582.2	1582.2	1578.1	1586.3	1586.3
10°	1569.8	1569.8	1567.8	1578.1	1578.1
12.5°	1551.3	1553.4	1551.3	1563.7	1563.7
15°	1530.7	1532.8	1534.8	1549.2	1549.2
17.5°	1503.9	1508.0	1512.2	1528.6	1530.7
20°	1479.2	1481.3	1489.5	1508.0	1510.1
22.5°	1446.2	1452.4	1462.7	1481.3	1487.4
25°	1409.1	1417.4	1429.7	1454.5	1458.6
27.5°	1374.1	1380.3	1396.8	1423.6	1431.8
30°	1330.9	1341.2	1361.8	1388.5	1398.8
32.5°	1289.7	1300.0	1324.7	1353.5	1361.8
35°	1238.2	1252.6	1281.4	1314.4	1324.7
37.5°	1188.7	1203.1	1238.2	1275.2	1287.6
40°	1137.2	1153.7	1190.8	1234.0	1250.5
42.5°	1081.6	1104.2	1145.4	1192.8	1211.4
45°	1026.0	1046.6	1098.1	1151.6	1172.2
47.5°	966.2	990.9	1046.6	1110.4	1135.1
50°	902.3	933.3	997.1	1067.2	1093.9
52.5°	838.5	873.5	945.6	1023.9	1052.7
55°	776.7	809.6	896.2	980.6	1011.5
57.5°	708.7	749.9	844.7	935.3	966.2
60°	638.6	684.0	793.2	887.9	920.9
62.5°	568.6	620.1	743.7	838.5	873.5
65°	498.6	556.2	686.0	787.0	822.0
67.5°	430.6	494.4	632.5	733.4	768.4
70°	352.3	432.6	574.8	673.7	708.7
72.5°	280.2	372.9	519.2	611.9	642.8
75°	216.3	315.2	457.4	541.8	554.2
77.5°	158.6	257.5	393.5	422.3	424.4
80°	107.1	206.0	300.8	296.7	300.8
82.5°	70.0	154.5	189.5	212.2	214.3
85°	41.2	90.6	111.2	123.6	125.7
87.5°	20.6	30.9	39.1	41.2	45.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)