

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P313920

Luminaire Tested: **24FCZ2-40-UNV-L83050-CA125-W2A-U-3000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P313920  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-15)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: 24FCZ2-40-UNV-L83050-CA125-W2A-U-3000K  
Description: 2'X4' TROFFER LED MODULE, RIBBED LENS, 0.125" ACRYLIC SHEET  
Light Source: (168) 3000K TUNABLE CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment: 

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3485.0 lumens  
Efficiency: N/A  
Efficacy: 106.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.29 / 1.38  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 32.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P313920  
CATALOG NUMBER: 24FCZ2-40-UNV-L83050-CA125-W2A-U-3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P313920

CATALOG NUMBER: 24FC22-40-UNV-L83050-CA125-W2A-U-3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	92	89	92	89	87	88	86	84	82
2	98	89	81	75	95	87	80	74	83	78	73	80	75	71	77	73	69	67
3	89	77	69	62	86	76	68	61	73	66	60	70	64	59	67	62	58	56
4	81	68	59	52	79	67	58	52	64	57	51	62	56	50	60	54	50	47
5	74	61	52	45	72	60	51	44	58	50	44	56	49	43	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	64	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	37	31	57	45	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	25	35	29	24	23

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1546	1546	1546
5°	1549	1540	1549
10°	1540	1536	1548
15°	1527	1530	1549
20°	1508	1520	1548
25°	1485	1509	1547
30°	1457	1496	1545
35°	1428	1481	1546
40°	1395	1470	1556
45°	1362	1461	1569
50°	1321	1457	1593
55°	1288	1459	1625
60°	1238	1472	1680
65°	1182	1487	1741
70°	1119	1533	1838
75°	998	1599	2008
80°	851	1693	2052
85°	607	1678	1964



TEST NUMBER: P313920

CATALOG NUMBER: 24FCZ2-40-UNV-L83050-CA125-W2A-U-3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.8	3.1
10°-20°	311.0	8.9
20°-30°	469.8	13.5
30°-40°	566.2	16.2
40°-50°	594.4	17.1
50°-60°	556.1	16.0
60°-70°	459.2	13.2
70°-80°	312.9	9.0
80°-90°	106.7	3.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	889.5	25.5
0°-40°	1455.7	41.8
0°-60°	2606.2	74.8
0°-90°	3485.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3485.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1149	1149	1149	1149	1149	
5°	1147	1146	1140	1147	1147	109
15°	1096	1097	1098	1110	1112	309
25°	1000	1005	1016	1036	1042	460
35°	870	879	902	932	941	543
45°	716	731	768	809	824	552
55°	549	571	622	673	693	490
65°	371	402	467	526	547	368
75°	192	236	308	365	386	205
85°	39	78	109	123	127	49
90°	0	0	0	0	0	



TEST NUMBER: P313920

CATALOG NUMBER: 24FCZ2-40-UNV-L83050-CA125-W2A-U-3000K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1149.3	1149.3	1149.3	1149.3	1149.3
2.5°	1150.5	1149.3	1143.5	1149.3	1148.2
5°	1147.0	1145.9	1140.1	1147.0	1147.0
7.5°	1138.9	1138.9	1133.1	1141.2	1142.4
10°	1127.4	1127.4	1123.9	1133.1	1133.1
12.5°	1113.5	1113.5	1113.5	1122.7	1123.9
15°	1096.1	1097.3	1098.4	1110.0	1112.3
17.5°	1075.3	1077.6	1081.1	1095.0	1097.3
20°	1053.4	1055.7	1061.4	1077.6	1081.1
22.5°	1025.6	1031.4	1039.5	1058.0	1061.4
25°	1000.2	1004.8	1016.4	1036.0	1041.8
27.5°	968.9	975.9	990.9	1011.7	1019.8
30°	937.7	944.7	963.2	987.4	994.4
32.5°	904.2	914.6	934.3	959.7	967.8
35°	869.5	878.8	901.9	931.9	941.2
37.5°	831.4	844.1	869.5	901.9	913.4
40°	794.4	808.2	837.1	871.8	885.7
42.5°	757.4	771.2	803.6	842.9	856.8
45°	715.7	730.8	767.8	809.4	824.4
47.5°	674.1	692.6	733.1	777.0	793.2
50°	631.3	652.1	696.1	742.3	760.8
52.5°	593.2	612.8	659.1	708.8	726.1
55°	549.2	571.2	622.1	672.9	692.6
57.5°	504.1	528.4	582.8	638.3	657.9
60°	460.2	486.8	546.9	602.4	624.4
62.5°	417.4	444.0	506.4	564.3	586.2
65°	371.2	402.4	467.1	526.1	546.9
67.5°	327.2	360.8	429.0	486.8	507.6
70°	284.4	316.8	389.7	446.3	467.1
72.5°	238.2	275.2	348.0	407.0	429.0
75°	191.9	235.9	307.6	365.4	386.2
77.5°	149.2	194.3	265.9	313.3	323.8
80°	109.8	156.1	218.5	252.1	264.8
82.5°	70.5	116.8	166.5	190.8	201.2
85°	39.3	77.5	108.7	122.6	127.2
87.5°	16.2	33.5	43.9	49.7	49.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)