

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P313471

Luminaire Tested: **24FCZ2-35HE-UNV-L83050-RDP-CA125-W2A-U-3500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P313471
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-35HE-UNV-L83050-RDP-CA125-W2A-U-3500K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS WITH INSERT, 0.125" ACRYLIC SHEET
Light Source: (336) 3500K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2156.0 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 26
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P313471

CATALOG NUMBER: 24FCZ2-35HE-UNV-L83050-RDP-CA125-W2A-U-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P313471

CATALOG NUMBER: 24FCZ2-35HE-UNV-L83050-RDP-CA125-W2A-U-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67
3	88	77	68	62	86	76	67	61	72	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	912	912	912
5°	916	910	914
10°	913	910	915
15°	912	910	916
20°	905	910	919
25°	902	911	921
30°	894	909	924
35°	885	906	927
40°	875	905	939
45°	861	906	961
50°	842	911	989
55°	820	926	1034
60°	785	944	1091
65°	735	977	1158
70°	669	1022	1245
75°	567	1079	1301
80°	447	1086	1052
85°	330	826	925



TEST NUMBER: P313471

CATALOG NUMBER: 24FCZ2-35HE-UNV-L83050-RDP-CA125-W2A-U-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.3	3.0
10°-20°	185.1	8.6
20°-30°	283.0	13.1
30°-40°	346.0	16.0
40°-50°	368.8	17.1
50°-60°	352.6	16.4
60°-70°	298.7	13.9
70°-80°	200.8	9.3
80°-90°	56.6	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	532.5	24.7
0°-40°	878.5	40.7
0°-60°	1599.9	74.2
0°-90°	2156.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2156.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	678	678	678	678	678	
5°	678	677	674	677	677	64
15°	654	654	653	659	658	185
25°	607	610	614	619	620	280
35°	539	543	552	562	565	338
45°	452	460	476	496	505	349
55°	350	362	395	426	441	311
65°	231	254	307	348	364	229
75°	109	149	208	243	250	117
85°	21	44	54	58	60	26
90°	0	0	0	0	0	



TEST NUMBER: P313471

CATALOG NUMBER: 24FCZ2-35HE-UNV-L83050-RDP-CA125-W2A-U-3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	678.0	678.0	678.0	678.0	678.0
2.5°	679.1	679.1	675.9	678.0	678.0
5°	678.0	676.9	673.7	676.9	676.9
7.5°	674.8	673.7	671.6	674.8	673.7
10°	668.4	668.4	666.2	669.4	669.4
12.5°	663.0	662.0	660.9	665.2	664.1
15°	654.5	654.5	653.4	658.8	657.7
17.5°	643.8	644.8	645.9	650.2	651.3
20°	632.0	634.2	635.2	641.6	641.6
22.5°	621.3	622.4	624.5	630.9	630.9
25°	607.4	609.6	613.8	619.2	620.3
27.5°	593.5	594.6	599.9	607.4	608.5
30°	575.3	578.5	585.0	593.5	594.6
32.5°	559.3	562.5	570.0	578.5	580.7
35°	539.0	543.3	551.8	562.5	564.6
37.5°	520.8	524.0	534.7	546.5	549.7
40°	498.3	504.8	515.5	529.4	534.7
42.5°	475.9	482.3	495.1	513.3	519.7
45°	452.4	459.8	475.9	496.2	504.8
47.5°	428.8	437.4	455.6	479.1	488.7
50°	402.1	412.8	435.2	462.0	472.7
52.5°	376.4	389.3	413.9	443.8	457.7
55°	349.7	362.5	394.6	425.6	440.6
57.5°	319.8	336.9	372.2	407.4	423.5
60°	291.9	308.0	350.8	389.3	405.3
62.5°	262.0	283.4	329.4	370.0	386.1
65°	231.0	254.5	306.9	347.6	363.6
67.5°	203.2	228.9	284.5	325.1	341.1
70°	170.0	202.1	259.9	300.5	316.5
72.5°	139.0	174.3	234.2	273.8	288.7
75°	109.1	148.6	207.5	242.8	250.2
77.5°	81.3	123.0	179.7	194.6	189.3
80°	57.7	98.4	140.1	132.6	135.8
82.5°	37.4	74.9	86.6	98.4	101.6
85°	21.4	43.8	53.5	57.7	59.9
87.5°	9.6	16.0	21.4	21.4	20.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)