

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P313515

Luminaire Tested: **24FCZ2-40HE-UNV-L83050-RDP-CA08-W2A-U-3000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P313515
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-40HE-UNV-L83050-RDP-CA08-W2A-U-3000K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS WITH INSERT, 0.08" ACRYLIC SHEET
Light Source: (336) 3000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2367.0 lumens
Efficiency: N/A
Efficacy: 78.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 30.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P313515

CATALOG NUMBER: 24FCZ2-40HE-UNV-L83050-RDP-CA08-W2A-U-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P313515

CATALOG NUMBER: 24FCZ2-40HE-UNV-L83050-RDP-CA08-W2A-U-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67
3	88	77	68	62	86	76	67	61	72	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1002	1002	1002
5°	1005	999	1004
10°	1003	999	1004
15°	1001	999	1006
20°	994	999	1009
25°	990	1000	1011
30°	981	998	1014
35°	972	995	1018
40°	961	994	1031
45°	945	994	1055
50°	924	1000	1086
55°	901	1016	1135
60°	862	1036	1197
65°	807	1073	1271
70°	734	1122	1367
75°	623	1184	1428
80°	491	1192	1155
85°	363	906	1014



TEST NUMBER: P313515

CATALOG NUMBER: 24FCZ2-40HE-UNV-L83050-RDP-CA08-W2A-U-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.6	3.0
10°-20°	203.2	8.6
20°-30°	310.8	13.1
30°-40°	379.9	16.0
40°-50°	404.9	17.1
50°-60°	387.1	16.4
60°-70°	327.9	13.9
70°-80°	220.4	9.3
80°-90°	62.2	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	584.6	24.7
0°-40°	964.5	40.7
0°-60°	1756.5	74.2
0°-90°	2367.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2367.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	744	744	744	744	744	
5°	744	743	740	743	743	71
15°	718	718	717	723	722	203
25°	667	669	674	680	681	307
35°	592	596	606	618	620	371
45°	497	505	522	545	554	383
55°	384	398	433	467	484	342
65°	254	279	337	382	399	252
75°	120	163	228	266	275	128
85°	24	48	59	63	66	29
90°	0	0	0	0	0	



TEST NUMBER: P313515

CATALOG NUMBER: 24FCZ2-40HE-UNV-L83050-RDP-CA08-W2A-U-3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	744.4	744.4	744.4	744.4	744.4
2.5°	745.5	745.5	742.0	744.4	744.4
5°	744.4	743.2	739.7	743.2	743.2
7.5°	740.8	739.7	737.3	740.8	739.7
10°	733.8	733.8	731.4	735.0	735.0
12.5°	727.9	726.7	725.6	730.3	729.1
15°	718.5	718.5	717.4	723.2	722.0
17.5°	706.8	708.0	709.1	713.8	715.0
20°	693.9	696.2	697.4	704.4	704.4
22.5°	682.1	683.3	685.7	692.7	692.7
25°	666.9	669.2	673.9	679.8	681.0
27.5°	651.6	652.8	658.6	666.9	668.0
30°	631.6	635.2	642.2	651.6	652.8
32.5°	614.0	617.6	625.8	635.2	637.5
35°	591.7	596.4	605.8	617.6	619.9
37.5°	571.8	575.3	587.0	599.9	603.5
40°	547.1	554.2	565.9	581.2	587.0
42.5°	522.5	529.5	543.6	563.5	570.6
45°	496.6	504.8	522.5	544.8	554.2
47.5°	470.8	480.2	500.1	526.0	536.5
50°	441.4	453.2	477.8	507.2	518.9
52.5°	413.3	427.4	454.4	487.2	502.5
55°	383.9	398.0	433.2	467.3	483.7
57.5°	351.0	369.8	408.6	447.3	464.9
60°	320.5	338.1	385.1	427.4	445.0
62.5°	287.6	311.1	361.6	406.2	423.8
65°	253.6	279.4	337.0	381.6	399.2
67.5°	223.1	251.2	312.3	356.9	374.5
70°	186.7	221.9	285.3	329.9	347.5
72.5°	152.6	191.4	257.1	300.6	317.0
75°	119.8	163.2	227.8	266.5	274.7
77.5°	89.2	135.0	197.2	213.7	207.8
80°	63.4	108.0	153.8	145.6	149.1
82.5°	41.1	82.2	95.1	108.0	111.5
85°	23.5	48.1	58.7	63.4	65.7
87.5°	10.6	17.6	23.5	23.5	22.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)