

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P313626

Luminaire Tested: **24FCZ2-50HE-UNV-L83050-RDP-CP125-W2A-U-3500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P313626
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-50HE-UNV-L83050-RDP-CP125-W2A-U-3500K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS WITH INSERT, 0.125" POLYCARB SHEET
Light Source: (336) 3500K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3020.0 lumens
Efficiency: N/A
Efficacy: 78.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 38.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P313626

CATALOG NUMBER: 24FCZ2-50HE-UNV-L83050-RDP-CP125-W2A-U-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P313626

CATALOG NUMBER: 24FCZ2-50HE-UNV-L83050-RDP-CP125-W2A-U-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67
3	88	77	68	62	86	76	67	61	72	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1278	1278	1278
5°	1283	1275	1281
10°	1279	1275	1281
15°	1277	1275	1283
20°	1268	1274	1287
25°	1263	1276	1290
30°	1252	1273	1294
35°	1240	1270	1299
40°	1226	1268	1316
45°	1206	1268	1345
50°	1179	1276	1386
55°	1149	1297	1448
60°	1100	1322	1528
65°	1030	1369	1621
70°	937	1432	1744
75°	794	1511	1822
80°	627	1520	1474
85°	463	1156	1295



TEST NUMBER: P313626

CATALOG NUMBER: 24FCZ2-50HE-UNV-L83050-RDP-CP125-W2A-U-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.1	3.0
10°-20°	259.3	8.6
20°-30°	396.5	13.1
30°-40°	484.7	16.0
40°-50°	516.6	17.1
50°-60°	493.9	16.4
60°-70°	418.4	13.9
70°-80°	281.2	9.3
80°-90°	79.3	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	745.8	24.7
0°-40°	1230.5	40.7
0°-60°	2241.1	74.2
0°-90°	3020.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3020.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	950	950	950	950	950	
5°	950	948	944	948	948	90
15°	917	917	915	923	921	258
25°	851	854	860	867	869	392
35°	755	761	773	788	791	473
45°	634	644	667	695	707	489
55°	490	508	553	596	617	436
65°	324	356	430	487	509	321
75°	153	208	291	340	350	164
85°	30	61	75	81	84	37
90°	0	0	0	0	0	



TEST NUMBER: P313626

CATALOG NUMBER: 24FCZ2-50HE-UNV-L83050-RDP-CP125-W2A-U-3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	949.7	949.7	949.7	949.7	949.7
2.5°	951.2	951.2	946.7	949.7	949.7
5°	949.7	948.2	943.7	948.2	948.2
7.5°	945.2	943.7	940.7	945.2	943.7
10°	936.2	936.2	933.2	937.7	937.7
12.5°	928.7	927.2	925.7	931.7	930.2
15°	916.7	916.7	915.3	922.7	921.2
17.5°	901.8	903.3	904.8	910.8	912.3
20°	885.3	888.3	889.8	898.8	898.8
22.5°	870.3	871.8	874.8	883.8	883.8
25°	850.8	853.8	859.8	867.3	868.8
27.5°	831.4	832.9	840.4	850.8	852.3
30°	805.9	810.4	819.4	831.4	832.9
32.5°	783.4	787.9	798.4	810.4	813.4
35°	755.0	761.0	772.9	787.9	790.9
37.5°	729.5	734.0	749.0	765.5	769.9
40°	698.0	707.0	722.0	741.5	749.0
42.5°	666.6	675.6	693.6	719.0	728.0
45°	633.6	644.1	666.6	695.1	707.0
47.5°	600.7	612.7	638.1	671.1	684.6
50°	563.2	578.2	609.7	647.1	662.1
52.5°	527.3	545.3	579.7	621.7	641.1
55°	489.8	507.8	552.7	596.2	617.2
57.5°	447.9	471.9	521.3	570.7	593.2
60°	408.9	431.4	491.3	545.3	567.7
62.5°	367.0	397.0	461.4	518.3	540.8
65°	323.6	356.5	429.9	486.8	509.3
67.5°	284.6	320.6	398.5	455.4	477.8
70°	238.2	283.1	364.0	420.9	443.4
72.5°	194.7	244.2	328.1	383.5	404.4
75°	152.8	208.2	290.6	340.0	350.5
77.5°	113.8	172.3	251.7	272.6	265.1
80°	80.9	137.8	196.2	185.7	190.2
82.5°	52.4	104.9	121.3	137.8	142.3
85°	30.0	61.4	74.9	80.9	83.9
87.5°	13.5	22.5	30.0	30.0	28.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)