

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P314252

Luminaire Tested: **24FCZ2-35-UNV-L83050-S-CP125-W2A-U-4000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P314252
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-35-UNV-L83050-S-CP125-W2A-U-4000K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS, 0.125" POLYCARB SHEET
Light Source: (168) 4000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3506.0 lumens
Efficiency: N/A
Efficacy: 122.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 28.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P314252

CATALOG NUMBER: 24FCZ2-35-UNV-L83050-S-CP125-W2A-U-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P314252

CATALOG NUMBER: 24FCZ2-35-UNV-L83050-S-CP125-W2A-U-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42
6	70	56	47	40	68	55	47	40	53	46	40	52	45	40	50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1657	1657	1657
5°	1656	1652	1662
10°	1649	1649	1661
15°	1634	1641	1658
20°	1612	1628	1653
25°	1582	1612	1643
30°	1547	1594	1630
35°	1513	1568	1617
40°	1461	1541	1598
45°	1413	1511	1581
50°	1359	1483	1562
55°	1298	1455	1547
60°	1238	1432	1543
65°	1160	1408	1553
70°	1073	1415	1595
75°	961	1442	1685
80°	776	1527	1648
85°	585	1342	1306



TEST NUMBER: P314252

CATALOG NUMBER: 24FCZ2-35-UNV-L83050-S-CP125-W2A-U-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.6	3.3
10°-20°	333.2	9.5
20°-30°	500.8	14.3
30°-40°	596.6	17.0
40°-50°	610.6	17.4
50°-60°	549.7	15.7
60°-70°	431.7	12.3
70°-80°	280.2	8.0
80°-90°	86.7	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	950.6	27.1
0°-40°	1547.2	44.1
0°-60°	2707.5	77.2
0°-90°	3506.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3506.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1232	1232	1232	1232	1232	
5°	1226	1228	1223	1230	1231	117
15°	1173	1176	1178	1188	1190	331
25°	1066	1075	1086	1104	1107	491
35°	921	932	954	978	984	575
45°	743	761	794	824	831	573
55°	554	578	620	653	659	496
65°	364	392	442	479	488	363
75°	185	220	277	315	324	196
85°	38	70	87	85	85	46
90°	0	0	0	0	0	



TEST NUMBER: P314252

CATALOG NUMBER: 24FCZ2-35-UNV-L83050-S-CP125-W2A-U-4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1231.7	1231.7	1231.7	1231.7	1231.7
2.5°	1232.8	1232.8	1227.2	1232.8	1233.9
5°	1226.1	1228.3	1222.8	1229.5	1230.6
7.5°	1219.4	1219.4	1216.1	1222.8	1223.9
10°	1207.2	1208.3	1207.2	1215.0	1216.1
12.5°	1191.6	1193.8	1194.9	1202.7	1203.8
15°	1172.7	1176.0	1178.2	1188.2	1190.5
17.5°	1151.5	1154.8	1160.4	1171.5	1173.8
20°	1125.9	1130.3	1137.0	1151.5	1154.8
22.5°	1098.0	1102.5	1113.6	1127.0	1132.6
25°	1065.7	1074.7	1085.8	1103.6	1107.0
27.5°	1033.5	1041.2	1055.7	1074.7	1079.1
30°	995.6	1007.8	1025.7	1044.6	1049.0
32.5°	958.8	971.1	992.2	1012.3	1017.9
35°	921.0	932.1	954.4	977.8	984.5
37.5°	877.5	892.0	916.5	939.9	946.6
40°	831.9	849.7	877.5	902.0	909.8
42.5°	788.5	807.4	835.2	862.0	870.9
45°	742.8	760.6	794.0	824.1	830.8
47.5°	696.0	716.1	751.7	781.8	792.9
50°	649.2	670.4	708.3	739.5	746.1
52.5°	602.5	624.7	664.8	698.2	701.6
55°	553.5	578.0	620.3	652.6	659.3
57.5°	508.9	530.1	575.7	609.2	617.0
60°	459.9	483.3	532.3	563.5	573.5
62.5°	413.2	437.7	488.9	520.1	529.0
65°	364.2	392.0	442.1	478.9	487.8
67.5°	321.8	348.6	402.0	437.7	446.6
70°	272.8	302.9	359.7	396.5	405.4
72.5°	230.5	261.7	318.5	354.1	367.5
75°	184.9	220.5	277.3	315.2	324.1
77.5°	140.3	181.5	239.4	268.4	268.4
80°	100.2	143.7	197.1	210.5	212.7
82.5°	65.7	108.0	145.9	144.8	144.8
85°	37.9	70.2	86.9	84.6	84.6
87.5°	14.5	29.0	31.2	31.2	30.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)