

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P314227

Luminaire Tested: **24FCZ2-35HE-UNV-L83050-S-CP125-W2A-U-4000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P314227
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-35HE-UNV-L83050-S-CP125-W2A-U-4000K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS, 0.125" POLYCARB SHEET
Light Source: (336) 4000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3468.0 lumens
Efficiency: N/A
Efficacy: 130.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 26.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P314227

CATALOG NUMBER: 24FCZ2-35HE-UNV-L83050-S-CP125-W2A-U-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P314227

CATALOG NUMBER: 24FCZ2-35HE-UNV-L83050-S-CP125-W2A-U-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42
6	70	56	47	40	68	55	47	40	53	46	40	52	45	40	50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1639	1639	1639
5°	1638	1634	1644
10°	1631	1631	1643
15°	1616	1623	1640
20°	1595	1610	1636
25°	1565	1594	1626
30°	1530	1576	1612
35°	1496	1551	1600
40°	1445	1525	1581
45°	1398	1494	1564
50°	1344	1467	1545
55°	1284	1439	1530
60°	1224	1417	1527
65°	1147	1392	1536
70°	1062	1400	1578
75°	951	1426	1667
80°	768	1511	1630
85°	579	1326	1292



TEST NUMBER: P314227

CATALOG NUMBER: 24FCZ2-35HE-UNV-L83050-S-CP125-W2A-U-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.3	3.3
10°-20°	329.6	9.5
20°-30°	495.4	14.3
30°-40°	590.1	17.0
40°-50°	604.0	17.4
50°-60°	543.7	15.7
60°-70°	427.0	12.3
70°-80°	277.1	8.0
80°-90°	85.7	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	940.3	27.1
0°-40°	1530.4	44.1
0°-60°	2678.1	77.2
0°-90°	3468.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3468.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1218	1218	1218	1218	1218	
5°	1213	1215	1210	1216	1217	115
15°	1160	1163	1166	1175	1178	327
25°	1054	1063	1074	1092	1095	486
35°	911	922	944	967	974	568
45°	735	752	785	815	822	566
55°	548	572	614	646	652	491
65°	360	388	437	474	482	359
75°	183	218	274	312	321	194
85°	38	69	86	84	84	45
90°	0	0	0	0	0	



TEST NUMBER: P314227

CATALOG NUMBER: 24FCZ2-35HE-UNV-L83050-S-CP125-W2A-U-4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1218.3	1218.3	1218.3	1218.3	1218.3
2.5°	1219.4	1219.4	1213.9	1219.4	1220.5
5°	1212.8	1215.0	1209.5	1216.1	1217.2
7.5°	1206.2	1206.2	1202.9	1209.5	1210.6
10°	1194.1	1195.2	1194.1	1201.8	1202.9
12.5°	1178.7	1180.9	1182.0	1189.7	1190.8
15°	1159.9	1163.3	1165.5	1175.4	1177.6
17.5°	1139.0	1142.3	1147.8	1158.8	1161.0
20°	1113.7	1118.1	1124.7	1139.0	1142.3
22.5°	1086.1	1090.5	1101.6	1114.8	1120.3
25°	1054.2	1063.0	1074.0	1091.7	1095.0
27.5°	1022.3	1030.0	1044.3	1063.0	1067.4
30°	984.8	996.9	1014.5	1033.3	1037.7
32.5°	948.4	960.6	981.5	1001.3	1006.8
35°	911.0	922.0	944.0	967.2	973.8
37.5°	868.0	882.4	906.6	929.7	936.3
40°	822.9	840.5	868.0	892.3	900.0
42.5°	779.9	798.6	826.2	852.6	861.4
45°	734.7	752.4	785.4	815.2	821.8
47.5°	688.5	708.3	743.6	773.3	784.3
50°	642.2	663.1	700.6	731.4	738.0
52.5°	595.9	618.0	657.6	690.7	694.0
55°	547.5	571.7	613.6	645.5	652.1
57.5°	503.4	524.3	569.5	602.6	610.3
60°	454.9	478.1	526.5	557.4	567.3
62.5°	408.7	432.9	483.6	514.4	523.2
65°	360.2	387.8	437.3	473.7	482.5
67.5°	318.4	344.8	397.7	432.9	441.7
70°	269.9	299.6	355.8	392.2	401.0
72.5°	228.0	258.9	315.0	350.3	363.5
75°	182.9	218.1	274.3	311.7	320.6
77.5°	138.8	179.6	236.8	265.5	265.5
80°	99.1	142.1	195.0	208.2	210.4
82.5°	65.0	106.9	144.3	143.2	143.2
85°	37.5	69.4	85.9	83.7	83.7
87.5°	14.3	28.6	30.8	30.8	29.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)