

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P313722

Luminaire Tested: **24FCZ2-65HE-UNV-L83050-RDP-CA125-W2A-U-4000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P313722
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-65HE-UNV-L83050-RDP-CA125-W2A-U-4000K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS WITH INSERT, 0.125" ACRYLIC SHEET
Light Source: (336) 4000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4205.0 lumens
Efficiency: N/A
Efficacy: 78.2 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 53.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P313722

CATALOG NUMBER: 24FCZ2-65HE-UNV-L83050-RDP-CA125-W2A-U-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P313722

CATALOG NUMBER: 24FCZ2-65HE-UNV-L83050-RDP-CA125-W2A-U-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67
3	88	77	68	62	86	76	68	61	72	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1779	1779	1779
5°	1786	1775	1783
10°	1781	1775	1784
15°	1778	1775	1787
20°	1765	1774	1792
25°	1759	1777	1796
30°	1743	1773	1802
35°	1727	1768	1809
40°	1707	1766	1832
45°	1679	1766	1873
50°	1641	1777	1930
55°	1600	1805	2016
60°	1532	1841	2127
65°	1434	1906	2258
70°	1304	1994	2429
75°	1106	2103	2537
80°	872	2117	2053
85°	644	1610	1803



TEST NUMBER: P313722

CATALOG NUMBER: 24FCZ2-65HE-UNV-L83050-RDP-CA125-W2A-U-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.4	3.0
10°-20°	361.0	8.6
20°-30°	552.1	13.1
30°-40°	674.9	16.0
40°-50°	719.3	17.1
50°-60°	687.7	16.4
60°-70°	582.6	13.9
70°-80°	391.5	9.3
80°-90°	110.4	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1038.5	24.7
0°-40°	1713.4	40.7
0°-60°	3120.4	74.2
0°-90°	4205.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4205.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1322	1322	1322	1322	1322	
5°	1322	1320	1314	1320	1320	126
15°	1276	1276	1274	1285	1283	360
25°	1185	1189	1197	1208	1210	546
35°	1051	1060	1076	1097	1101	659
45°	882	897	928	968	984	680
55°	682	707	770	830	859	607
65°	450	496	599	678	709	447
75°	213	290	405	474	488	228
85°	42	86	104	113	117	52
90°	0	0	0	0	0	



TEST NUMBER: P313722

CATALOG NUMBER: 24FCZ2-65HE-UNV-L83050-RDP-CA125-W2A-U-4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1322.4	1322.4	1322.4	1322.4	1322.4
2.5°	1324.4	1324.4	1318.2	1322.4	1322.4
5°	1322.4	1320.3	1314.0	1320.3	1320.3
7.5°	1316.1	1314.0	1309.8	1316.1	1314.0
10°	1303.6	1303.6	1299.4	1305.7	1305.7
12.5°	1293.2	1291.1	1289.0	1297.3	1295.2
15°	1276.5	1276.5	1274.4	1284.8	1282.7
17.5°	1255.6	1257.7	1259.8	1268.1	1270.2
20°	1232.7	1236.8	1238.9	1251.4	1251.4
22.5°	1211.8	1213.9	1218.1	1230.6	1230.6
25°	1184.7	1188.9	1197.2	1207.6	1209.7
27.5°	1157.6	1159.7	1170.1	1184.7	1186.8
30°	1122.1	1128.4	1140.9	1157.6	1159.7
32.5°	1090.8	1097.1	1111.7	1128.4	1132.6
35°	1051.2	1059.6	1076.2	1097.1	1101.3
37.5°	1015.8	1022.0	1042.9	1065.8	1072.1
40°	971.9	984.5	1005.3	1032.4	1042.9
42.5°	928.1	940.7	965.7	1001.2	1013.7
45°	882.3	896.9	928.1	967.8	984.5
47.5°	836.4	853.1	888.5	934.4	953.2
50°	784.2	805.1	848.9	901.0	921.9
52.5°	734.2	759.2	807.2	865.6	892.7
55°	682.0	707.1	769.6	830.1	859.3
57.5°	623.6	657.0	725.8	794.7	825.9
60°	569.4	600.7	684.1	759.2	790.5
62.5°	511.0	552.7	642.4	721.7	752.9
65°	450.5	496.4	598.6	677.9	709.1
67.5°	396.3	446.3	554.8	634.1	665.3
70°	331.6	394.2	506.8	586.1	617.4
72.5°	271.1	340.0	456.8	533.9	563.1
75°	212.7	289.9	404.6	473.5	488.1
77.5°	158.5	239.9	350.4	379.6	369.2
80°	112.6	191.9	273.2	258.6	264.9
82.5°	73.0	146.0	168.9	191.9	198.1
85°	41.7	85.5	104.3	112.6	116.8
87.5°	18.8	31.3	41.7	41.7	39.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)