

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P313851

Luminaire Tested: **24FCZ2-35HE-UNV-L83050-CP125-W2A-U-3500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P313851  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-15)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: 24FCZ2-35HE-UNV-L83050-CP125-W2A-U-3500K  
Description: 2'X4' TROFFER LED MODULE, RIBBED LENS, 0.125" POLYCARB SHEET  
Light Source: (336) 3500K TUNABLE CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment: 

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3143.0 lumens  
Efficiency: N/A  
Efficacy: 120.9 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.29 / 1.38  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 26  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P313851

CATALOG NUMBER: 24FCZ2-35HE-UNV-L83050-CP125-W2A-U-3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P313851

CATALOG NUMBER: 24FCZ2-35HE-UNV-L83050-CP125-W2A-U-3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	92	89	92	89	87	88	86	84	82
2	98	89	81	75	95	87	80	74	83	78	73	80	75	71	77	73	69	67
3	89	77	69	62	86	76	68	61	73	66	60	70	64	59	67	62	58	56
4	81	68	59	52	79	67	58	52	64	57	51	62	56	50	60	54	50	47
5	74	61	52	45	72	60	51	44	58	50	44	56	49	43	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	64	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	37	31	57	45	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	25	35	29	24	23

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1395	1395	1395
5°	1397	1389	1397
10°	1389	1385	1396
15°	1377	1380	1397
20°	1360	1371	1396
25°	1339	1361	1395
30°	1314	1349	1393
35°	1288	1336	1394
40°	1258	1326	1403
45°	1228	1318	1415
50°	1192	1314	1436
55°	1162	1316	1465
60°	1117	1327	1515
65°	1066	1341	1570
70°	1009	1382	1657
75°	900	1442	1811
80°	768	1527	1850
85°	548	1513	1771



TEST NUMBER: P313851

CATALOG NUMBER: 24FCZ2-35HE-UNV-L83050-CP125-W2A-U-3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	98.1	3.1
10°-20°	280.5	8.9
20°-30°	423.7	13.5
30°-40°	510.6	16.2
40°-50°	536.0	17.1
50°-60°	501.5	16.0
60°-70°	414.1	13.2
70°-80°	282.2	9.0
80°-90°	96.2	3.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	802.2	25.5
0°-40°	1312.9	41.8
0°-60°	2350.4	74.8
0°-90°	3143.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3143.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1036	1036	1036	1036	1036	
5°	1034	1033	1028	1034	1034	98
15°	989	990	991	1001	1003	279
25°	902	906	917	934	940	415
35°	784	792	813	840	849	490
45°	646	659	692	730	744	498
55°	495	515	561	607	625	442
65°	335	363	421	474	493	332
75°	173	213	277	330	348	185
85°	36	70	98	110	115	44
90°	0	0	0	0	0	



TEST NUMBER: P313851

CATALOG NUMBER: 24FCZ2-35HE-UNV-L83050-CP125-W2A-U-3500K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1036.5	1036.5	1036.5	1036.5	1036.5
2.5°	1037.6	1036.5	1031.3	1036.5	1035.5
5°	1034.4	1033.4	1028.2	1034.4	1034.4
7.5°	1027.1	1027.1	1021.9	1029.2	1030.3
10°	1016.7	1016.7	1013.6	1021.9	1021.9
12.5°	1004.2	1004.2	1004.2	1012.5	1013.6
15°	988.6	989.6	990.7	1001.1	1003.2
17.5°	969.8	971.9	975.0	987.5	989.6
20°	950.0	952.1	957.3	971.9	975.0
22.5°	925.0	930.2	937.5	954.2	957.3
25°	902.0	906.2	916.6	934.3	939.6
27.5°	873.9	880.1	893.7	912.4	919.7
30°	845.7	852.0	868.6	890.5	896.8
32.5°	815.5	824.8	842.6	865.5	872.8
35°	784.2	792.5	813.4	840.5	848.8
37.5°	749.8	761.2	784.2	813.4	823.8
40°	716.4	728.9	755.0	786.3	798.8
42.5°	683.0	695.5	724.7	760.2	772.7
45°	645.5	659.0	692.4	730.0	743.5
47.5°	607.9	624.6	661.1	700.8	715.4
50°	569.4	588.1	627.8	669.5	686.2
52.5°	535.0	552.7	594.4	639.2	654.9
55°	495.3	515.1	561.0	606.9	624.6
57.5°	454.7	476.6	525.6	575.6	593.3
60°	415.0	439.0	493.2	543.3	563.1
62.5°	376.4	400.4	456.7	508.9	528.7
65°	334.7	362.9	421.3	474.5	493.2
67.5°	295.1	325.4	386.9	439.0	457.8
70°	256.5	285.7	351.4	402.5	421.3
72.5°	214.8	248.2	313.9	367.1	386.9
75°	173.1	212.7	277.4	329.5	348.3
77.5°	134.5	175.2	239.8	282.6	292.0
80°	99.1	140.8	197.1	227.3	238.8
82.5°	63.6	105.3	150.2	172.1	181.4
85°	35.5	69.9	98.0	110.5	114.7
87.5°	14.6	30.2	39.6	44.8	44.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)