

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P256286

Luminaire Tested: **HC4R10D010-HM412935-42RMDC**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P256286
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1805-779-41)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC4R10D010-HM412935-42RMDC
Description: HALO COMMERCIAL 4" ROUND, RETROFIT FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 875.5 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.03
Luminous Opening: Circular (Dia: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P256286

CATALOG NUMBER: HC4R10D010-HM412935-42RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P256286

CATALOG NUMBER: HC4R10D010-HM412935-42RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82		88	84	81		85	82	80	78
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80	76	74	72
5	90	81	75	70	88	80	74	70	78	73	69		76	72	68		75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70	66	63	61
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62	57	54	52
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58	53	50	49
10	68	58	51	47	67	57	51	47	56	51	47		55	50	47		55	50	47	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	65268
5°	65752
10°	66858
15°	68882
20°	70442
25°	67821
30°	57820
35°	41736
40°	27048
45°	16773
50°	6626
55°	2413
60°	1384
65°	807
70°	684
75°	452
80°	0
85°	0



TEST NUMBER: P256286

CATALOG NUMBER: HC4R10D010-HM412935-42RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.2	7.3
10°-20°	193.1	22.1
20°-30°	283.7	32.4
30°-40°	219.7	25.1
40°-50°	93.2	10.7
50°-60°	16.3	1.9
60°-70°	4.1	0.5
70°-80°	1.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	541.0	61.8
0°-40°	760.7	86.9
0°-60°	870.2	99.4
0°-90°	875.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	875.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	670	
5°	672	64
15°	683	193
25°	631	284
35°	351	220
45°	122	93
55°	14	16
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P256286

CATALOG NUMBER: HC4R10D010-HM412935-42RMDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	669.7
2.5°	669.7
5°	672.1
7.5°	673.3
10°	675.6
12.5°	679.2
15°	682.7
17.5°	683.9
20°	679.2
22.5°	662.6
25°	630.7
27.5°	581.1
30°	513.8
32.5°	433.5
35°	350.8
37.5°	275.2
40°	212.6
42.5°	163.0
45°	121.7
47.5°	78.0
50°	43.7
52.5°	24.8
55°	14.2
57.5°	9.4
60°	7.1
62.5°	4.7
65°	3.5
67.5°	3.5
70°	2.4
72.5°	1.2
75°	1.2
77.5°	1.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)