

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P256304

Luminaire Tested: **HC4R30D010-HM434827-42RMDC**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P256304
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1805-779-41)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC4R30D010-HM434827-42RMDC
Description: HALO COMMERCIAL 4" ROUND, RETROFIT FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2616.5 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.03
Luminous Opening: Circular (Dia: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 26
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P256304

CATALOG NUMBER: HC4R30D010-HM434827-42RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P256304

CATALOG NUMBER: HC4R30D010-HM434827-42RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82		88	84	81		85	82	80	78
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80	76	74	72
5	90	81	75	70	88	80	74	70	78	73	69		76	72	68		75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70	66	63	61
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62	57	54	52
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58	53	50	49
10	68	58	51	47	67	57	51	47	56	51	47		55	50	47		55	50	47	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	195062
5°	196502
10°	199823
15°	205858
20°	210516
25°	202700
30°	172809
35°	124733
40°	80837
45°	50114
50°	19801
55°	7204
60°	4132
65°	2444
70°	2023
75°	1318
80°	0
85°	0



TEST NUMBER: P256304

CATALOG NUMBER: HC4R30D010-HM434827-42RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	192.0	7.3
10°-20°	577.0	22.1
20°-30°	847.9	32.4
30°-40°	656.5	25.1
40°-50°	278.6	10.6
50°-60°	48.6	1.9
60°-70°	12.2	0.5
70°-80°	3.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1616.9	61.8
0°-40°	2273.4	86.9
0°-60°	2600.6	99.4
0°-90°	2616.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2616.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2002	
5°	2009	192
15°	2040	577
25°	1885	848
35°	1048	657
45°	364	279
55°	42	49
65°	11	12
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P256304

CATALOG NUMBER: HC4R30D010-HM434827-42RMDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	2001.5
2.5°	2001.5
5°	2008.6
7.5°	2012.1
10°	2019.2
12.5°	2029.8
15°	2040.3
17.5°	2043.9
20°	2029.8
22.5°	1980.3
25°	1885.0
27.5°	1736.8
30°	1535.6
32.5°	1295.5
35°	1048.4
37.5°	822.5
40°	635.4
42.5°	487.1
45°	363.6
47.5°	233.0
50°	130.6
52.5°	74.1
55°	42.4
57.5°	28.2
60°	21.2
62.5°	14.1
65°	10.6
67.5°	10.6
70°	7.1
72.5°	3.5
75°	3.5
77.5°	3.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)