

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P256318

Luminaire Tested: **HC4R40D010-HM434935-42RMDC**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P256318  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1805-779-41)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC4R40D010-HM434935-42RMDC  
Description: HALO COMMERCIAL 4" ROUND, RETROFIT FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3233.0 lumens  
Efficiency: N/A  
Efficacy: 80.8 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.03  
Luminous Opening: Circular (Dia: 0.38' x H: 0')  
CIE Type: Direct


Input Watts (W): 40  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P256318

CATALOG NUMBER: HC4R40D010-HM434935-42RMDC

### Luminous Intensity Polar Plot





TEST NUMBER: P256318

CATALOG NUMBER: HC4R40D010-HM434935-42RMDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82		88	84	81		85	82	80	78
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80	76	74	72
5	90	81	75	70	88	80	74	70	78	73	69		76	72	68		75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70	66	63	61
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62	57	54	52
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58	53	50	49
10	68	58	51	47	67	57	51	47	56	51	47		55	50	47		55	50	47	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	241024
5°	242795
10°	246899
15°	254369
20°	260112
25°	250466
30°	213524
35°	154119
40°	99882
45°	61925
50°	24471
55°	8886
60°	5107
65°	3021
70°	2479
75°	1657
80°	0
85°	0



TEST NUMBER: P256318

CATALOG NUMBER: HC4R40D010-HM434935-42RMDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	237.2	7.3
10°-20°	713.0	22.1
20°-30°	1047.7	32.4
30°-40°	811.2	25.1
40°-50°	344.3	10.6
50°-60°	60.0	1.9
60°-70°	15.1	0.5
70°-80°	4.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1997.8	61.8
0°-40°	2809.0	86.9
0°-60°	3213.4	99.4
0°-90°	3233.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3233.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2473	
5°	2482	237
15°	2521	713
25°	2329	1048
35°	1295	811
45°	449	344
55°	52	60
65°	13	15
75°	4	5
85°	0	0
90°	0	



TEST NUMBER: P256318

CATALOG NUMBER: HC4R40D010-HM434935-42RMDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2473.1
2.5°	2473.1
5°	2481.8
7.5°	2486.2
10°	2494.9
12.5°	2508.0
15°	2521.1
17.5°	2525.5
20°	2508.0
22.5°	2446.9
25°	2329.2
27.5°	2146.0
30°	1897.4
32.5°	1600.8
35°	1295.4
37.5°	1016.3
40°	785.1
42.5°	601.9
45°	449.3
47.5°	287.9
50°	161.4
52.5°	91.6
55°	52.3
57.5°	34.9
60°	26.2
62.5°	17.4
65°	13.1
67.5°	13.1
70°	8.7
72.5°	4.4
75°	4.4
77.5°	4.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)