

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P313989

Luminaire Tested: **24FCZ2-45-UNV-L83050-CP250-W2A-U-5000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P313989
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-15)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-45-UNV-L83050-CP250-W2A-U-5000K
Description: 2'X4' TROFFER LED MODULE, RIBBED LENS, 0.250" POLYCARB SHEET
Light Source: (168) 5000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4076.0 lumens
Efficiency: N/A
Efficacy: 103.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.29 / 1.38
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 39.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P313989
CATALOG NUMBER: 24FCZ2-45-UNV-L83050-CP250-W2A-U-5000K

Luminous Intensity Polar Plot





TEST NUMBER: P313989

CATALOG NUMBER: 24FCZ2-45-UNV-L83050-CP250-W2A-U-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	92	89	92	89	87	88	86	84	82
2	98	89	81	75	95	87	80	74	83	78	73	80	75	71	77	73	69	67
3	89	77	69	62	86	76	68	61	73	66	60	70	64	59	67	62	58	56
4	81	68	59	52	79	67	58	52	64	57	51	62	56	50	60	54	50	47
5	74	61	52	45	72	60	51	44	58	50	44	56	49	43	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	64	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	37	31	57	45	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	25	35	29	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1809	1809	1809
5°	1812	1801	1812
10°	1801	1796	1811
15°	1786	1790	1812
20°	1764	1778	1810
25°	1737	1765	1809
30°	1704	1750	1807
35°	1670	1733	1808
40°	1632	1720	1819
45°	1593	1709	1835
50°	1546	1704	1863
55°	1507	1707	1900
60°	1448	1721	1965
65°	1382	1739	2037
70°	1309	1793	2149
75°	1167	1870	2348
80°	996	1980	2400
85°	710	1962	2297



TEST NUMBER: P313989

CATALOG NUMBER: 24FCZ2-45-UNV-L83050-CP250-W2A-U-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.2	3.1
10°-20°	363.8	8.9
20°-30°	549.4	13.5
30°-40°	662.2	16.2
40°-50°	695.2	17.1
50°-60°	650.4	16.0
60°-70°	537.1	13.2
70°-80°	366.0	9.0
80°-90°	124.8	3.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1040.4	25.5
0°-40°	1702.6	41.8
0°-60°	3048.1	74.8
0°-90°	4076.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4076.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1344	1344	1344	1344	1344	
5°	1342	1340	1333	1342	1342	127
15°	1282	1283	1285	1298	1301	361
25°	1170	1175	1189	1212	1218	538
35°	1017	1028	1055	1090	1101	636
45°	837	855	898	947	964	646
55°	642	668	728	787	810	573
65°	434	471	546	615	640	431
75°	224	276	360	427	452	239
85°	46	91	127	143	149	58
90°	0	0	0	0	0	



TEST NUMBER: P313989

CATALOG NUMBER: 24FCZ2-45-UNV-L83050-CP250-W2A-U-5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1344.2	1344.2	1344.2	1344.2	1344.2
2.5°	1345.6	1344.2	1337.5	1344.2	1342.9
5°	1341.5	1340.2	1333.4	1341.5	1341.5
7.5°	1332.1	1332.1	1325.3	1334.8	1336.1
10°	1318.5	1318.5	1314.5	1325.3	1325.3
12.5°	1302.3	1302.3	1302.3	1313.1	1314.5
15°	1282.0	1283.4	1284.7	1298.2	1301.0
17.5°	1257.7	1260.4	1264.4	1280.7	1283.4
20°	1232.0	1234.7	1241.5	1260.4	1264.4
22.5°	1199.5	1206.3	1215.8	1237.4	1241.5
25°	1169.8	1175.2	1188.7	1211.7	1218.5
27.5°	1133.3	1141.4	1159.0	1183.3	1192.8
30°	1096.8	1104.9	1126.5	1154.9	1163.0
32.5°	1057.5	1069.7	1092.7	1122.4	1131.9
35°	1017.0	1027.8	1054.8	1090.0	1100.8
37.5°	972.3	987.2	1017.0	1054.8	1068.4
40°	929.1	945.3	979.1	1019.7	1035.9
42.5°	885.8	902.0	939.9	985.9	1002.1
45°	837.1	854.7	898.0	946.6	964.2
47.5°	788.4	810.1	857.4	908.8	927.7
50°	738.4	762.7	814.1	868.2	889.8
52.5°	693.8	716.7	770.8	829.0	849.3
55°	642.4	668.1	727.6	787.1	810.1
57.5°	589.6	618.0	681.6	746.5	769.5
60°	538.2	569.3	639.7	704.6	730.3
62.5°	488.2	519.3	592.3	659.9	685.6
65°	434.1	470.6	546.3	615.3	639.7
67.5°	382.7	421.9	501.7	569.3	593.7
70°	332.7	370.5	455.7	522.0	546.3
72.5°	278.6	321.9	407.1	476.0	501.7
75°	224.5	275.9	359.7	427.3	451.7
77.5°	174.5	227.2	311.0	366.5	378.7
80°	128.5	182.6	255.6	294.8	309.7
82.5°	82.5	136.6	194.7	223.1	235.3
85°	46.0	90.6	127.1	143.3	148.8
87.5°	18.9	39.2	51.4	58.2	58.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)