

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579702

Luminaire Tested: **HC410D010-HM40525830-41WDBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579702
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC410D010-HM40525830-41WDBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 918.7 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579702

CATALOG NUMBER: HC410D010-HM40525830-41WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P579702

CATALOG NUMBER: HC410D010-HM40525830-41WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93																
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85			85																
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72			72																
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49																
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45			45																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	91633
5°	91711
10°	91895
15°	93219
20°	90912
25°	85292
30°	75444
35°	57370
40°	36148
45°	20741
50°	11015
55°	4580
60°	1233
65°	1022
70°	793
75°	667
80°	497
85°	991



TEST NUMBER: P579702

CATALOG NUMBER: HC410D010-HM40525830-41WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.4	7.7
10°-20°	204.4	22.3
20°-30°	285.3	31.1
30°-40°	234.8	25.6
40°-50°	96.7	10.5
50°-60°	21.8	2.4
60°-70°	3.5	0.4
70°-80°	1.3	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	560.2	61.0
0°-40°	795.0	86.5
0°-60°	913.5	99.4
0°-90°	918.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	918.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	743	
5°	741	70
15°	730	204
25°	627	285
35°	381	235
45°	119	97
55°	21	22
65°	4	3
75°	1	1
85°	1	0
90°	0	



TEST NUMBER: P579702

CATALOG NUMBER: HC410D010-HM40525830-41WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	742.9
2.5°	739.2
5°	740.7
7.5°	737.9
10°	733.7
12.5°	731.5
15°	730.0
17.5°	717.3
20°	692.6
22.5°	661.4
25°	626.7
27.5°	584.9
30°	529.7
32.5°	461.7
35°	381.0
37.5°	299.5
40°	224.5
42.5°	163.5
45°	118.9
47.5°	85.0
50°	57.4
52.5°	36.1
55°	21.3
57.5°	10.6
60°	5.0
62.5°	4.2
65°	3.5
67.5°	2.8
70°	2.2
72.5°	1.4
75°	1.4
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)