

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579704

Luminaire Tested: **HC410D010-HM40525830-41MDH**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P579704  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-5)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC410D010-HM40525830-41MDH  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1041.3 lumens  
Efficiency: N/A  
Efficacy: 105.2 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.91  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P579704

CATALOG NUMBER: HC410D010-HM40525830-41MDH

### Luminous Intensity Polar Plot





TEST NUMBER: P579704

CATALOG NUMBER: HC410D010-HM40525830-41MDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86	86	86	86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79	79	79	79
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73	73	73	73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67	67	67	67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62	62	62	62
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58	58	58	58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51	51	51	51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	47	47	47	47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	134804
5°	131989
10°	124735
15°	116498
20°	106545
25°	95145
30°	79887
35°	56210
40°	34667
45°	20758
50°	12224
55°	6086
60°	3133
65°	2072
70°	1262
75°	1048
80°	497
85°	991



TEST NUMBER: P579704

CATALOG NUMBER: HC410D010-HM40525830-41MDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	99.5	9.6
10°-20°	255.0	24.5
20°-30°	318.0	30.5
30°-40°	234.3	22.5
40°-50°	96.3	9.3
50°-60°	28.1	2.7
60°-70°	7.2	0.7
70°-80°	2.2	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	672.6	64.6
0°-40°	906.8	87.1
0°-60°	1031.3	99.0
0°-90°	1041.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1041.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1093	
5°	1066	100
15°	912	255
25°	699	318
35°	373	234
45°	119	96
55°	28	28
65°	7	7
75°	2	2
85°	1	0
90°	0	



TEST NUMBER: P579704

CATALOG NUMBER: HC410D010-HM40525830-41MDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1092.9
2.5°	1081.6
5°	1066.0
7.5°	1037.6
10°	995.9
12.5°	954.8
15°	912.3
17.5°	864.8
20°	811.7
22.5°	756.4
25°	699.1
27.5°	635.3
30°	560.9
32.5°	471.0
35°	373.3
37.5°	286.9
40°	215.3
42.5°	159.3
45°	119.0
47.5°	87.9
50°	63.7
52.5°	43.9
55°	28.3
57.5°	17.0
60°	12.7
62.5°	9.2
65°	7.1
67.5°	5.0
70°	3.5
72.5°	2.8
75°	2.2
77.5°	1.4
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)