

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592610

Luminaire Tested: **HC410D010-HM40525850-41WDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592610
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC410D010-HM40525850-41WDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1280.4 lumens
Efficiency: N/A
Efficacy: 129.3 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.11
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592610
CATALOG NUMBER: HC410D010-HM40525850-41WDC

Luminous Intensity Polar Plot





TEST NUMBER: P592610

CATALOG NUMBER: HC410D010-HM40525850-41WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | |
| 1 | 113 | 110 | 107 | 105 | 110 | 108 | 105 | 103 | 104 | 102 | 100 | 100 | 98 | 97 | 97 | 95 | 94 | 92 | | |
| 2 | 107 | 101 | 97 | 93 | 104 | 100 | 96 | 92 | 96 | 93 | 90 | 93 | 91 | 88 | 91 | 88 | 86 | 85 | | |
| 3 | 101 | 93 | 88 | 84 | 98 | 92 | 87 | 83 | 89 | 85 | 82 | 87 | 83 | 80 | 85 | 82 | 79 | 77 | | |
| 4 | 95 | 86 | 80 | 76 | 93 | 85 | 79 | 75 | 83 | 78 | 74 | 81 | 77 | 73 | 79 | 75 | 72 | 71 | | |
| 5 | 89 | 80 | 73 | 69 | 87 | 79 | 73 | 68 | 77 | 72 | 68 | 75 | 71 | 67 | 74 | 70 | 66 | 65 | | |
| 6 | 84 | 74 | 67 | 63 | 82 | 73 | 67 | 62 | 72 | 66 | 62 | 70 | 65 | 62 | 69 | 65 | 61 | 60 | | |
| 7 | 79 | 69 | 62 | 57 | 78 | 68 | 62 | 57 | 67 | 61 | 57 | 65 | 60 | 57 | 64 | 60 | 56 | 55 | | |
| 8 | 75 | 64 | 57 | 53 | 73 | 63 | 57 | 53 | 62 | 57 | 53 | 61 | 56 | 52 | 60 | 56 | 52 | 51 | | |
| 9 | 70 | 60 | 53 | 49 | 69 | 59 | 53 | 49 | 58 | 53 | 49 | 57 | 52 | 48 | 56 | 52 | 48 | 47 | | |
| 10 | 67 | 56 | 50 | 45 | 66 | 55 | 49 | 45 | 55 | 49 | 45 | 54 | 49 | 45 | 53 | 48 | 45 | 43 | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 103438 |
| 5° | 104959 |
| 10° | 108240 |
| 15° | 115655 |
| 20° | 122559 |
| 25° | 121221 |
| 30° | 108786 |
| 35° | 84670 |
| 40° | 57370 |
| 45° | 35812 |
| 50° | 15505 |
| 55° | 5183 |
| 60° | 1283 |
| 65° | 905 |
| 70° | 541 |
| 75° | 381 |
| 80° | 568 |
| 85° | 0 |



TEST NUMBER: P592610

CATALOG NUMBER: HC410D010-HM40525850-41WDC

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 81.4 | 6.4 |
| 10°-20° | 257.1 | 20.1 |
| 20°-30° | 402.9 | 31.5 |
| 30°-40° | 347.7 | 27.2 |
| 40°-50° | 159.9 | 12.5 |
| 50°-60° | 27.1 | 2.1 |
| 60°-70° | 3.1 | 0.2 |
| 70°-80° | 1.1 | 0.1 |
| 80°-90° | 0.1 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 741.4 | 57.9 |
| 0°-40° | 1089.1 | 85.1 |
| 0°-60° | 1276.1 | 99.7 |
| 0°-90° | 1280.4 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1280.4 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 839 | |
| 5° | 848 | 81 |
| 15° | 906 | 257 |
| 25° | 891 | 403 |
| 35° | 562 | 348 |
| 45° | 205 | 160 |
| 55° | 24 | 27 |
| 65° | 3 | 3 |
| 75° | 1 | 1 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P592610

CATALOG NUMBER: HC410D010-HM40525850-41WDC

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 838.6 |
| 2.5° | 838.6 |
| 5° | 847.7 |
| 7.5° | 856.0 |
| 10° | 864.2 |
| 12.5° | 881.6 |
| 15° | 905.7 |
| 17.5° | 926.1 |
| 20° | 933.7 |
| 22.5° | 922.3 |
| 25° | 890.7 |
| 27.5° | 839.4 |
| 30° | 763.8 |
| 32.5° | 668.8 |
| 35° | 562.3 |
| 37.5° | 455.2 |
| 40° | 356.3 |
| 42.5° | 272.4 |
| 45° | 205.3 |
| 47.5° | 144.2 |
| 50° | 80.8 |
| 52.5° | 44.5 |
| 55° | 24.1 |
| 57.5° | 12.1 |
| 60° | 5.2 |
| 62.5° | 3.8 |
| 65° | 3.1 |
| 67.5° | 2.3 |
| 70° | 1.5 |
| 72.5° | 1.5 |
| 75° | 0.8 |
| 77.5° | 0.8 |
| 80° | 0.8 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)