

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P314055

Luminaire Tested: **24FCZ2-55HE-UNV-L83050-CP187-W2A-U-3000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P314055
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-15)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-55HE-UNV-L83050-CP187-W2A-U-3000K
Description: 2'X4' TROFFER LED MODULE, RIBBED LENS, 0.187" POLYCARB SHEET
Light Source: (336) 3000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4487.0 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.29 / 1.38
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 43
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P314055

CATALOG NUMBER: 24FCZ2-55HE-UNV-L83050-CP187-W2A-U-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P314055

CATALOG NUMBER: 24FCZ2-55HE-UNV-L83050-CP187-W2A-U-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	92	89	92	89	87	88	86	84	82
2	98	89	81	75	95	87	80	74	83	78	73	80	75	71	77	73	69	67
3	89	77	69	62	86	76	68	61	73	66	60	70	64	59	67	62	58	56
4	81	68	59	52	79	67	58	52	64	57	51	62	56	50	60	54	50	47
5	74	61	52	45	72	60	51	44	58	50	44	56	49	43	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	64	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	37	31	57	45	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	25	35	29	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1991	1991	1991
5°	1995	1983	1995
10°	1983	1977	1993
15°	1966	1970	1995
20°	1942	1957	1993
25°	1912	1943	1991
30°	1876	1927	1989
35°	1839	1907	1990
40°	1796	1893	2003
45°	1753	1881	2020
50°	1701	1876	2051
55°	1659	1879	2092
60°	1594	1895	2163
65°	1521	1915	2242
70°	1441	1974	2366
75°	1285	2059	2585
80°	1096	2180	2641
85°	781	2160	2529



TEST NUMBER: P314055

CATALOG NUMBER: 24FCZ2-55HE-UNV-L83050-CP187-W2A-U-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.0	3.1
10°-20°	400.4	8.9
20°-30°	604.8	13.5
30°-40°	729.0	16.2
40°-50°	765.3	17.1
50°-60°	715.9	16.0
60°-70°	591.3	13.2
70°-80°	402.9	9.0
80°-90°	137.4	3.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1145.3	25.5
0°-40°	1874.3	41.8
0°-60°	3355.5	74.8
0°-90°	4487.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4487.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1480	1480	1480	1480	1480	
5°	1477	1475	1468	1477	1477	140
15°	1411	1413	1414	1429	1432	398
25°	1288	1294	1309	1334	1341	592
35°	1120	1131	1161	1200	1212	700
45°	922	941	988	1042	1061	711
55°	707	735	801	866	892	631
65°	478	518	601	677	704	474
75°	247	304	396	470	497	263
85°	51	100	140	158	164	63
90°	0	0	0	0	0	



TEST NUMBER: P314055

CATALOG NUMBER: 24FCZ2-55HE-UNV-L83050-CP187-W2A-U-3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1479.8	1479.8	1479.8	1479.8	1479.8
2.5°	1481.3	1479.8	1472.3	1479.8	1478.3
5°	1476.8	1475.3	1467.9	1476.8	1476.8
7.5°	1466.4	1466.4	1458.9	1469.4	1470.8
10°	1451.5	1451.5	1447.0	1458.9	1458.9
12.5°	1433.6	1433.6	1433.6	1445.5	1447.0
15°	1411.3	1412.8	1414.3	1429.2	1432.1
17.5°	1384.5	1387.5	1391.9	1409.8	1412.8
20°	1356.2	1359.2	1366.6	1387.5	1391.9
22.5°	1320.5	1327.9	1338.3	1362.2	1366.6
25°	1287.7	1293.7	1308.6	1333.9	1341.3
27.5°	1247.5	1256.5	1275.8	1302.6	1313.0
30°	1207.3	1216.3	1240.1	1271.4	1280.3
32.5°	1164.2	1177.6	1202.9	1235.6	1246.0
35°	1119.5	1131.4	1161.2	1199.9	1211.8
37.5°	1070.4	1086.8	1119.5	1161.2	1176.1
40°	1022.7	1040.6	1077.8	1122.5	1140.3
42.5°	975.1	993.0	1034.7	1085.3	1103.1
45°	921.5	940.9	988.5	1042.1	1061.4
47.5°	867.9	891.7	943.8	1000.4	1021.3
50°	812.8	839.6	896.2	955.7	979.6
52.5°	763.7	789.0	848.6	912.6	934.9
55°	707.1	735.4	800.9	866.4	891.7
57.5°	649.1	680.3	750.3	821.8	847.1
60°	592.5	626.7	704.2	775.6	803.9
62.5°	537.4	571.7	652.1	726.5	754.8
65°	477.9	518.1	601.4	677.4	704.2
67.5°	421.3	464.5	552.3	626.7	653.5
70°	366.2	407.9	501.7	574.6	601.4
72.5°	306.7	354.3	448.1	524.0	552.3
75°	247.1	303.7	396.0	470.4	497.2
77.5°	192.0	250.1	342.4	403.4	416.8
80°	141.4	201.0	281.4	324.5	340.9
82.5°	90.8	150.4	214.4	245.6	259.0
85°	50.6	99.7	139.9	157.8	163.8
87.5°	20.8	43.2	56.6	64.0	64.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)